

## Fluke 424D, 419D and 414D Laser Distance Meters

### **Technical Data**

Professional-grade distance measuring tools that are fast, easy to use, and fit in your pocket.

The Fluke laser distance meters use the most advanced distance measuring technology. These meters are fast, accurate, durable, and easy to use—just point and shoot. Their simple design and easy one-button operation means you spend less time measuring while increasing the reliability of the answers that you need.

The compact and handy Fluke laser distance meters were designed for indoor and limited outdoor applications. All three models are simple to operate, with the Fluke durability and quality you expect. And, with specific function buttons, different tasks can be completed quickly and easily.

The extra bright laser is clearly visible so you can always see your targeting point even if the target object is in a hard-to-reach spot, or a long distance away. These units have a large LCD screen and buttons positioned for one-handed measurements.

### **Features and benefits**

### All meters offer:

- Reduction of estimation errors, saving both time and money
- The most advanced laser technology for distance measurement
- Instant measurement with one-button operation
- Easy targeting with bright laser
- Quick calculation of area (square footage) and volume
- Easy addition and subtraction of measurements
- Minimum/maximum function
- Improved battery life from automatic shut-off feature
- Pythagoras calculation for determining distance indirectly from two other measurements
- Pouch with Fluke logo
- Three-year warranty





Fluke 414D, 419D and 424D Laser Distance Meters.

### The 424D and 419D additionally offers:

- · Improved visibility with backlit screen
- Ability to measure up to 80 m (260 ft) for 419D, 100 m (330 ft) for 424D
- Tripod mode allows you to mount to a tripod for measuring long distances
- Stake out function
- Enhanced Pythagoras calculation for determining distance indirectly from three other measurements
- Audible keypad feedback
- Storage of the last twenty measurements for quick recall of distance
- Strong environmental protection with IP54 (water spray and dust proof) sealing

### The 424D additionally offers:

- Inclination sensor for taking measurements in hard to reach areas
- Compass provides a "heading" for distance measurement
- Automated endpiece correction: when measuring from an edge or corner, a built-in sensor detects the position of this bracket and automatically changes the reference point



### **General specifications**

	414D	419D	424D			
Distance measurement						
Typical measuring tolerance[1]	± 2.0 mm <sup>[3]</sup>	± 1.0 mm <sup>[3]</sup>				
Maximum measuring tolerance <sup>[2]</sup>	$\pm 3.0 \text{ mm}^{[3]}$ $\pm 2.0 \text{ mm}^{[3]}$					
Range at Leica target plate GZM26	50 m/165 ft	80 m/260 ft	100 m/330 ft			
Typical range[1]	40 m/130 ft	80 m/260 ft	80 m/260 ft			
Range at unfavorable condition <sup>[4]</sup>	35 m/115 ft	60 m/195 ft	60 m/195 ft			
Smallest unit displayed	1 mm /¹/16 in 1 mm /¹/32 in					
Power Range Technology™	no	yes	yes			
$\varnothing$ laser point at distances	6/30/60 mm (10/50/100 m) 0.23/1.18/2.36 in (32.8/164/330)	6/30/60 mm (10/50/100 m) 0.23/1.18/2.36 in (32.8/164/330)				
Tilt measurement						
Measuring tolerance to laser beam <sup>[5]</sup>	no	no	± 0.2°			
Measuring tolerance to housing <sup>[5]</sup>	no	no	± 0.2°			
Range	no	no	360°			
General						
Laser class	II					
Laser type	635 nm, <1 mW					
Protection class	IP40 IP54					
Automatic laser off	After 90 seconds					
Automatic power off	After 180 seconds					
Battery life (2 x AAA) 1.5 V NEDA 24A/IEC LRO3	up to 3,000 measurements	up to 5,000 n	neasurements			
Size (HxWxD)	116 mm x 53 mm x 33 mm (4.56 in x 2.08 in x 1.29 in)	127 mm x 56 mm x 33 mm (5 in x 2.20 in x 1.29 in)	127 mm x 56 mm x 33 mm (5 in x 2.20 in x 1.29 in)			
Weight (with batteries)	113 g (3.98 oz)	153 g (5.39 oz)	158 g (5.57 oz)			
Temperature range: Storage Operation	-25 °C to +70°C (-13 °F to +158 °F) 0 °C to +40 °C (32 °F to +104 °F)	-25 °C to +70°C (-13 °F to +158 °F) -10 °C to +50 °C (14 °F to +122 °F)				
Calibration cycle	Not applicable	Not applicable	tilt and compass			
Maximum altitude	3000 m	3000 m	3000 m			
Maximum relative humidity	85 % at 20 °F to 120 °F (-7 °C to 50 °C)	85 % at 20 °F to 120 °F (-7 °C to 50 °C)	85 % at 20 °F to 120 °F (-7 °C to 50 °C)			
Safety	CAN/CSA-C22.2 No. 61010-1-04, UL Std. No. 61010-1 (2nd Edition), ISA-82.02.01, IEC Standard No. 61010-1:2001, EN60825-1:2007 (Class II)					
EMC	61326-1:2006					

<sup>[1]</sup> Applies for 100 % target reflectivity (white painted wall), low background illumination, 25 °C (13 °F). [2] Applies for 10 % to 500 % target reflectivity, high background illumination, -10 °C to +50 °C (14 °F to +122 °F).

### **Ordering information**

Fluke 424D Laser Distance Meter Fluke 419D Laser Distance Meter Fluke 414D Laser Distance Meter

All models include: Laser distance meter, two AAA batteries, users manual on CD, quick reference guide, vinyl carrying pouch, and three-year warranty

### Why use a distance meter?

Instant measurements up to 100 meters/330 feet. Just point, click, done. Measure with greater accuracy. Up to  $\pm$  1 mm. No scales to interpret or misread.

Do the work of two. Instead of holding the tape, your helper can do other jobs.

**Speed up the job.** Easily measure hard-to-access areas, like high ceilings, without climbing a ladder.

**Keep it on the level.** New inclination sensor on the Fluke 424D helps with leveling, height tracking, and measuring around obstacles.

**Reduce estimating errors—let the meters do the math.** Find area and volume. Easily add and subtract distances. Use Pythagoras calculations for height.

**Trust Fluke tools.** Rugged and reliable, dust- and splash-proof, you can work indoors and out with confidence, because they're Fluke tools.

For more information visit www.fluke.com/distance

### Fluke. Keeping your world up and running.®

### Fluke Corporation

PO Box 9090, Everett, WA USA 98206

#### Fluke Europe B.V.

PO Box 1186, 5602 BD Eindhoven, The Netherlands

### For more information call:

In the U.S.A. (800) 443-5853 or Fax (425) 446-5116 In Europe/M-East/Africa (31 40) 2 675 200 or Fax (31 40) 2 675 222 In Canada (800)-36-FLUKE or Fax (905) 890-6866 From other countries +1 (425) 446-5500 or Fax +1 (425) 446-5116


Web access: http://www.fluke.com

©2007-2012 Fluke Corporation. Specifications subject to change without notice. Printed in U.S.A. 4/2012 3028711E D-EN-N

Modification of this document is not permitted without written permission from Fluke Corporation.

<sup>[3]</sup> Tolerances apply from 0.05 m to 10 m (0.001 ft to 32.8 ft) with a confidence level of 95 %. The maximum tolerance may deteriorate to 0.1 mm/m (0.003 in/ft) between 10 m to 30 m (32.8 ft to 98.4 ft) and to 0.15 mm/m (0.005 in/ft) for distances above 30 m (98.4 ft).

<sup>[4]</sup> Applies for 100 % target reflectivity, background illumination between 10'000 lux and 30'000 lux. [5] After user calibration. Additional angle related deviation of  $\pm$  0.01° per degree up to  $\pm$  45° in each quadrant. Applies at room temperature. For the whole operating temperature range the maximum deviation increases by  $\pm$  0.1°.



## **Temperature solutions:**

fit for your job, fit for your pocket

Distance to spot

**Temperature range** 

Hot/cold



Fluke 62MAX Fluke 62MAX+

- Min/max/avg/dif
- Dust/water resistant (IP54)

Fluke 561

- Combined IR + contact
- HVAC applications

Fluke 566 Fluke 568

- Data logging
- Combined IR + contact

Fluke 572-2

- · Data logging
- Hi/Lo alarm
- Min/max/avg/dif
- IR + contact

markers



Fluke VT04 Fluke VT02

- Image storage
- Analysis software

MEM

**Exact spot positioning** Heat map **Features** 62MAX 572-2 VT02 **Infrared thermometer Multipurpose thermometer** High Visual IR thermometer termperature infrared thermometer Temperature -30 to 500 °C -30 to 650°C -40 to 550 °C -40 to 650 °C -40 to 800 °C -30 to 900 °C -10 to 250 °C -10 to 250 °C range D:S 10:1 12:1 12:1 30:1 50:1 60:1 6:1 9:1 Laser sighting Single laser Dual laser Single-point Single-point Single-point Offset dual No laser No laser laser laser laser laser necessary necessary £84 £100 £131 E 339 429 £ 395 £ 595





## Fluke CNX™ Wireless Test Tools. Safer. Easier. Faster.



### Your tools - connected.

Take readings quicker. Solve problems faster. Fluke CNX<sup>™</sup> wireless test tools work together to help you troubleshoot faster. With the CNX<sup>™</sup> team, measurements are:

- Remote
- Simultaneous
- Recordable

Connect any of the CNX<sup>™</sup> Modules to your test point, and view the results up to 20 meters away on the CNX<sup>™</sup> Wireless Multimeter. You'll save time, with less run-around collecting multiple measurements.







Fluke CNX 3000
Wireless Multimeter















## Fluke 6200-2 and 6500-2 Portable Appliance Testers

NEW

Perform more tests each day! The low weight, small size, one-touch solutions.

Improved auto-test capabilities to help you increase the number of tests completed each day. Designed to work faster without compromising safety – yours or your customer's.

- · 'One-touch' testing: dedicated key per test
- Save time: pre-set pass/fail levels
- Easy reading: large backlit display
- · Rapid data entry: integral keyboard
- Back-up data storage and transfer: additional USB memory drive
- Pre-set, auto-test sequences

**NEW colour Dot Matrix Display:** 

Superior visibility and viewing angle

NEW 250V Insulation Test
NEW 110V Test Functionality

NEW RCD Test

### **Optional accessories:**

- DMS 0702/PAT software
- SP-SCAN-6000 barcode scanner
- SP6000 printer

Also available as a kit.





## Fluke TestGuide

The NEW TestGuide app shows electricians in short and clear steps what the actions are for the most common measurements, what to look at and how to interpret the results. You will also find background articles and in-depth application notes which can be downloaded or send to your email.

Free Download!

www.fluke.co.uk/testguide



# Special promotions New Fluke Multifunction Installation Tester Kits



Fast, lightweight, easy to use, robust and reliable installation tester. Now all models with great offers!

- Fast high current loop test
- Reliable 3-wire loop test
- No complex multi-level menus: rotary dial clearly indicates selected function
- Easy test lead compensation: Zero adapter
- Extended memory\*
- mΩ resolution: loop & line resistance\*
- Variable RCD current mode for customised settings
- Test smooth DC sensitive RCDs\*
- PASS/FAIL indication for RCD tests



Now with FREE Cabinet key\*\*



Fluke 1652C-TPOLEKIT

### Fluke 1653B / Software / Fluke T130 kit







Fluke 1653B-TPOLEKIT/D

### Fluke 1654B / Software / Fluke T150 kit





Now with FREE Cabinet key\*\*



Fluke 1654B-TPOLEKIT/D

<sup>\* 1654</sup>B only

<sup>\*\*</sup> Free Cabinet key offer valid until 30.06.2014, only available direct from Fluke by using special offer voucher, proof of purchase required.

Go to www.fluke.co.uk/promotions to download the voucher and view full terms and conditions or contact Fluke directly.

## Fluke Clamp Meters: Readings you can rely on

**True RMS** 

Wire in tight spaces - panels out of reach - extra large conductors. Noise free measurements for every workspace.



	Fluke 365	Fluke 323	Fluke 324	Fluke 325	Fluke 373	Fluke 374	Fluke 375	Fluke 376
Jaw opening	18 mm	30 mm	30 mm	30 mm	32 mm	34 mm	34 mm	34 mm
Current AC TRMS	200 A	400 A	400 A	400 A	600 A	600 A	600 A	1000 A
Current DC	200 A	-	-	400 A	-	600 A	600 A	1000 A
Voltage AC	600 V	1000 V						
Voltage DC	600 V	1000 V						
Continuity	•	•	•	•	•	•	•	•
Resistance	•	•	•	•	•	•	•	•
Capacitance	-	-	•	•	•	•	•	•
Frequency	-	-	-	•	ı	-	•	•
Contact temperature	-	-	-10 400°C	-10 400°C	-	-	-	-
In-rush	-	-	-	-	•	•	•	•
i-Flex	-	-	-	-	-	optional	optional	included (18")
Price	£ 199	£ 99	£ 118	£ 159	£ 176	£ 265	£ 317	£ 379

\* Free 2AC offer valid until 30.06.2014, only available direct from Fluke by using special offer voucher, proof of purchase required. Go to www.fluke.co.uk/promotions to download the voucher and view full terms and conditions or contact Fluke directly.



electrician's toolbelt page! www.fluke.co.uk/toolbelt

## **Earth ground testing**

Simpler and Faster.

The Fluke 1623-2 and 1625-2 earth ground testers are accurate, safe and very easy to use. Perform basic earth ground tests up to the most advanced tests. Several test methods provide quick and precise impedance measurements:

- · 3-and-4-pole Fall-of-Potential
- · 2-pole
- · selective
- · stakeless

NEW USB Data Storage and transfer NEW larger display: Automatic Frequency Control (AFC)

## NEW world class accessories:

- Easy to use reels
- Heavy-duty stakes
- Colour coded wires (faster set up)



Fluke 1625-2 £ 1599

## Fluke 110 series Digital Multimeters

Economic investment in accuracy, simple operation for easy and fast measurements.




	Fluke 113	Fluke 114	Fluke 115	Fluke 116	Fluke 117
True RMS readings	•	•	•	•	•
Display backlight	•	•	•	•	•
Voltalert™, Non-contact voltage detection	-	-	-	-	•
Built-in thermometer (probe included)	-	-	-	•	-
LoZ (low input impedance)	-	•	-	•	•
Microamps to test flame sensors	-	-	-	•	-
Frequency, capacitance, Diode test	-/●/●	-	●/●/●	●/●/●	●/●/●
Recommended AC current clamp**	-	i200s	i200s	i200s	i200s
Recommended pouch	C25	C25	C25	C25	C25
CAT III	600V	600V	600V	600V	600V
Price	£ 109	£ 128	£ 151	£ 174	£ 180

\* Free 2AC offer valid until 30.06.2014, only available direct from Fluke by using special offer voucher, proof of purchase required. Go to www.fluke.co.uk/promotions to download the voucher and view full terms and conditions or contact Fluke directly.

FREE 2AC \*

FREE 2AC \*

\*\* for AC current 1 - 200 A



## **PLAY AND WIN!**

Play the Electrician Game and win rugged and innovative Fluke tools!

www.fluke.co.uk/game

### Laser Distance Meters

Fluke laser distance meters will become the next essential item on your toolbelt.



Fluke 414D £ 99
Fluke 419D £ 185
Fluke 424D £ 283

### **VoltAlert™**

When the tip of the Fluke VoltAlert AC voltage detector glows red and the unit beeps, you know there is voltage on the line.

## Fluke 2AC £ 19

### **Two Pole Testers from Fluke**



Fluke T150 £ 109



Fluke T130 £89



Fluke T110 £56



Fluke T90

## **T5/H5/1AC Kit**

Fluke T5-1000
 Electrical Tester
 Fluke 1AC-II Volt Alert

• Fluke H5 holster

£ 142 Save up to 20%\*

## T5-600/62MAX+/1AC Kit

- Fluke T5-600 Electrical Tester
- Fluke 62MAX+ IR Thermometer
- Fluke 1AC-II Volt Alert
- C115 soft meter case

£ 197
Save up to
330/6\*



## 62MAX+/323/1AC Kit

- Fluke 62MAX+ IR Thermometer
- Fluke 323 Clamp Meter
- Fluke 1AC-II Volt Alert
- C115 Soft meter case

£ 200
Save up to



## 414D/62MAX+ Kit

- Fluke 414D Laser
   Distance Meter
- Fluke 62MAX+ IR Thermometer

£ 150
Save up to



\* Saving based on the cost of purchasing the individual items separately at manufacturers recommended resale price.