



Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 12

Loctite3430A -Kit Component

sds no. : 298562
V005.1

Revision: 05.11.2013
printing date: 05.03.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Loctite3430A -Kit Component

Contains:

Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight \leq 700)
RP Bisphenol F-epichlorhydrin resin, MW \leq 700
Bisphenol A diglycidyl ether polymer

1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:
Epoxy adhesive

1.3. Details of the supplier of the safety data sheet

Henkel Limited
2 Bishop Square Business Park
AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933
Fax-no.: +44 1606 863762

ua-productsafety.uk@uk.henkel.com

1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification (CLP):

Skin irritation	Category 2
H315 Causes skin irritation.	
Serious eye irritation	Category 2
H319 Causes serious eye irritation.	
Skin sensitizer	Category 1
H317 May cause an allergic skin reaction.	
Chronic hazards to the aquatic environment	Category 2
H411 Toxic to aquatic life with long lasting effects.	

Classification (DPD):

Sensitizing
R43 May cause sensitisation by skin contact.
Xi - Irritant
R36/38 Irritating to eyes and skin.
N - Dangerous for the environment
R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

2.2. Label elements

Label elements (CLP):

Hazard pictogram:



Signal word:

Warning

Hazard statement:

H315 Causes skin irritation.
H317 May cause an allergic skin reaction.
H319 Causes serious eye irritation.
H411 Toxic to aquatic life with long lasting effects.

**Precautionary statement:
Prevention**

P273 Avoid release to the environment.
P280 Wear protective gloves.

**Precautionary statement:
Response**

P302+P352 IF ON SKIN: Wash with plenty of soap and water.
P333+P313 If skin irritation or rash occurs: Get medical advice/attention.
P337+P313 If eye irritation persists: Get medical advice/attention.

Label elements (DPD):

Xi - Irritant

N - Dangerous for the environment



Risk phrases:

R36/38 Irritating to eyes and skin.
R43 May cause sensitisation by skin contact.
R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

Safety phrases:

S24 Avoid contact with skin.
S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
S28 After contact with skin, wash immediately with plenty of water and soap.
S37 Wear suitable gloves.
S61 Avoid release to the environment. Refer to special instructions/Safety data sheets.

Additional labeling:

Contains epoxy constituents. See information supplied by the manufacturer.
For consumer use only: S2 Keep out of the reach of children
S46 If swallowed, seek medical advice immediately and show this container or label.

Contains:

Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700),
 RP Bisphenol F-epichlorhydrin resin, MW<=700,
 Bisphenol A diglycidyl ether polymer

2.3. Other hazards

None if used properly.

SECTION 3: Composition/information on ingredients**General chemical description:**

Epoxy resin

Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	500-033-5 500-033-5 01-2119456619-26	30- 40 %	Serious eye irritation 2 H319 Skin irritation 2 H315 Skin sensitizer 1 H317 Chronic hazards to the aquatic environment 2 H411
RP Bisphenol F-epichlorhydrin resin, MW<=700 28064-14-4		30- 40 %	Serious eye irritation 2 H319 Skin irritation 2 H315 Skin sensitizer 1 H317 Chronic hazards to the aquatic environment 2 H411
Bisphenol A diglycidyl ether polymer 25085-99-8		20- 30 %	Serious eye irritation 2 H319 Skin irritation 2 H315 Skin sensitizer 1 H317 Chronic hazards to the aquatic environment 2 H411

For full text of the H - statements and other abbreviations see section 16 "Other information".
 Substances without classification may have community workplace exposure limits available.

Declaration of ingredients according to DPD (EC) No 1999/45:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	500-033-5 500-033-5 01-2119456619-26	30 - 40 %	R43 Xi - Irritant; R36/38 N - Dangerous for the environment; R51/53
RP Bisphenol F-epichlorhydrin resin, MW<=700 28064-14-4		30 - 40 %	Xi - Irritant; R36/38, R43 N - Dangerous for the environment; R51/53
Bisphenol A diglycidyl ether polymer 25085-99-8		20 - 30 %	N - Dangerous for the environment; R51/53 Xi - Irritant; R36/38, R43

For full text of the R-Phrases indicated by codes see section 16 'Other Information'.
 Substances without classification may have community workplace exposure limits available.

SECTION 4: First aid measures**4.1. Description of first aid measures**

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.
Seek medical advice.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes). Seek medical attention if necessary.

Ingestion:

Rinse out mouth, drink 1-2 glasses of water, do not induce vomiting.
Seek medical advice.

4.2. Most important symptoms and effects, both acute and delayed

SKIN: Rash, Urticaria.

SKIN: Redness, inflammation.

EYE: Irritation, conjunctivitis.

4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media:

Carbon dioxide, foam, powder

Extinguishing media which must not be used for safety reasons:

High pressure waterjet

5.2. Special hazards arising from the substance or mixture

Do not expose to direct heat.
Oxides of carbon, oxides of nitrogen, irritating organic vapors.

5.3. Advice for firefighters

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Avoid skin and eye contact.
Ensure adequate ventilation.

6.2. Environmental precautions

Do not let product enter drains.

6.3. Methods and material for containment and cleaning up

For small spills wipe up with paper towel and place in container for disposal.
For large spills absorb onto inert absorbent material and place in sealed container for disposal.
Wash spillage site thoroughly with soap and water or detergent solution.
Dispose of contaminated material as waste according to Chapter 13.

6.4. Reference to other sections

See advice in chapter 8

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Use only in well-ventilated areas.
 Avoid skin and eye contact.
 Prolonged or repeated skin contact should be avoided to minimise any risk of sensitisation.
 See advice in chapter 8

Hygiene measures:

Wash hands before work breaks and after finishing work.
 Do not eat, drink or smoke while working.
 Good industrial hygiene practices should be observed.

7.2. Conditions for safe storage, including any incompatibilities

Store in a cool, well-ventilated place.

7.3. Specific end use(s)

Epoxy adhesive

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational Exposure Limits**

Valid for
 Great Britain

None

Predicted No-Effect Concentration (PNEC):

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (freshwater)					0,006 mg/L	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (marine water)					0,0006 mg/L	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	aqua (intermittent releases)					0,018 mg/L	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	STP					10 mg/L	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sediment (freshwater)				0,996 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sediment (marine water)				0,0996 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	soil				0,196 mg/kg		
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	oral					11 mg/kg food	

Derived No-Effect Level (DNEL):

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	worker	Dermal	Acute/short term exposure - systemic effects		8,33 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	worker	inhalation	Acute/short term exposure - systemic effects		12,25 mg/m ³	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	worker	Dermal	Long term exposure - systemic effects		8,33 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	worker	inhalation	Long term exposure - systemic effects		12,25 mg/m ³	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Dermal	Acute/short term exposure - systemic effects		3,571 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	Dermal	Long term exposure - systemic effects		3,571 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	inhalation	Acute/short term exposure - systemic effects		0,75 mg/m ³	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	inhalation	Long term exposure - systemic effects		0,75 mg/m ³	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	oral	Acute/short term exposure - systemic effects		0,75 mg/kg bw/day	
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	general population	oral	Long term exposure - systemic effects		0,75 mg/kg bw/day	

Biological Exposure Indices:

None

8.2. Exposure controls:

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30

minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374):

nitrile rubber (NBR; ≥ 0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Tightly fitting safety goggles

Skin protection:

Wear suitable protective clothing.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

Appearance	liquid liquid transparent
Odor	odorless
Odour threshold	No data available / Not applicable
pH	Not applicable
Initial boiling point	No data available / Not applicable
Flash point	> 100,0 °C (> 212 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Density	1,17 g/cm ³
()	
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Not miscible
(Solvent: Water)	
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

9.2. Other information

No data available / Not applicable

SECTION 10: Stability and reactivity**10.1. Reactivity**

Reaction with strong acids.

Reacts with strong oxidants.

10.2. Chemical stability

Stable under recommended storage conditions.

10.3. Possibility of hazardous reactions

See section reactivity

10.4. Conditions to avoid

None if used for intended purpose.

10.5. Incompatible materials

See section reactivity

10.6. Hazardous decomposition products

carbon oxides.

SECTION 11: Toxicological information**11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Oral toxicity:

May cause irritation to the digestive tract.

Inhalative toxicity:

May cause irritation to respiratory system.

Skin irritation:

Causes skin irritation.

Eye irritation:

Causes serious eye irritation.

Sensitizing:

May cause an allergic skin reaction.

Acute oral toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

Acute inhalative toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

Acute dermal toxicity:

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

Skin corrosion/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Reaction product: bisphenol-A- (epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	slightly irritating	4 h	rabbit	OECD Guideline 404 (Acute Dermal Irritation / Corrosion)

Serious eye damage/irritation:

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	not irritating		rabbit	OECD Guideline 405 (Acute Eye Irritation / Corrosion)

Respiratory or skin sensitization:

Hazardous components CAS-No.	Result	Test type	Species	Method
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	sensitising	Mouse local lymphnode assay (LLNA)	mouse	OECD Guideline 429 (Skin Sensitisation: Local Lymph Node Assay)

Germ cell mutagenicity:

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	negative	bacterial reverse mutation assay (e.g Ames test)			OECD Guideline 472 (Genetic Toxicology: Escherichia coli, Reverse Mutation Assay)

SECTION 12: Ecological information**General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

12.1. Toxicity**Ecotoxicity:**

Do not empty into drains / surface water / ground water.
Toxic to aquatic life with long lasting effects.

Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Reaction product: bisphenol-A-(epichlorhydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	LC50	1,750000 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
RP Bisphenol F-epichlorhydrin resin, MW<=700 28064-14-4	EC50	3,5 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

12.2. Persistence and degradability**Persistence and Biodegradability:**

No data available for the product.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
------------------------------	--------	----------------------	---------------	--------

RP Bisphenol F- epichlorohydrin resin, MW<=700 28064-14-4		aerobic	10 - 16 %	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)
--	--	---------	-----------	---

12.3. Bioaccumulative potential / 12.4. Mobility in soil**Mobility:**

Cured adhesives are immobile.

Bioaccumulative potential:

No data available for the product.

12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB
Reaction product: bisphenol-A-(epichlorohydrin); epoxy resin (number average molecular weight <= 700) 25068-38-6	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

12.6. Other adverse effects

No data available.

SECTION 13: Disposal considerations**13.1. Waste treatment methods****Product disposal:**

Dispose of in accordance with local and national regulations.

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

SECTION 14: Transport information**14.1. UN number**

ADR	3082
RID	3082
ADNR	3082
IMDG	3082
IATA	3082

14.2. UN proper shipping name

ADR	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-F Epichlorhydrin resin,Bisphenol-A Epichlorhydrin resin)
RID	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-F Epichlorhydrin resin,Bisphenol-A Epichlorhydrin resin)
ADNR	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-F Epichlorhydrin resin,Bisphenol-A Epichlorhydrin resin)
IMDG	ENVIRONMENTALLY HAZARDOUS SUBSTANCE, LIQUID, N.O.S. (Bisphenol-F Epichlorhydrin resin,Bisphenol-A Epichlorhydrin resin)
IATA	Environmentally hazardous substance, liquid, n.o.s. (Bisphenol-F Epichlorhydrin resin,Bisphenol-A Epichlorhydrin resin)

14.3. Transport hazard class(es)

ADR	9
RID	9
ADNR	9
IMDG	9
IATA	9

14.4. Packaging group

ADR	III
RID	III
ADNR	III
IMDG	III
IATA	III

14.5. Environmental hazards

ADR	not applicable
RID	not applicable
ADNR	not applicable
IMDG	Marine pollutant
IATA	not applicable

14.6. Special precautions for user

ADR	not applicable Tunnelcode: (E)
RID	not applicable
ADNR	not applicable
IMDG	not applicable
IATA	not applicable

14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

SECTION 15: Regulatory information**15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**

VOC content < 3,00 %

(2004/42/EC)

15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

R36/38 Irritating to eyes and skin.

R43 May cause sensitisation by skin contact.

R51/53 Toxic to aquatic organisms, may cause long-term adverse effects in the aquatic environment.

H315 Causes skin irritation.

H317 May cause an allergic skin reaction.

H319 Causes serious eye irritation.

H411 Toxic to aquatic life with long lasting effects.

Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.