

MINIATURE LAMP (50) Details



Part #	50				
Description	G3 1/2 M SCREW 7.5V.22A.1CP				
Bulb Shape	G-3 1/2	Filament	C-2R	Base Style	Miniature Screw (E10)
Glass Diameter (in)	0.46	MOL[†] (in)	0.94	LCL^{††} (in)	0.72
Glass Diameter (mm)	11.7	MOL (mm)	23.88	LCL (mm)	18.29
Volts	7.5	MSCP[‡]	1	Avg Life Hrs	1000
Watts	1.65	Amps	0.22	RoHS Compliant	

† MOL (Maximum Overall Length):

The overall length of a lamp, from the top of the shell to the bottom of the base.

‡ MSCP (Mean Spherical Candlepower):

Candlepower produced at design volts. Candlepower is increased rapidly with an increase of applied voltage and conversely is reduced rapidly with a reduction of applied voltage.

†† LCL (Light Center Length):

The distance from a reference point, usually the bottom of the lamp base, to the center of the light source.