


# Cree® XLamp® XP Family LEDs



## TABLE OF CONTENTS

|  |    |   |    |
|--|----|---|----|
| Introduction.....  | 2  | XP-E2 Warm White .....                      | 31 |
| Bin and Order Code Format.....   | 2  | XP-E2 Color .....                           | 32 |
| Performance Groups – Brightness .....  | 3  | XP-E2 Warm White .....                      | 32 |
| Performance Groups – Radiant Flux.....   | 4  | XP-E HEW ANSI Cool White.....               | 35 |
| Performance Groups – Chromaticity .....  | 5  | XP-E HEW Neutral White, Outdoor White ..... | 36 |
| Performance Groups – Dominant Wavelength .....   | 10 | XP-G ANSI Cool White.....                   | 38 |
| Performance Groups – Forward Voltage .....   | 10 | XP-G Neutral White, Outdoor White.....      | 39 |
| Cree’s Standard Chromaticity Regions Plotted on the 1931 CIE Curve.....                        | 11 | XP-G Warm White.....                        | 41 |
| Cree’s Standard Cool White Kits Plotted on ANSI Standard Chromaticity Regions.....             | 13 | XP-G2 ANSI Cool White .....                 | 43 |
| Cree’s Outdoor White Kits Plotted on ANSI Standard Chromaticity Regions.....                   | 14 | XP-G2 Neutral White, Outdoor White.....     | 44 |
| Cree’s Standard Warm and Neutral White Kits Plotted on ANSI Standard Chromaticity Regions..... | 16 | XP-G2 Warm White.....                       | 46 |
| Cree’s 2200 K CCT White Kits Plotted on ANSI Standard Chromaticity Regions.....                | 18 |   |    |
| Cree’s Standard Chromaticity Kits.....   | 19 |   |    |
| Standard Order Codes and Pre-ANSI Bins   |    |   |    |
| XP-C Cool White .....  | 20 |   |    |
| Standard Order Codes and Bins  |    |   |    |
| XP-C ANSI Cool White .....   | 20 |   |    |
| XP-C Neutral White.....  | 21 |   |    |
| XP-C Warm White.....   | 22 |   |    |
| XP-C Color.....  | 22 |   |    |
| XP-E Cool White .....  | 24 |   |    |
| XP-E ANSI Cool White .....   | 24 |   |    |
| XP-E Neutral White, Outdoor White .....  | 25 |   |    |
| XP-E Warm White .....  | 26 |   |    |
| XP-E Color.....  | 27 |   |    |
| XP-E2 ANSI Cool White .....  | 29 |   |    |
| XP-E2 Neutral White, Outdoor White .....   | 29 |   |    |

**INTRODUCTION**


This document describes the product nomenclature required to select and order Cree’s XLamp XP Family LEDs. XLamp XP Family LEDs are tested and sorted into bins which are then combined into orderable kits identified by an order code.

All XLamp LEDs are tested and sorted by color and brightness into a unique bin. Each bin contains LEDs from only one color and brightness group and is uniquely identified by a bin code. White XLamp LEDs are sorted by chromaticity (color) and luminous flux (brightness). High-Efficiency White (HEW) XLamp LEDs are additionally binned into forward voltage bins. Color XLamp LEDs are sorted by dominant wavelength (color) and luminous or radiant flux (brightness). Amber, red-orange and red LEDs are additionally binned into forward voltage bins. LEDs are shipped on reels containing LEDs from one bin and are always labeled with the appropriate bin code.

Kits contain LEDs from a number of similar bins and are fully defined by their order codes. A full explanation of the order codes for XLamp XP Family LEDs, as well as a list of standard order codes, is provided in this document.

**BIN AND ORDER CODE FORMAT**

Bin codes and order codes are configured in the following manner:



**PERFORMANCE GROUPS – BRIGHTNESS**

XLamp XP Family LEDs (except royal blue) are tested for luminous flux and placed into one of the following luminous-flux groups:

| Group Code | Min. Luminous Flux @ 350 mA (lm) | Max. Luminous Flux @ 350 mA (lm) |
|------------|----------------------------------|----------------------------------|
| J          | 23.5                             | 30.6                             |
| K2         | 30.6                             | 35.2                             |
| K3         | 35.2                             | 39.8                             |
| M2         | 39.8                             | 45.7                             |
| M3         | 45.7                             | 51.7                             |
| N2         | 51.7                             | 56.8                             |
| N3         | 56.8                             | 62.0                             |
| N4         | 62.0                             | 67.2                             |
| P2         | 67.2                             | 73.9                             |
| P3         | 73.9                             | 80.6                             |
| P4         | 80.6                             | 87.4                             |
| Q2         | 87.4                             | 93.9                             |
| Q3         | 93.9                             | 100                              |
| Q4         | 100                              | 107                              |
| Q5         | 107                              | 114                              |
| R2         | 114                              | 122                              |
| R3         | 122                              | 130                              |
| R4         | 130                              | 139                              |
| R5         | 139                              | 148                              |
| S2         | 148                              | 156                              |
| S3         | 156                              | 164                              |

**PERFORMANCE GROUPS – RADIANT FLUX ( $T_j = 25\text{ }^\circ\text{C}$ )**

XLamp XP-C and XP-E royal-blue LEDs are tested for radiant flux and sorted into one of the following radiant-flux bins:

| Group | Minimum Radiant Flux (mW) @ 350 mA | Maximum Radiant Flux (mW) @ 350 mA |
|-------|------------------------------------|------------------------------------|
| 12    | 250                                | 300                                |
| 13    | 300                                | 350                                |
| 14    | 350                                | 425                                |
| 15    | 425                                | 500                                |
| 16    | 500                                | 600                                |

XLamp XP-E2 royal blue LEDs are tested for radiant flux and placed into one the following bins:

| Group  | Minimum Radiant Flux (mW) @ 350 mA | Maximum Radiant Flux (mW) @ 350 mA |
|--------|------------------------------------|------------------------------------|
| 31 (K) | 475                                | 500                                |
| 32 (L) | 500                                | 525                                |
| 33 (M) | 525                                | 550                                |
| 34 (N) | 550                                | 575                                |
| 35 (P) | 575                                | 600                                |
| 36 (Q) | 600                                | 625                                |
| 37 (R) | 625                                | 650                                |
| 38 (S) | 650                                | 675                                |
| 39 (T) | 675                                | 700                                |

**PERFORMANCE GROUPS – CHROMATICITY**

White XLamp LEDs are tested for chromaticity and placed into one of the regions defined by the bounding coordinates on the following pages.

| Region | x    | y    | Region | x    | y    |
|--------|------|------|--------|------|------|
| WK     | .283 | .284 | WF     | .314 | .355 |
|        | .295 | .297 |        | .316 | .332 |
|        | .298 | .288 |        | .306 | .322 |
|        | .287 | .276 |        | .301 | .342 |
| WA     | .292 | .306 | WP     | .317 | .319 |
|        | .295 | .297 |        | .329 | .330 |
|        | .283 | .284 |        | .329 | .318 |
|        | .279 | .291 |        | .318 | .308 |
| WM     | .295 | .297 | WD     | .329 | .345 |
|        | .308 | .311 |        | .329 | .330 |
|        | .310 | .300 |        | .317 | .319 |
|        | .298 | .288 |        | .316 | .332 |
| WB     | .306 | .322 | WG     | .329 | .369 |
|        | .308 | .311 |        | .329 | .345 |
|        | .295 | .297 |        | .316 | .332 |
|        | .292 | .306 |        | .314 | .355 |
| WE     | .301 | .342 | WJ     | .329 | .330 |
|        | .306 | .322 |        | .329 | .345 |
|        | .292 | .306 |        | .346 | .359 |
|        | .287 | .321 |        | .344 | .342 |
| WN     | .308 | .311 | WH     | .348 | .384 |
|        | .317 | .319 |        | .346 | .359 |
|        | .318 | .308 |        | .329 | .345 |
|        | .310 | .300 |        | .329 | .369 |
| WC     | .316 | .332 |        |      |      |
|        | .317 | .319 |        |      |      |
|        | .308 | .311 |        |      |      |
|        | .306 | .322 |        |      |      |

**PERFORMANCE GROUPS – CHROMATICITY (CONTINUED)**

| Region | x      | y      | Region | x      | y      | Region | x      | y      | Region | x      | y      |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 0A     | 0.2950 | 0.2970 | 0B     | 0.2920 | 0.3060 | 0C     | 0.2984 | 0.3133 | 0D     | 0.2984 | 0.3133 |
|        | 0.2920 | 0.3060 |        | 0.2895 | 0.3135 |        | 0.2962 | 0.3220 |        | 0.3048 | 0.3207 |
|        | 0.2984 | 0.3133 |        | 0.2962 | 0.3220 |        | 0.3028 | 0.3304 |        | 0.3068 | 0.3113 |
|        | 0.3009 | 0.3042 |        | 0.2984 | 0.3133 |        | 0.3048 | 0.3207 |        | 0.3009 | 0.3042 |
| 0R     | 0.2980 | 0.2880 | 0S     | 0.2895 | 0.3135 | 0T     | 0.2962 | 0.3220 | 0U     | 0.3037 | 0.2937 |
|        | 0.2950 | 0.2970 |        | 0.2870 | 0.3210 |        | 0.2937 | 0.3312 |        | 0.3009 | 0.3042 |
|        | 0.3009 | 0.3042 |        | 0.2937 | 0.3312 |        | 0.3005 | 0.3415 |        | 0.3068 | 0.3113 |
|        | 0.3037 | 0.2937 |        | 0.2962 | 0.3220 |        | 0.3028 | 0.3304 |        | 0.3093 | 0.2993 |
| 1A     | 0.3048 | 0.3207 | 1B     | 0.3028 | 0.3304 | 1C     | 0.3115 | 0.3391 | 1D     | 0.3130 | 0.3290 |
|        | 0.3130 | 0.3290 |        | 0.3115 | 0.3391 |        | 0.3205 | 0.3481 |        | 0.3213 | 0.3373 |
|        | 0.3144 | 0.3186 |        | 0.3130 | 0.3290 |        | 0.3213 | 0.3373 |        | 0.3221 | 0.3261 |
|        | 0.3068 | 0.3113 |        | 0.3048 | 0.3207 |        | 0.3130 | 0.3290 |        | 0.3144 | 0.3186 |
| 1R     | 0.3068 | 0.3113 | 1S     | 0.3005 | 0.3415 | 1T     | 0.3099 | 0.3509 | 1U     | 0.3144 | 0.3186 |
|        | 0.3144 | 0.3186 |        | 0.3099 | 0.3509 |        | 0.3196 | 0.3602 |        | 0.3221 | 0.3261 |
|        | 0.3161 | 0.3059 |        | 0.3115 | 0.3391 |        | 0.3205 | 0.3481 |        | 0.3231 | 0.3120 |
|        | 0.3093 | 0.2993 |        | 0.3028 | 0.3304 |        | 0.3115 | 0.3391 |        | 0.3161 | 0.3059 |
| 2A     | 0.3215 | 0.3350 | 2B     | 0.3207 | 0.3462 | 2C     | 0.3290 | 0.3538 | 2D     | 0.3290 | 0.3417 |
|        | 0.3290 | 0.3417 |        | 0.3290 | 0.3538 |        | 0.3376 | 0.3616 |        | 0.3371 | 0.3490 |
|        | 0.3290 | 0.3300 |        | 0.3290 | 0.3417 |        | 0.3371 | 0.3490 |        | 0.3366 | 0.3369 |
|        | 0.3222 | 0.3243 |        | 0.3215 | 0.3350 |        | 0.3290 | 0.3417 |        | 0.3290 | 0.3300 |
| 2R     | 0.3222 | 0.3243 | 2S     | 0.3196 | 0.3602 | 2T     | 0.3290 | 0.3690 | 2U     | 0.3290 | 0.3300 |
|        | 0.3290 | 0.3300 |        | 0.3290 | 0.3690 |        | 0.3381 | 0.3762 |        | 0.3366 | 0.3369 |
|        | 0.3290 | 0.3180 |        | 0.3290 | 0.3538 |        | 0.3376 | 0.3616 |        | 0.3361 | 0.3245 |
|        | 0.3231 | 0.3120 |        | 0.3207 | 0.3462 |        | 0.3290 | 0.3538 |        | 0.3290 | 0.3180 |
| 3A     | 0.3371 | 0.3490 | 3B     | 0.3376 | 0.3616 | 3C     | 0.3463 | 0.3687 | 3D     | 0.3451 | 0.3554 |
|        | 0.3451 | 0.3554 |        | 0.3463 | 0.3687 |        | 0.3551 | 0.3760 |        | 0.3533 | 0.3620 |
|        | 0.3440 | 0.3427 |        | 0.3451 | 0.3554 |        | 0.3533 | 0.3620 |        | 0.3515 | 0.3487 |
|        | 0.3366 | 0.3369 |        | 0.3371 | 0.3490 |        | 0.3451 | 0.3554 |        | 0.3440 | 0.3427 |
| 3R     | 0.3366 | 0.3369 | 3S     | 0.3381 | 0.3762 | 3T     | 0.3480 | 0.3840 | 3U     | 0.3440 | 0.3428 |
|        | 0.3440 | 0.3428 |        | 0.3480 | 0.3840 |        | 0.3571 | 0.3907 |        | 0.3515 | 0.3487 |
|        | 0.3429 | 0.3307 |        | 0.3463 | 0.3687 |        | 0.3551 | 0.3760 |        | 0.3495 | 0.3339 |
|        | 0.3361 | 0.3245 |        | 0.3376 | 0.3616 |        | 0.3463 | 0.3687 |        | 0.3429 | 0.3307 |
| 4A     | 0.3530 | 0.3597 | 4B     | 0.3548 | 0.3736 | 4C     | 0.3641 | 0.3804 | 4D     | 0.3615 | 0.3659 |
|        | 0.3615 | 0.3659 |        | 0.3641 | 0.3804 |        | 0.3736 | 0.3874 |        | 0.3702 | 0.3722 |
|        | 0.3590 | 0.3521 |        | 0.3615 | 0.3659 |        | 0.3702 | 0.3722 |        | 0.3670 | 0.3578 |
|        | 0.3512 | 0.3465 |        | 0.3530 | 0.3597 |        | 0.3615 | 0.3659 |        | 0.3590 | 0.3521 |
| 4R     | 0.3512 | 0.3465 | 4S     | 0.3571 | 0.3907 | 4T     | 0.3668 | 0.3957 | 4U     | 0.3590 | 0.3521 |
|        | 0.3590 | 0.3521 |        | 0.3668 | 0.3957 |        | 0.3771 | 0.4034 |        | 0.3670 | 0.3578 |
|        | 0.3567 | 0.3389 |        | 0.3641 | 0.3804 |        | 0.3736 | 0.3874 |        | 0.3640 | 0.3440 |
|        | 0.3495 | 0.3339 |        | 0.3548 | 0.3736 |        | 0.3641 | 0.3804 |        | 0.3567 | 0.3389 |

PERFORMANCE GROUPS – CHROMATICITY (CONTINUED)

| Region | x      | y      | Region | x      | y      | Region | x      | y      | Region | x      | y      |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 5A1    | 0.3670 | 0.3578 | 5A2    | 0.3686 | 0.3649 | 5A3    | 0.3744 | 0.3685 | 5A4    | 0.3726 | 0.3612 |
|        | 0.3686 | 0.3649 |        | 0.3702 | 0.3722 |        | 0.3763 | 0.3760 |        | 0.3744 | 0.3685 |
|        | 0.3744 | 0.3685 |        | 0.3763 | 0.3760 |        | 0.3825 | 0.3798 |        | 0.3804 | 0.3721 |
|        | 0.3726 | 0.3612 |        | 0.3744 | 0.3685 |        | 0.3804 | 0.3721 |        | 0.3783 | 0.3646 |
| 5B1    | 0.3702 | 0.3722 | 5B2    | 0.3719 | 0.3797 | 5B3    | 0.3782 | 0.3837 | 5B4    | 0.3763 | 0.3760 |
|        | 0.3719 | 0.3797 |        | 0.3736 | 0.3874 |        | 0.3802 | 0.3916 |        | 0.3782 | 0.3837 |
|        | 0.3782 | 0.3837 |        | 0.3802 | 0.3916 |        | 0.3869 | 0.3958 |        | 0.3847 | 0.3877 |
|        | 0.3763 | 0.3760 |        | 0.3782 | 0.3837 |        | 0.3847 | 0.3877 |        | 0.3825 | 0.3798 |
| 5C1    | 0.3825 | 0.3798 | 5C2    | 0.3847 | 0.3877 | 5C3    | 0.3912 | 0.3917 | 5C4    | 0.3887 | 0.3836 |
|        | 0.3847 | 0.3877 |        | 0.3869 | 0.3958 |        | 0.3937 | 0.4001 |        | 0.3912 | 0.3917 |
|        | 0.3912 | 0.3917 |        | 0.3937 | 0.4001 |        | 0.4006 | 0.4044 |        | 0.3978 | 0.3958 |
|        | 0.3887 | 0.3836 |        | 0.3912 | 0.3917 |        | 0.3978 | 0.3958 |        | 0.3950 | 0.3875 |
| 5D1    | 0.3783 | 0.3646 | 5D2    | 0.3804 | 0.3721 | 5D3    | 0.3863 | 0.3758 | 5D4    | 0.3840 | 0.3681 |
|        | 0.3804 | 0.3721 |        | 0.3825 | 0.3798 |        | 0.3887 | 0.3836 |        | 0.3863 | 0.3758 |
|        | 0.3863 | 0.3758 |        | 0.3887 | 0.3836 |        | 0.3950 | 0.3875 |        | 0.3924 | 0.3794 |
|        | 0.3840 | 0.3681 |        | 0.3863 | 0.3758 |        | 0.3924 | 0.3794 |        | 0.3898 | 0.3716 |
| 5R     | 0.3670 | 0.3578 | 5S     | 0.3771 | 0.4034 | 5T     | 0.3916 | 0.4127 | 5U     | 0.3783 | 0.3646 |
|        | 0.3783 | 0.3646 |        | 0.3916 | 0.4127 |        | 0.4064 | 0.4221 |        | 0.3898 | 0.3716 |
|        | 0.3743 | 0.3502 |        | 0.3869 | 0.3958 |        | 0.4006 | 0.4044 |        | 0.3848 | 0.3565 |
|        | 0.3640 | 0.3440 |        | 0.3736 | 0.3874 |        | 0.3869 | 0.3958 |        | 0.3743 | 0.3502 |
| 6A1    | 0.3889 | 0.3690 | 6A2    | 0.3915 | 0.3768 | 6A3    | 0.3981 | 0.3800 | 6A4    | 0.3953 | 0.3720 |
|        | 0.3915 | 0.3768 |        | 0.3941 | 0.3848 |        | 0.4010 | 0.3882 |        | 0.3981 | 0.3800 |
|        | 0.3981 | 0.3800 |        | 0.4010 | 0.3882 |        | 0.4080 | 0.3916 |        | 0.4048 | 0.3832 |
|        | 0.3953 | 0.3720 |        | 0.3981 | 0.3800 |        | 0.4048 | 0.3832 |        | 0.4017 | 0.3751 |
| 6B1    | 0.3941 | 0.3848 | 6B2    | 0.3968 | 0.3930 | 6B3    | 0.4040 | 0.3966 | 6B4    | 0.4010 | 0.3882 |
|        | 0.3968 | 0.3930 |        | 0.3996 | 0.4015 |        | 0.4071 | 0.4052 |        | 0.4040 | 0.3966 |
|        | 0.4040 | 0.3966 |        | 0.4071 | 0.4052 |        | 0.4146 | 0.4089 |        | 0.4113 | 0.4001 |
|        | 0.4010 | 0.3882 |        | 0.4040 | 0.3966 |        | 0.4113 | 0.4001 |        | 0.4080 | 0.3916 |
| 6C1    | 0.4080 | 0.3916 | 6C2    | 0.4113 | 0.4001 | 6C3    | 0.4186 | 0.4037 | 6C4    | 0.4150 | 0.3950 |
|        | 0.4113 | 0.4001 |        | 0.4146 | 0.4089 |        | 0.4222 | 0.4127 |        | 0.4186 | 0.4037 |
|        | 0.4186 | 0.4037 |        | 0.4222 | 0.4127 |        | 0.4299 | 0.4165 |        | 0.4259 | 0.4073 |
|        | 0.4150 | 0.3950 |        | 0.4186 | 0.4037 |        | 0.4259 | 0.4073 |        | 0.4221 | 0.3984 |
| 6D1    | 0.4017 | 0.3751 | 6D2    | 0.4048 | 0.3832 | 6D3    | 0.4116 | 0.3865 | 6D4    | 0.4082 | 0.3782 |
|        | 0.4048 | 0.3832 |        | 0.4080 | 0.3916 |        | 0.4150 | 0.3950 |        | 0.4116 | 0.3865 |
|        | 0.4116 | 0.3865 |        | 0.4150 | 0.3950 |        | 0.4221 | 0.3984 |        | 0.4183 | 0.3898 |
|        | 0.4082 | 0.3782 |        | 0.4116 | 0.3865 |        | 0.4183 | 0.3898 |        | 0.4147 | 0.3814 |
| 6R     | 0.3889 | 0.3690 | 6S     | 0.4054 | 0.4191 | 6T     | 0.4217 | 0.4273 | 6U     | 0.4017 | 0.3751 |
|        | 0.4017 | 0.3751 |        | 0.4217 | 0.4273 |        | 0.4382 | 0.4356 |        | 0.4147 | 0.3814 |
|        | 0.3957 | 0.3596 |        | 0.4146 | 0.4089 |        | 0.4299 | 0.4165 |        | 0.4077 | 0.3652 |
|        | 0.3840 | 0.3540 |        | 0.3996 | 0.4015 |        | 0.4146 | 0.4089 |        | 0.3957 | 0.3596 |

PERFORMANCE GROUPS – CHROMATICITY (CONTINUED)

| Region | x      | y      | Region | x      | y      | Region | x      | y      | Region | x      | y      |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| 7A1    | 0.4147 | 0.3814 | 7A2    | 0.4183 | 0.3898 | 7A3    | 0.4242 | 0.3919 | 7A4    | 0.4203 | 0.3833 |
|        | 0.4183 | 0.3898 |        | 0.4221 | 0.3984 |        | 0.4281 | 0.4006 |        | 0.4242 | 0.3919 |
|        | 0.4242 | 0.3919 |        | 0.4281 | 0.4006 |        | 0.4342 | 0.4028 |        | 0.4300 | 0.3939 |
|        | 0.4203 | 0.3833 |        | 0.4242 | 0.3919 |        | 0.4300 | 0.3939 |        | 0.4259 | 0.3853 |
| 7B1    | 0.4221 | 0.3984 | 7B2    | 0.4259 | 0.4073 | 7B3    | 0.4322 | 0.4096 | 7B4    | 0.4281 | 0.4006 |
|        | 0.4259 | 0.4073 |        | 0.4299 | 0.4165 |        | 0.4364 | 0.4188 |        | 0.4322 | 0.4096 |
|        | 0.4322 | 0.4096 |        | 0.4364 | 0.4188 |        | 0.4430 | 0.4212 |        | 0.4385 | 0.4119 |
|        | 0.4281 | 0.4006 |        | 0.4322 | 0.4096 |        | 0.4385 | 0.4119 |        | 0.4342 | 0.4028 |
| 7C1    | 0.4342 | 0.4028 | 7C2    | 0.4385 | 0.4119 | 7C3    | 0.4449 | 0.4141 | 7C4    | 0.4403 | 0.4049 |
|        | 0.4385 | 0.4119 |        | 0.4430 | 0.4212 |        | 0.4496 | 0.4236 |        | 0.4449 | 0.4141 |
|        | 0.4449 | 0.4141 |        | 0.4496 | 0.4236 |        | 0.4562 | 0.4260 |        | 0.4513 | 0.4164 |
|        | 0.4403 | 0.4049 |        | 0.4449 | 0.4141 |        | 0.4513 | 0.4164 |        | 0.4465 | 0.4071 |
| 7D1    | 0.4259 | 0.3853 | 7D2    | 0.4300 | 0.3939 | 7D3    | 0.4359 | 0.3960 | 7D4    | 0.4316 | 0.3873 |
|        | 0.4300 | 0.3939 |        | 0.4342 | 0.4028 |        | 0.4403 | 0.4049 |        | 0.4359 | 0.3960 |
|        | 0.4359 | 0.3960 |        | 0.4403 | 0.4049 |        | 0.4465 | 0.4071 |        | 0.4418 | 0.3981 |
|        | 0.4316 | 0.3873 |        | 0.4359 | 0.3960 |        | 0.4418 | 0.3981 |        | 0.4373 | 0.3893 |
| 8A1    | 0.4373 | 0.3893 | 8A2    | 0.4418 | 0.3981 | 8A3    | 0.4475 | 0.3994 | 8A4    | 0.4428 | 0.3906 |
|        | 0.4418 | 0.3981 |        | 0.4465 | 0.4071 |        | 0.4523 | 0.4085 |        | 0.4475 | 0.3994 |
|        | 0.4475 | 0.3994 |        | 0.4523 | 0.4085 |        | 0.4582 | 0.4099 |        | 0.4532 | 0.4008 |
|        | 0.4428 | 0.3906 |        | 0.4475 | 0.3994 |        | 0.4532 | 0.4008 |        | 0.4483 | 0.3919 |
| 8B1    | 0.4465 | 0.4071 | 8B2    | 0.4513 | 0.4164 | 8B3    | 0.4573 | 0.4178 | 8B4    | 0.4523 | 0.4085 |
|        | 0.4513 | 0.4164 |        | 0.4562 | 0.4260 |        | 0.4624 | 0.4274 |        | 0.4573 | 0.4178 |
|        | 0.4573 | 0.4178 |        | 0.4624 | 0.4274 |        | 0.4687 | 0.4289 |        | 0.4634 | 0.4193 |
|        | 0.4523 | 0.4085 |        | 0.4573 | 0.4178 |        | 0.4634 | 0.4193 |        | 0.4582 | 0.4099 |
| 8C1    | 0.4582 | 0.4099 | 8C2    | 0.4634 | 0.4193 | 8C3    | 0.4695 | 0.4207 | 8C4    | 0.4641 | 0.4112 |
|        | 0.4634 | 0.4193 |        | 0.4687 | 0.4289 |        | 0.4750 | 0.4304 |        | 0.4695 | 0.4207 |
|        | 0.4695 | 0.4207 |        | 0.4750 | 0.4304 |        | 0.4813 | 0.4319 |        | 0.4756 | 0.4221 |
|        | 0.4641 | 0.4112 |        | 0.4695 | 0.4207 |        | 0.4756 | 0.4221 |        | 0.4700 | 0.4126 |
| 8D1    | 0.4483 | 0.3919 | 8D2    | 0.4532 | 0.4008 | 8D3    | 0.4589 | 0.4021 | 8D4    | 0.4538 | 0.3931 |
|        | 0.4532 | 0.4008 |        | 0.4582 | 0.4099 |        | 0.4641 | 0.4112 |        | 0.4589 | 0.4021 |
|        | 0.4589 | 0.4021 |        | 0.4641 | 0.4112 |        | 0.4700 | 0.4126 |        | 0.4646 | 0.4034 |
|        | 0.4538 | 0.3931 |        | 0.4589 | 0.4021 |        | 0.4646 | 0.4034 |        | 0.4593 | 0.3944 |
| AA1    | 0.4822 | 0.3973 | AA2    | 0.4884 | 0.4067 | AA3    | 0.4942 | 0.4066 | AA4    | 0.4879 | 0.3972 |
|        | 0.4884 | 0.4067 |        | 0.4946 | 0.4162 |        | 0.5006 | 0.4160 |        | 0.4942 | 0.4066 |
|        | 0.4942 | 0.4066 |        | 0.5006 | 0.4160 |        | 0.5066 | 0.4158 |        | 0.5001 | 0.4064 |
|        | 0.4879 | 0.3972 |        | 0.4942 | 0.4066 |        | 0.5001 | 0.4064 |        | 0.4936 | 0.3970 |
| AB1    | 0.4946 | 0.4162 | AB2    | 0.5008 | 0.4256 | AB3    | 0.5069 | 0.4254 | AB4    | 0.5006 | 0.4160 |
|        | 0.5008 | 0.4256 |        | 0.5070 | 0.4350 |        | 0.5133 | 0.4348 |        | 0.5069 | 0.4254 |
|        | 0.5069 | 0.4254 |        | 0.5133 | 0.4348 |        | 0.5196 | 0.4346 |        | 0.5131 | 0.4252 |
|        | 0.5006 | 0.4160 |        | 0.5069 | 0.4254 |        | 0.5131 | 0.4252 |        | 0.5066 | 0.4158 |



**PERFORMANCE GROUPS – CHROMATICITY (CONTINUED)**

| Region | x      | y      | Region | x      | y      | Region | x      | y      | Region | x      | y      |
|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|
| AC1    | 0.5066 | 0.4158 | AC2    | 0.5131 | 0.4252 | AC3    | 0.5192 | 0.4250 | AC4    | 0.5126 | 0.4156 |
|        | 0.5131 | 0.4252 |        | 0.5196 | 0.4346 |        | 0.5258 | 0.4343 |        | 0.5192 | 0.4250 |
|        | 0.5192 | 0.4250 |        | 0.5258 | 0.4343 |        | 0.5321 | 0.4341 |        | 0.5253 | 0.4248 |
|        | 0.5126 | 0.4156 |        | 0.5192 | 0.4250 |        | 0.5253 | 0.4248 |        | 0.5186 | 0.4154 |
| AD1    | 0.4936 | 0.3970 | AD2    | 0.5001 | 0.4064 | AD3    | 0.5059 | 0.4062 | AD4    | 0.4993 | 0.3969 |
|        | 0.5001 | 0.4064 |        | 0.5066 | 0.4158 |        | 0.5126 | 0.4156 |        | 0.5059 | 0.4062 |
|        | 0.5059 | 0.4062 |        | 0.5126 | 0.4156 |        | 0.5186 | 0.4154 |        | 0.5118 | 0.4061 |
|        | 0.4993 | 0.3969 |        | 0.5059 | 0.4062 |        | 0.5118 | 0.4061 |        | 0.5050 | 0.3967 |

## PERFORMANCE GROUPS – DOMINANT WAVELENGTH

Color XLamp LEDs are tested for dominant wavelength (DWL) and sorted into one of the DWL bins defined below.

| Color      | DWL Group | Min. DWL (nm)<br>@ 350 mA | Max. DWL (nm)<br>@ 350 mA |
|------------|-----------|---------------------------|---------------------------|
| Royal Blue | D3        | 450                       | 455                       |
|            | D4        | 455                       | 460                       |
|            | D5        | 460                       | 465                       |
| Blue       | B3        | 465                       | 470                       |
|            | B4        | 470                       | 475                       |
|            | B5        | 475                       | 480                       |
|            | B6        | 480                       | 485                       |
| Green      | G2        | 520                       | 525                       |
|            | G3        | 525                       | 530                       |
|            | G4        | 530                       | 535                       |
| Amber      | A2        | 585                       | 590                       |
|            | A3        | 590                       | 595                       |
| Red-Orange | O3        | 610                       | 615                       |
|            | O4        | 615                       | 620                       |
| Red        | R2        | 620                       | 625                       |
|            | R3        | 625                       | 630                       |


## PERFORMANCE GROUPS – FORWARD VOLTAGE

Amber, red-orange, red and High-Efficiency White XLamp LEDs are tested for forward voltage and sorted into one of the forward voltage bins defined below.


| Forward Voltage Group | Min. Forward Voltage<br>@ 350 mA | Max. Forward Voltage<br>@ 350 mA |
|-----------------------|----------------------------------|----------------------------------|
| B                     | 1.75                             | 2.0                              |
| C                     | 2.0                              | 2.25                             |
| D                     | 2.25                             | 2.5                              |
| E                     | 2.5                              | 2.75                             |
| F                     | 2.75                             | 3.0                              |
| G                     | 3.0                              | 3.25                             |
| H                     | 3.25                             | 3.5                              |
| J                     | 3.5                              | 3.75                             |

**CREE'S STANDARD CHROMATICITY REGIONS PLOTTED ON THE 1931 CIE CURVE**

Cool White




ANSI Cool White




**CREE'S STANDARD CHROMATICITY REGIONS PLOTTED ON THE 1931 CIE CURVE (CONTINUED)**


Neutral White









ANSI Neutral White and ANSI Warm White






CREE'S STANDARD COOL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS





CREE'S OUTDOOR WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS



**CREE'S OUTDOOR WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS (CONTINUED)**






**CREE'S STANDARD WARM AND NEUTRAL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS**






**CREE'S STANDARD WARM AND NEUTRAL WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS (CONTINUED)**



**CREE'S 2200 K CCT WHITE KITS PLOTTED ON ANSI STANDARD CHROMATICITY REGIONS**



**CREE'S STANDARD CHROMATICITY KITS**

The following table provides the chromaticity bins associated with chromaticity kits.

| Color         | CCT    | Kit  | Chromaticity Bins  |
|---------------|--------|--|--|
| Cool White    | 6200 K | 51   | 0A, 0B, 0C, 0D, 0R, 0S, 0T, 0U, 1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U, 2A, 2B, 2C, 2D, 2R, 2S, 2T, 2U, 3A, 3B, 3R, 3S   |
|               | 6000 K | 53   | 1A, 1B, 1C, 1D, 1R, 1S, 1T, 1U, 2A, 2B, 2C, 2D, 2R, 2S, 2T, 3A, 3B, 3S   |
|               | 6200 K | 50   | 1A, 1B, 1C, 1D, 2A, 2B, 2C, 2D   |
|               | 6500 K | E1   | 1A, 1B, 1C, 1D   |
|               | 5700 K | E2   | 2A, 2B, 2C, 2D   |
| Neutral White | 5000 K | E3   | 3A, 3B, 3C, 3D   |
|               | 5000 K | C1   | 3A, 3B, 3C, 3D, 3R, 3S, 3T, 3U, 4A, 4B, 4R, 4S   |
|               | 4750 K | F4   | 3C, 3D, 4A, 4B   |
|               | 4750 K | D1   | 3A, 3B, 3C, 3D, 3R, 3S, 3T, 3U, 4A, 4B, 4C, 4D, 4R, 4S, 4T, 4U   |
|               | 4500 K | E4   | 4A, 4B, 4C, 4D   |
|               | 4500 K | D2   | 3C, 3D, 3T, 3U, 4A, 4B, 4C, 4D, 4R, 4S, 4T, 4U, 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5R, 5S   |
|               | 4500 K | C2   | 3C, 3D, 3T, 3U, 4A, 4B, 4C, 4D, 4R, 4S, 4T, 4U   |
|               | 4300 K | C3   | 4A, 4B, 4C, 4D, 4R, 4S, 4T, 4U, 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5R, 5S   |
|               | 4300 K | D3   | 4A, 4B, 4C, 4D, 4R, 4S, 4T, 4U, 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 5R, 5S, 5T, 5U   |
|               | 4250 K | F5   | 4C, 4D, 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4   |
|               | 4100 K | C4   | 4C, 4D, 4T, 4U, 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 5R, 5S, 5T, 5U   |
|               | 4000 K | D4   | 4C, 4D, 4T, 4U, 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 5R, 5S, 5T, 5U, 6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4, 6R, 6S                                 |
|               | 4000 K | E5   | 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4   |
|               | 4000 K | Z5   | 5A3, 5B4, 5C1, 5D2   |
|               | 3800 K | C5   | 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 5R, 5S, 5T, 5U, 6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4, 6R, 6S   |
| Warm White    | 3750 K | F6   | 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4   |
|               | 3700 K | D5   | 5A1, 5A2, 5A3, 5A4, 5B1, 5B2, 5B3, 5B4, 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 5R, 5S, 5T, 5U, 6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4, 6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4, 6R, 6S, 6T, 6U |
|               | 3600 K | C6   | 5C1, 5C2, 5C3, 5C4, 5D1, 5D2, 5D3, 5D4, 5T, 5U, 6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4, 6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4, 6R, 6S, 6T, 6U   |
|               | 3500 K | E6   | 6A1, 6A2, 6A3, 6A4, 6B1, 6B2, 6B3, 6B4, 6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4   |
|               | 3500 K | Z6   | 6A3, 6B4, 6C1, 6D2   |
|               | 3250 K | F7   | 6C1, 6C2, 6C3, 6C4, 6D1, 6D2, 6D3, 6D4, 7A1, 7A2, 7A3, 7A4, 7B1, 7B2, 7B3, 7B4   |
|               | 3000 K | E7   | 7A1, 7A2, 7A3, 7A4, 7B1, 7B2, 7B3, 7B4, 7C1, 7C2, 7C3, 7C4, 7D1, 7D2, 7D3, 7D4   |
|               | 3000 K | Z7   | 7A3, 7B4, 7C1, 7D2   |
|               | 2850 K | F8   | 7C1, 7C2, 7C3, 7C4, 7D1, 7D2, 7D3, 7D4, 8A1, 8A2, 8A3, 8A4, 8B1, 8B2, 8B3, 8B4   |
|               | 2700 K | E8   | 8A1, 8A2, 8A3, 8A4, 8B1, 8B2, 8B3, 8B4, 8C1, 8C2, 8C3, 8C4, 8D1, 8D2, 8D3, 8D4   |
|               | 2700 K | Z8   | 8A3, 8B4, 8C1, 8D2   |
| 2200 K        | EA     | AA1, AA2, AA3, AA4, AB1, AB2, AB3, AB4, AC1, AC2, AC3, AC4, AD1, AD2, AD3, AD4 |  |

The following tables of order codes list flux minimums and chromaticity regions for the various categories of XLamp XP LEDs. For other flux and chromaticity combinations, contact Cree or an authorized distributor.

**STANDARD ORDER CODES AND PRE-ANSI BINS (XP-C COOL WHITE, T<sub>j</sub> = 25 °C)**

| XLamp XP-C LED Standard Order Codes - White |           |  |  |                      |
|---|-----------|--|--|----------------------|
| Min. Luminous Flux (lm)<br>@ 350 mA*        |           | Chromaticity Regions                               |  | Order Codes          |
| Group                                       | Flux (lm) |  |  |                      |
| Cool White (5000 K - 10,000 K)              |           |  |  |                      |
| Q2  | 87.4      | WA, WB, WC, WD, WE, WF, WG, WH, WJ, WK, WM, WN, WP |  | XPCWHT-L1-0000-00A01 |
|   |           | WC, WD, WF, WG                                     |  | XPCWHT-L1-0000-00A02 |
|   |           | WC, WD, WF, WG, WH, WJ, WN, WP                     |  | XPCWHT-L1-0000-00A03 |
| Q3  | 93.9      | WA, WB, WC, WD, WE, WF, WG, WH, WJ, WK, WM, WN, WP |  | XPCWHT-L1-0000-00B01 |
|   |           | WC, WD, WF, WG                                     |  | XPCWHT-L1-0000-00B02 |
|   |           | WC, WD, WF, WG, WH, WJ, WN, WP                     |  | XPCWHT-L1-0000-00B03 |
| Q4  | 100       | WA, WB, WC, WD, WE, WF, WG, WH, WJ, WK, WM, WN, WP |  | XPCWHT-L1-0000-00C01 |
|   |           | WC, WD, WF, WG                                     |  | XPCWHT-L1-0000-00C02 |
|   |           | WC, WD, WF, WG, WH, WJ, WN, WP                     |  | XPCWHT-L1-0000-00C03 |
| Q5  | 107       | WA, WB, WC, WD, WE, WF, WG, WH, WJ, WK, WM, WN, WP |  | XPCWHT-L1-0000-00D01 |
|   |           | WC, WD, WF, WG                                     |  | XPCWHT-L1-0000-00D02 |
|   |           | WC, WD, WF, WG, WH, WJ, WN, WP                     |  | XPCWHT-L1-0000-00D03 |

**STANDARD ORDER CODES AND BINS (XP-C ANSI COOL WHITE, T<sub>j</sub> = 25 °C)**

| XLamp XP-C Standard Order Codes - White |        |                                      |           |                      |
|---|--------|--------------------------------------|-----------|----------------------|
| Chromaticity                            |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |
| Kit                                     | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       |
| ANSI Cool White (5000 K - 8300 K)       |        |                                      |           |                      |
| 51                                      | 6200 K | Q5                                   | 107       | XPCWHT-L1-0000-00D51 |
|   |        | Q4                                   | 100       | XPCWHT-L1-0000-00C51 |
|   |        | Q3                                   | 93.9      | XPCWHT-L1-0000-00B51 |
|   |        | Q2                                   | 87.4      | XPCWHT-L1-0000-00A51 |
| 53                                      | 6000 K | Q5                                   | 107       | XPCWHT-L1-0000-00D53 |
|   |        | Q4                                   | 100       | XPCWHT-L1-0000-00C53 |
|   |        | Q3                                   | 93.9      | XPCWHT-L1-0000-00B53 |
|   |        | Q2                                   | 87.4      | XPCWHT-L1-0000-00A53 |
| 50                                      | 6200 K | Q5                                   | 107       | XPCWHT-L1-0000-00D50 |
|   |        | Q4                                   | 100       | XPCWHT-L1-0000-00C50 |
|   |        | Q3                                   | 93.9      | XPCWHT-L1-0000-00B50 |
|   |        | Q2                                   | 87.4      | XPCWHT-L1-0000-00A50 |
| E1                                      | 6500 K | Q5                                   | 107       | XPCWHT-L1-0000-00DE1 |
|   |        | Q4                                   | 100       | XPCWHT-L1-0000-00CE1 |
|   |        | Q3                                   | 93.9      | XPCWHT-L1-0000-00BE1 |
|   |        | Q2                                   | 87.4      | XPCWHT-L1-0000-00AE1 |
| E2                                      | 5700 K | Q5                                   | 107       | XPCWHT-L1-0000-00DE2 |
|   |        | Q4                                   | 100       | XPCWHT-L1-0000-00CE2 |
|   |        | Q3                                   | 93.9      | XPCWHT-L1-0000-00BE2 |
|   |        | Q2                                   | 87.4      | XPCWHT-L1-0000-00AE2 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-C NEUTRAL WHITE, T<sub>j</sub> = 25 °C)**

| XLamp XP-C Standard Kit Codes - White |        |                                      |           |                      |
|---------------------------------------|--------|--------------------------------------|-----------|----------------------|
| Chromaticity                          |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |
| Kit                                   | CCT    | Code                                 | Flux (lm) | 75 CRI Typical       |
| ANSI Neutral White (3700 K – 5000 K)  |        |                                      |           |                      |
| E3                                    | 5000 K | Q2                                   | 87.4      | XPCWHT-L1-0000-00AE3 |
|                                       |        | P4                                   | 80.6      | XPCWHT-L1-0000-009E3 |
|                                       |        | P3                                   | 73.9      | XPCWHT-L1-0000-008E3 |
| F4                                    | 4750 K | Q2                                   | 87.4      | XPCWHT-L1-0000-00AF4 |
|                                       |        | P4                                   | 80.6      | XPCWHT-L1-0000-009F4 |
|                                       |        | P3                                   | 73.9      | XPCWHT-L1-0000-008F4 |
| E4                                    | 4500 K | Q2                                   | 87.4      | XPCWHT-L1-0000-00AE4 |
|                                       |        | P4                                   | 80.6      | XPCWHT-L1-0000-009E4 |
|                                       |        | P3                                   | 73.9      | XPCWHT-L1-0000-008E4 |
| F5                                    | 4250 K | Q2                                   | 87.4      | XPCWHT-L1-0000-00AF5 |
|                                       |        | P4                                   | 80.6      | XPCWHT-L1-0000-009F5 |
|                                       |        | P3                                   | 73.9      | XPCWHT-L1-0000-008F5 |
|                                       |        | P2                                   | 67.2      | XPCWHT-L1-0000-007F5 |
| E5                                    | 4000 K | Q2                                   | 87.4      | XPCWHT-L1-0000-00AE5 |
|                                       |        | P4                                   | 80.6      | XPCWHT-L1-0000-009E5 |
|                                       |        | P3                                   | 73.9      | XPCWHT-L1-0000-008E5 |
|                                       |        | P2                                   | 67.2      | XPCWHT-L1-0000-007E5 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-C WARM WHITE,  $T_j = 25\text{ }^\circ\text{C}$ )**

| XLampXP-C Standard Kit Codes - White |        |                                      |           |                      |
|--------------------------------------|--------|--------------------------------------|-----------|----------------------|
| Chromaticity                         |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |
| Kit                                  | CCT    | Code                                 | Flux (lm) | 80 CRI Typical       |
| ANSI Warm White (2700 K - 3750 K)    |        |                                      |           |                      |
| F6                                   | 3750 K | P4                                   | 80.6      | XPCWHT-L1-0000-009F6 |
|                                      |        | P3                                   | 73.9      | XPCWHT-L1-0000-008F6 |
|                                      |        | P2                                   | 67.2      | XPCWHT-L1-0000-007F6 |
| E6                                   | 3500 K | P4                                   | 80.6      | XPCWHT-L1-0000-009E6 |
|                                      |        | P3                                   | 73.9      | XPCWHT-L1-0000-008E6 |
|                                      |        | P2                                   | 67.2      | XPCWHT-L1-0000-007E6 |
| F7                                   | 3250 K | P3                                   | 73.9      | XPCWHT-L1-0000-008F7 |
|                                      |        | P2                                   | 67.2      | XPCWHT-L1-0000-007F7 |
|                                      |        | N4                                   | 62        | XPCWHT-L1-0000-006F7 |
| E7                                   | 3000 K | P3                                   | 73.9      | XPCWHT-L1-0000-008E7 |
|                                      |        | P2                                   | 67.2      | XPCWHT-L1-0000-007E7 |
|                                      |        | N4                                   | 62        | XPCWHT-L1-0000-006E7 |
| F8                                   | 2850 K | P2                                   | 67.2      | XPCWHT-L1-0000-007F8 |
|                                      |        | N4                                   | 62        | XPCWHT-L1-0000-006F8 |
|                                      |        | N3                                   | 56.8      | XPCWHT-L1-0000-005F8 |
| E8                                   | 2700 K | P2                                   | 67.2      | XPCWHT-L1-0000-007E8 |
|                                      |        | N4                                   | 62        | XPCWHT-L1-0000-006E8 |
|                                      |        | N3                                   | 56.8      | XPCWHT-L1-0000-005E8 |

**STANDARD ORDER CODES AND BINS (XP-C COLOR,  $T_j = 25\text{ }^\circ\text{C}$ )**

| XLamp XP-C LED Standard Order Codes - Royal Blue |                                  |           |  |                          |       |          |     |                      |
|--|----------------------------------|-----------|--|--------------------------|-------|----------|-----|----------------------|
| Color  | Min. Radiant Flux (mW) @ 350 mA* |           | Calculated Min. Radiant Flux (mW) @ 125 mA** | Dominant Wavelength (nm) |       |          |     | Order Codes          |
|  | Group                            | Flux (mW) |  | Min.                     |       | Max.     |     |                      |
|  |                                  |           | Group  | DWL (nm)                 | Group | DWL (nm) |     |                      |
| Royal Blue                                       | 12                               | 250       | 104  | D3                       | 450   | D5       | 465 | XPCROY-L1-0000-00701 |
|  |                                  |           |  | D3                       | 450   | D4       | 460 | XPCROY-L1-0000-00702 |
|  |                                  |           |  | D4                       | 455   | D5       | 465 | XPCROY-L1-0000-00703 |
|  | 13                               | 300       | 124  | D3                       | 450   | D5       | 465 | XPCROY-L1-0000-00801 |
|  |                                  |           |  | D3                       | 450   | D4       | 460 | XPCROY-L1-0000-00802 |
|  |                                  |           |  | D4                       | 455   | D5       | 465 | XPCROY-L1-0000-00803 |
|  | 14                               | 350       | 145  | D3                       | 450   | D5       | 465 | XPCROY-L1-0000-00901 |
|  |                                  |           |  | D3                       | 450   | D4       | 460 | XPCROY-L1-0000-00902 |

\*\* Calculated values for reference only

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-C COLOR, T<sub>j</sub> = 25 °C, CONTINUED)**

| XLamp XP-C LED Standard Order Codes - Color |                                      |           |   |                          |       |          |     |                      |
|---|--------------------------------------|-----------|---|--------------------------|-------|----------|-----|----------------------|
| Color                                       | Min. Luminous Flux (lm)<br>@ 350 mA* |           | Calculated Min.<br>Luminous Flux (lm)<br>@ 125 mA** | Dominant Wavelength (nm) |       |          |     | Order Codes          |
|   | Group                                | Flux (lm) |   | Min.                     |       | Max.     |     |                      |
|   |                                      |           | Group   | DWL (nm)                 | Group | DWL (nm) |     |                      |
| Blue  | J                                    | 23.5      | 10.8  | B3                       | 465   | B6       | 485 | XPCBLU-L1-0000-00W01 |
|   |                                      |           |   | B3                       | 465   | B5       | 480 | XPCBLU-L1-0000-00W02 |
|   |                                      |           |   | B4                       | 470   | B5       | 480 | XPCBLU-L1-0000-00W05 |
|   | K2                                   | 30.6      | 13.8  | B3                       | 465   | B6       | 485 | XPCBLU-L1-0000-00Y01 |
|   |                                      |           |   | B3                       | 465   | B5       | 480 | XPCBLU-L1-0000-00Y02 |
|   |                                      |           |   | B4                       | 470   | B5       | 480 | XPCBLU-L1-0000-00Y05 |
| Green                                       | N3                                   | 56.8      | 28.2  | G2                       | 520   | G4       | 535 | XPCGRN-L1-0000-00501 |
|   |                                      |           |   | G2                       | 520   | G3       | 530 | XPCGRN-L1-0000-00502 |
|   |                                      |           |   | G3                       | 525   | G4       | 535 | XPCGRN-L1-0000-00503 |
|   | N4                                   | 62.0      | 30.8  | G2                       | 520   | G4       | 535 | XPCGRN-L1-0000-00601 |
|   |                                      |           |   | G2                       | 520   | G3       | 530 | XPCGRN-L1-0000-00602 |
|   |                                      |           |   | G3                       | 525   | G4       | 535 | XPCGRN-L1-0000-00603 |
|   | P2                                   | 67.2      | 33.3  | G2                       | 520   | G4       | 535 | XPCGRN-L1-0000-00701 |
|   |                                      |           |   | G2                       | 520   | G3       | 530 | XPCGRN-L1-0000-00702 |
|   |                                      |           |   | G3                       | 525   | G4       | 535 | XPCGRN-L1-0000-00703 |
|   | P3                                   | 73.9      | 36.7  | G2                       | 520   | G4       | 535 | XPCGRN-L1-0000-00801 |
|   |                                      |           |   | G2                       | 520   | G3       | 530 | XPCGRN-L1-0000-00802 |
|   |                                      |           |   | G3                       | 525   | G4       | 535 | XPCGRN-L1-0000-00803 |
| Amber                                       | M2                                   | 39.8      | 14.9  | A2                       | 585   | A3       | 595 | XPCAMB-L1-0000-00201 |
|   | M3                                   | 45.7      | 17.1  | A2                       | 585   | A3       | 595 | XPCAMB-L1-0000-00301 |
|   | N2                                   | 51.7      | 19.4  | A2                       | 585   | A3       | 595 | XPCAMB-L1-0000-00401 |
|   | N3                                   | 56.8      | 21.3  | A2                       | 585   | A3       | 595 | XPCAMB-L1-0000-00501 |
| Red-Orange                                  | N2                                   | 51.7      | 19.8  | O3                       | 610   | O4       | 620 | XPCRDO-L1-0000-00401 |
|   | N3                                   | 56.8      | 21.7  | O3                       | 610   | O4       | 620 | XPCRDO-L1-0000-00501 |
|   | N4                                   | 62.0      | 23.7  | O3                       | 610   | O4       | 620 | XPCRDO-L1-0000-00601 |
|   | P2                                   | 67.2      | 25.7  | O3                       | 610   | O4       | 620 | XPCRDO-L1-0000-00701 |
| Red   | M2                                   | 39.8      | 15.2  | R2                       | 620   | R3       | 630 | XPCRED-L1-0000-00201 |
|   | M3                                   | 45.7      | 17.5  | R2                       | 620   | R3       | 630 | XPCRED-L1-0000-00301 |
|   | N2                                   | 51.7      | 19.7  | R2                       | 620   | R3       | 630 | XPCRED-L1-0000-00401 |
|   | N3                                   | 56.8      | 21.7  | R2                       | 620   | R3       | 630 | XPCRED-L1-0000-00501 |

\*\* Calculated values for reference only

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E COOL WHITE,  $T_j = 25\text{ }^\circ\text{C}$ )**

| XLamp XP-E LED Standard Order Codes - White |           |  |  |                      |
|---|-----------|--|--|----------------------|
| Minimum Luminous Flux (lm) @ 350 mA*        |           | Chromaticity Regions                               |  | Order Codes          |
| Group                                       | Flux (lm) |  |  | 70 CRI Typical       |
| Cool White (5000 K - 10,000 K)              |           |  |  |                      |
| Q4  | 100       | WA, WB, WC, WD, WE, WF, WG, WH, WJ, WK, WM, WN, WP |  | XPEWHT-L1-0000-00C01 |
|   |           | WC, WD, WF, WG                                     |  | XPEWHT-L1-0000-00C02 |
|   |           | WC, WD, WF, WG, WH, WJ, WN, WP                     |  | XPEWHT-L1-0000-00C03 |
| Q5  | 107       | WA, WB, WC, WD, WE, WF, WG, WH, WJ, WK, WM, WN, WP |  | XPEWHT-L1-0000-00D01 |
|   |           | WC, WD, WF, WG                                     |  | XPEWHT-L1-0000-00D02 |
|   |           | WC, WD, WF, WG, WH, WJ, WN, WP                     |  | XPEWHT-L1-0000-00D03 |
| R2  | 114       | WA, WB, WC, WD, WE, WF, WG, WH, WJ, WK, WM, WN, WP |  | XPEWHT-L1-0000-00E01 |
|   |           | WC, WD, WF, WG                                     |  | XPEWHT-L1-0000-00E02 |
|   |           | WC, WD, WF, WG, WH, WJ, WN, WP                     |  | XPEWHT-L1-0000-00E03 |
| R3  | 122       | WA, WB, WC, WD, WE, WF, WG, WH, WJ, WK, WM, WN, WP |  | XPEWHT-L1-0000-00F01 |
|   |           | WC, WD, WF, WG                                     |  | XPEWHT-L1-0000-00F02 |
|   |           | WC, WD, WF, WG, WH, WJ, WN, WP                     |  | XPEWHT-L1-0000-00F03 |

**STANDARD ORDER CODES AND BINS (XP-E ANSI COOL WHITE,  $T_j = 25\text{ }^\circ\text{C}$ )**

| XLamp XP-E Standard Order Codes - White |        |                                      |           |                      |
|---|--------|--------------------------------------|-----------|----------------------|
| Chromaticity                            |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |
| Kit                                     | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       |
| ANSI Cool White (5000 K - 8300 K)       |        |                                      |           |                      |
| 51                                      | 6200 K | R3                                   | 122       | XPEWHT-L1-0000-00F51 |
|   |        | R2                                   | 114       | XPEWHT-L1-0000-00E51 |
|   |        | Q5                                   | 107       | XPEWHT-L1-0000-00D51 |
|   |        | Q4                                   | 100       | XPEWHT-L1-0000-00C51 |
| 53                                      | 6000 K | R3                                   | 122       | XPEWHT-L1-0000-00F53 |
|   |        | R2                                   | 114       | XPEWHT-L1-0000-00E53 |
|   |        | Q5                                   | 107       | XPEWHT-L1-0000-00D53 |
|   |        | Q4                                   | 100       | XPEWHT-L1-0000-00C53 |
| 50                                      | 6200 K | R3                                   | 122       | XPEWHT-L1-0000-00F50 |
|   |        | R2                                   | 114       | XPEWHT-L1-0000-00E50 |
|   |        | Q5                                   | 107       | XPEWHT-L1-0000-00D50 |
|   |        | Q4                                   | 100       | XPEWHT-L1-0000-00C50 |
| E1                                      | 6500 K | R3                                   | 122       | XPEWHT-L1-0000-00FE1 |
|   |        | R2                                   | 114       | XPEWHT-L1-0000-00EE1 |
|   |        | Q5                                   | 107       | XPEWHT-L1-0000-00DE1 |
|   |        | Q4                                   | 100       | XPEWHT-L1-0000-00CE1 |
| E2                                      | 5700 K | R3                                   | 122       | XPEWHT-L1-0000-00FE2 |
|   |        | R2                                   | 114       | XPEWHT-L1-0000-00EE2 |
|   |        | Q5                                   | 107       | XPEWHT-L1-0000-00DE2 |
|   |        | Q4                                   | 100       | XPEWHT-L1-0000-00CE2 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.



**STANDARD ORDER CODES AND BINS (XP-E NEUTRAL WHITE, OUTDOOR WHITE, T<sub>j</sub> = 25 °C)**

| XLamp XP-E Standard Kit Codes - White |        |                                      |           |                      |                      |                      |
|---------------------------------------|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|
| Chromaticity                          |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |
| Kit                                   | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 75 CRI Typical       | 80 CRI Minimum       |
| ANSI Neutral White (3700 K – 5000 K)  |        |                                      |           |                      |                      |                      |
| E3                                    | 5000 K | Q5                                   | 107       |                      | XPEWHT-L1-0000-00DE3 |                      |
|                                       |        | Q4                                   | 100       |                      | XPEWHT-L1-0000-00CE3 |                      |
|                                       |        | Q3                                   | 93.9      |                      | XPEWHT-L1-0000-00BE3 |                      |
| C1                                    | 5000 K | R3                                   | 122       | XPEWHT-01-0000-00FC1 |                      |                      |
|                                       |        | R2                                   | 114       | XPEWHT-01-0000-00EC1 |                      |                      |
|                                       |        | Q5                                   | 107       | XPEWHT-01-0000-00DC1 |                      |                      |
|                                       |        | Q4                                   | 100       | XPEWHT-01-0000-00CC1 |                      |                      |
| F4                                    | 4750 K | Q5                                   | 107       |                      | XPEWHT-L1-0000-00DF4 |                      |
|                                       |        | Q4                                   | 100       |                      | XPEWHT-L1-0000-00CF4 |                      |
|                                       |        | Q3                                   | 93.9      |                      | XPEWHT-L1-0000-00BF4 |                      |
| D1                                    | 4750 K | R3                                   | 122       | XPEWHT-01-0000-00FD1 |                      |                      |
|                                       |        | R2                                   | 114       | XPEWHT-01-0000-00ED1 |                      |                      |
|                                       |        | Q5                                   | 107       | XPEWHT-01-0000-00DD1 |                      |                      |
|                                       |        | Q4                                   | 100       | XPEWHT-01-0000-00CD1 |                      |                      |
| E4                                    | 4500 K | Q5                                   | 107       |                      | XPEWHT-L1-0000-00DE4 |                      |
|                                       |        | Q4                                   | 100       |                      | XPEWHT-L1-0000-00CE4 |                      |
|                                       |        | Q3                                   | 93.9      |                      | XPEWHT-L1-0000-00BE4 |                      |
| D2                                    | 4500 K | R3                                   | 122       | XPEWHT-01-0000-00FD2 |                      |                      |
|                                       |        | R2                                   | 114       | XPEWHT-01-0000-00ED2 |                      |                      |
|                                       |        | Q5                                   | 107       | XPEWHT-01-0000-00DD2 |                      |                      |
|                                       |        | Q4                                   | 100       | XPEWHT-01-0000-00CD2 |                      |                      |
| C2                                    | 4500 K | R3                                   | 122       | XPEWHT-01-0000-00FC2 |                      |                      |
|                                       |        | R2                                   | 114       | XPEWHT-01-0000-00EC2 |                      |                      |
|                                       |        | Q5                                   | 107       | XPEWHT-01-0000-00DC2 |                      |                      |
|                                       |        | Q4                                   | 100       | XPEWHT-01-0000-00CC2 |                      |                      |
| C3                                    | 4300 K | R3                                   | 122       | XPEWHT-01-0000-00FC3 |                      |                      |
|                                       |        | R2                                   | 114       | XPEWHT-01-0000-00EC3 |                      |                      |
|                                       |        | Q5                                   | 107       | XPEWHT-01-0000-00DC3 |                      |                      |
|                                       |        | Q4                                   | 100       | XPEWHT-01-0000-00CC3 |                      |                      |
| F5                                    | 4250 K | Q5                                   | 107       |                      | XPEWHT-L1-0000-00DF5 |                      |
|                                       |        | Q4                                   | 100       |                      | XPEWHT-L1-0000-00CF5 |                      |
|                                       |        | Q3                                   | 93.9      |                      | XPEWHT-L1-0000-00BF5 |                      |
|                                       |        | Q2                                   | 87.4      |                      | XPEWHT-L1-0000-00AF5 |                      |
| E5                                    | 4000 K | Q5                                   | 107       |                      | XPEWHT-L1-0000-00DE5 |                      |
|                                       |        | Q4                                   | 100       |                      | XPEWHT-L1-0000-00CE5 | XPEWHT-H1-0000-00CE5 |
|                                       |        | Q3                                   | 93.9      |                      | XPEWHT-L1-0000-00BE5 | XPEWHT-H1-0000-00BE5 |
|                                       |        | Q2                                   | 87.4      |                      | XPEWHT-L1-0000-00AE5 | XPEWHT-H1-0000-00AE5 |
| Z5                                    | 4000 K | Q4                                   | 100       |                      | XPEWHT-L1-0000-00CZ5 |                      |
|                                       |        | Q3                                   | 93.9      |                      | XPEWHT-L1-0000-00BZ5 | XPEWHT-H1-0000-00BZ5 |
|                                       |        | Q2                                   | 87.4      |                      | XPEWHT-L1-0000-00AZ5 | XPEWHT-H1-0000-00AZ5 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E WARM WHITE, T<sub>j</sub> = 25 °C)**

| XLamp XP-E Standard Kit Codes - White |        |                                      |           |                      |                      |                      |                      |
|---------------------------------------|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|----------------------|
| Chromaticity                          |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |                      |
| Kit                                   | CCT    | Code                                 | Flux (lm) | 80 CRI Typical       | 80 CRI Minimum       | 85 CRI Minimum       | 90 CRI Minimum       |
| ANSI Warm White (2700 K - 3750 K)     |        |                                      |           |                      |                      |                      |                      |
| F6                                    | 3750 K | Q4                                   | 100       | XPEWHT-L1-0000-00CF6 |                      |                      |                      |
|                                       |        | Q3                                   | 93.9      | XPEWHT-L1-0000-00BF6 | XPEWHT-H1-0000-00BF6 |                      |                      |
|                                       |        | Q2                                   | 87.4      | XPEWHT-L1-0000-00AF6 | XPEWHT-H1-0000-00AF6 |                      |                      |
|                                       |        | P4                                   | 80.6      | XPEWHT-L1-0000-009F6 | XPEWHT-H1-0000-009F6 |                      |                      |
| E6                                    | 3500 K | Q4                                   | 100       | XPEWHT-L1-0000-00CE6 |                      |                      |                      |
|                                       |        | Q3                                   | 93.9      | XPEWHT-L1-0000-00BE6 | XPEWHT-H1-0000-00BE6 |                      |                      |
|                                       |        | Q2                                   | 87.4      | XPEWHT-L1-0000-00AE6 | XPEWHT-H1-0000-00AE6 |                      |                      |
|                                       |        | P4                                   | 80.6      | XPEWHT-L1-0000-009E6 | XPEWHT-H1-0000-009E6 |                      |                      |
| Z6                                    | 3500 K | Q3                                   | 93.9      | XPEWHT-L1-0000-00BZ6 |                      |                      |                      |
|                                       |        | Q2                                   | 87.4      | XPEWHT-L1-0000-00AZ6 | XPEWHT-H1-0000-00AZ6 |                      |                      |
|                                       |        | P4                                   | 80.6      | XPEWHT-L1-0000-009Z6 | XPEWHT-H1-0000-009Z6 |                      |                      |
| F7                                    | 3250 K | Q3                                   | 93.9      | XPEWHT-L1-0000-00BF7 |                      |                      |                      |
|                                       |        | Q2                                   | 87.4      | XPEWHT-L1-0000-00AF7 | XPEWHT-H1-0000-00AF7 |                      |                      |
|                                       |        | P4                                   | 80.6      | XPEWHT-L1-0000-009F7 | XPEWHT-H1-0000-009F7 |                      |                      |
| E7                                    | 3000 K | Q3                                   | 93.9      | XPEWHT-L1-0000-00BE7 |                      |                      |                      |
|                                       |        | Q2                                   | 87.4      | XPEWHT-L1-0000-00AE7 | XPEWHT-H1-0000-00AE7 |                      |                      |
|                                       |        | P4                                   | 80.6      | XPEWHT-L1-0000-009E7 | XPEWHT-H1-0000-009E7 | XPEWHT-P1-0000-009E7 |                      |
|                                       |        | P3                                   | 73.9      |                      |                      | XPEWHT-P1-0000-008E7 | XPEWHT-U1-0000-008E7 |
|                                       |        | P2                                   | 67.2      |                      |                      | XPEWHT-P1-0000-007E7 | XPEWHT-U1-0000-007E7 |
|                                       |        | N4                                   | 62        |                      |                      | XPEWHT-P1-0000-006E7 | XPEWHT-U1-0000-006E7 |
| Z7                                    | 3000 K | Q2                                   | 87.4      | XPEWHT-L1-0000-00AZ7 | XPEWHT-H1-0000-00AZ7 |                      |                      |
|                                       |        | P4                                   | 80.6      | XPEWHT-L1-0000-009Z7 | XPEWHT-H1-0000-009Z7 |                      |                      |
|                                       |        | P3                                   | 73.9      |                      |                      | XPEWHT-P1-0000-008Z7 |                      |
|                                       |        | P2                                   | 67.2      |                      |                      | XPEWHT-P1-0000-007Z7 | XPEWHT-U1-0000-007Z7 |
|                                       |        | N4                                   | 62        |                      |                      | XPEWHT-P1-0000-006Z7 | XPEWHT-U1-0000-006Z7 |
| F8                                    | 2850 K | Q2                                   | 87.4      | XPEWHT-L1-0000-00AF8 |                      |                      |                      |
|                                       |        | P4                                   | 80.6      | XPEWHT-L1-0000-009F8 | XPEWHT-H1-0000-009F8 |                      |                      |
|                                       |        | P3                                   | 73.9      | XPEWHT-L1-0000-008F8 | XPEWHT-H1-0000-008F8 | XPEWHT-P1-0000-008F8 |                      |
|                                       |        | P2                                   | 67.2      |                      |                      | XPEWHT-P1-0000-007F8 | XPEWHT-U1-0000-007F8 |
|                                       |        | N4                                   | 62        |                      |                      | XPEWHT-P1-0000-006F8 | XPEWHT-U1-0000-006F8 |
|                                       |        | N3                                   | 56.8      |                      |                      | XPEWHT-P1-0000-005F8 | XPEWHT-U1-0000-005F8 |
| E8                                    | 2700 K | Q2                                   | 87.4      | XPEWHT-L1-0000-00AE8 |                      |                      |                      |
|                                       |        | P4                                   | 80.6      | XPEWHT-L1-0000-009E8 | XPEWHT-H1-0000-009E8 |                      |                      |
|                                       |        | P3                                   | 73.9      | XPEWHT-L1-0000-008E8 | XPEWHT-H1-0000-008E8 | XPEWHT-P1-0000-008E8 |                      |
|                                       |        | P2                                   | 67.2      |                      |                      | XPEWHT-P1-0000-007E8 | XPEWHT-U1-0000-007E8 |
|                                       |        | N4                                   | 62        |                      |                      | XPEWHT-P1-0000-006E8 | XPEWHT-U1-0000-006E8 |
|                                       |        | N3                                   | 56.8      |                      |                      | XPEWHT-P1-0000-005E8 | XPEWHT-U1-0000-005E8 |
| Z8                                    | 2700 K | P4                                   | 80.6      | XPEWHT-L1-0000-009Z8 | XPEWHT-H1-0000-009Z8 |                      |                      |
|                                       |        | P3                                   | 73.9      | XPEWHT-L1-0000-008Z8 | XPEWHT-H1-0000-008Z8 |                      |                      |
|                                       |        | P2                                   | 67.2      |                      |                      | XPEWHT-P1-0000-007Z8 |                      |
|                                       |        | N4                                   | 62        |                      |                      | XPEWHT-P1-0000-006Z8 | XPEWHT-U1-0000-006Z8 |
|                                       |        | N3                                   | 56.8      |                      |                      | XPEWHT-P1-0000-005Z8 | XPEWHT-U1-0000-005Z8 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E COLOR, T<sub>j</sub> = 25 °C)**

| XLamp XP-E LED Standard Order Codes - Royal Blue |                                  |           |                          |          |       |          |                      |
|--|----------------------------------|-----------|--------------------------|----------|-------|----------|----------------------|
| Color  | Min. Radiant Flux (mW) @ 350 mA* |           | Dominant Wavelength (nm) |          |       |          | Order Codes          |
|  | Group                            | Flux (mW) | Min.                     |          | Max.  |          |                      |
|  |                                  |           | Group                    | DWL (nm) | Group | DWL (nm) |                      |
| Royal Blue                                       | 14                               | 350       | D3                       | 450      | D5    | 465      | XPEROY-L1-0000-00901 |
|  |                                  |           | D3                       | 450      | D4    | 460      | XPEROY-L1-0000-00902 |
|  |                                  |           | D4                       | 455      | D5    | 465      | XPEROY-L1-0000-00903 |
|  | 15                               | 425       | D3                       | 450      | D5    | 465      | XPEROY-L1-0000-00A01 |
|  |                                  |           | D3                       | 450      | D4    | 460      | XPEROY-L1-0000-00A02 |
|  |                                  |           | D4                       | 455      | D5    | 465      | XPEROY-L1-0000-00A03 |
|  | 16                               | 500       | D3                       | 450      | D5    | 465      | XPEROY-L1-0000-00B01 |
|  |                                  |           | D3                       | 450      | D4    | 460      | XPEROY-L1-0000-00B02 |

| XLamp XP-E LED Standard Order Codes - Color |                                   |           |                          |          |       |          |                      |
|---|-----------------------------------|-----------|--------------------------|----------|-------|----------|----------------------|
| Color                                       | Min. Luminous Flux (lm) @ 350 mA* |           | Dominant Wavelength (nm) |          |       |          | Order Codes          |
|   | Group                             | Flux (lm) | Min.                     |          | Max.  |          |                      |
|   |                                   |           | Group                    | DWL (nm) | Group | DWL (nm) |                      |
| Blue  | K2                                | 30.6      | B3                       | 465      | B6    | 485      | XPEBLU-L1-0000-00Y01 |
|   |                                   |           | B3                       | 465      | B5    | 480      | XPEBLU-L1-0000-00Y02 |
|   |                                   |           | B4                       | 470      | B5    | 480      | XPEBLU-L1-0000-00Y05 |
|   | K3                                | 35.2      | B3                       | 465      | B6    | 485      | XPEBLU-L1-0000-00Z01 |
|   |                                   |           | B3                       | 465      | B5    | 480      | XPEBLU-L1-0000-00Z02 |
|   |                                   |           | B4                       | 470      | B5    | 480      | XPEBLU-L1-0000-00Z05 |
|   | M2                                | 39.8      | B3                       | 465      | B6    | 485      | XPEBLU-L1-0000-00201 |
|   |                                   |           | B3                       | 465      | B5    | 480      | XPEBLU-L1-0000-00202 |
|   |                                   |           | B4                       | 470      | B5    | 480      | XPEBLU-L1-0000-00205 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E COLOR, T<sub>j</sub> = 25 °C, CONTINUED)**

| XLamp XP-E LED Standard Order Codes - Color |                                  |           |                          |          |       |          |                      |                      |
|---|----------------------------------|-----------|--------------------------|----------|-------|----------|----------------------|----------------------|
| Color                                       | Min. Luminous Flux (lm)@ 350 mA* |           | Dominant Wavelength (nm) |          |       |          | Order Codes          |                      |
|   | Group                            | Flux (lm) | Min.                     |          | Max.  |          |                      |                      |
|   |                                  |           | Group                    | DWL (nm) | Group | DWL (nm) |                      |                      |
| Green                                       | P4                               | 80.6      | G2                       | 520      | G4    | 535      | XPEGRN-L1-0000-00901 |                      |
|   |                                  |           | G2                       | 520      | G3    | 530      | XPEGRN-L1-0000-00902 |                      |
|   |                                  |           | G3                       | 525      | G4    | 535      | XPEGRN-L1-0000-00903 |                      |
|   | Q2                               | 87.4      | G2                       | 520      | G4    | 535      | XPEGRN-L1-0000-00A01 |                      |
|   |                                  |           | G2                       | 520      | G3    | 530      | XPEGRN-L1-0000-00A02 |                      |
|   |                                  |           | G3                       | 525      | G4    | 535      | XPEGRN-L1-0000-00A03 |                      |
|   | Q3                               | 93.9      | G2                       | 520      | G4    | 535      | XPEGRN-L1-0000-00B01 |                      |
|   |                                  |           | G2                       | 520      | G3    | 530      | XPEGRN-L1-0000-00B02 |                      |
|   |                                  |           | G3                       | 525      | G4    | 535      | XPEGRN-L1-0000-00B03 |                      |
|   | Q4                               | 100       | G2                       | 520      | G4    | 535      | XPEGRN-L1-0000-00C01 |                      |
|   |                                  |           | G2                       | 520      | G3    | 530      | XPEGRN-L1-0000-00C02 |                      |
|   |                                  |           | G3                       | 525      | G4    | 535      | XPEGRN-L1-0000-00C03 |                      |
|   | Q5                               | 107       | G2                       | 520      | G4    | 535      | XPEGRN-L1-0000-00D01 |                      |
|   |                                  |           | G2                       | 520      | G3    | 530      | XPEGRN-L1-0000-00D02 |                      |
|   |                                  |           | G3                       | 525      | G4    | 535      | XPEGRN-L1-0000-00D03 |                      |
|   | R2                               | 114       | G2                       | 520      | G4    | 535      | XPEGRN-L1-0000-00E01 |                      |
|   |                                  |           | G2                       | 520      | G3    | 530      | XPEGRN-L1-0000-00E02 |                      |
|   |                                  |           | G3                       | 525      | G4    | 535      | XPEGRN-L1-0000-00E03 |                      |
|   | Amber                            | M3        | 45.7                     | A2       | 585   | A3       | 595                  | XPEAMB-L1-0000-00301 |
|   |                                  | N2        | 51.7                     | A2       | 585   | A3       | 595                  | XPEAMB-L1-0000-00401 |
|   |                                  | N3        | 56.8                     | A2       | 585   | A3       | 595                  | XPEAMB-L1-0000-00501 |
|   |                                  | N4        | 62.0                     | A2       | 585   | A3       | 595                  | XPEAMB-L1-0000-00601 |
|   |                                  | P2        | 67.2                     | A2       | 585   | A3       | 595                  | XPEAMB-L1-0000-00701 |
|   |                                  | P3        | 73.9                     | A2       | 585   | A3       | 595                  | XPEAMB-L1-0000-00801 |
| P4  |                                  | 80.6      | A2                       | 585      | A3    | 595      | XPEAMB-L1-0000-00901 |                      |
| Red-Orange                                  | N3                               | 56.8      | O3                       | 610      | O4    | 620      | XPERDO-L1-0000-00501 |                      |
|   | N4                               | 62.0      | O3                       | 610      | O4    | 620      | XPERDO-L1-0000-00601 |                      |
|   | P2                               | 67.2      | O3                       | 610      | O4    | 620      | XPERDO-L1-0000-00701 |                      |
|   | P3                               | 73.9      | O3                       | 610      | O4    | 620      | XPERDO-L1-0000-00801 |                      |
|   | P4                               | 80.6      | O3                       | 610      | O4    | 620      | XPERDO-L1-0000-00901 |                      |
|   | Q2                               | 87.4      | O3                       | 610      | O4    | 620      | XPERDO-L1-0000-00A01 |                      |
| Red   | M3                               | 45.7      | R2                       | 620      | R3    | 630      | XPERED-L1-0000-00301 |                      |
|   | N2                               | 51.7      | R2                       | 620      | R3    | 630      | XPERED-L1-0000-00401 |                      |
|   | N3                               | 56.8      | R2                       | 620      | R3    | 630      | XPERED-L1-0000-00501 |                      |
|   | N4                               | 62        | R2                       | 620      | R3    | 630      | XPERED-L1-0000-00601 |                      |
|   | P2                               | 67.2      | R2                       | 620      | R3    | 630      | XPERED-L1-0000-00701 |                      |
|   | P3                               | 73.9      | R2                       | 620      | R3    | 630      | XPERED-L1-0000-00801 |                      |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E2 ANSI COOL WHITE, T<sub>j</sub> = 85 °C)**

| XLamp XP-E2 Standard Order Codes - White |        |                                      |           |                      |
|--|--------|--------------------------------------|-----------|----------------------|
| Chromaticity                             |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |
| Kit                                      | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       |
| ANSI Cool White (5000 K – 8300 K)        |        |                                      |           |                      |
| 51                                       | 6200 K | R3                                   | 122       | XPEBWT-L1-0000-00F51 |
|  |        | R2                                   | 114       | XPEBWT-L1-0000-00E51 |
|  |        | Q5                                   | 107       | XPEBWT-L1-0000-00D51 |
|  |        | Q4                                   | 100       | XPEBWT-L1-0000-00C51 |
| 53                                       | 6000 K | R3                                   | 122       | XPEBWT-L1-0000-00F53 |
|  |        | R2                                   | 114       | XPEBWT-L1-0000-00E53 |
|  |        | Q5                                   | 107       | XPEBWT-L1-0000-00D53 |
|  |        | Q4                                   | 100       | XPEBWT-L1-0000-00C53 |
| 50                                       | 6200 K | R3                                   | 122       | XPEBWT-L1-0000-00F50 |
|  |        | R2                                   | 114       | XPEBWT-L1-0000-00E50 |
|  |        | Q5                                   | 107       | XPEBWT-L1-0000-00D50 |
|  |        | Q4                                   | 100       | XPEBWT-L1-0000-00C50 |
| E1                                       | 6500 K | R3                                   | 122       | XPEBWT-L1-0000-00FE1 |
|  |        | R2                                   | 114       | XPEBWT-L1-0000-00EE1 |
|  |        | Q5                                   | 107       | XPEBWT-L1-0000-00DE1 |
|  |        | Q4                                   | 100       | XPEBWT-L1-0000-00CE1 |
| E2                                       | 5700 K | R3                                   | 122       | XPEBWT-L1-0000-00FE2 |
|  |        | R2                                   | 114       | XPEBWT-L1-0000-00EE2 |
|  |        | Q5                                   | 107       | XPEBWT-L1-0000-00DE2 |
|  |        | Q4                                   | 100       | XPEBWT-L1-0000-00CE2 |

**STANDARD ORDER CODES AND BINS (XP-E2 NEUTRAL WHITE, OUTDOOR WHITE, T<sub>j</sub> = 85 °C)**

| XLamp XP-E2 Standard Kit Codes - White |        |                                      |           |                      |                      |                |
|--|--------|--------------------------------------|-----------|----------------------|----------------------|----------------|
| Chromaticity                           |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                |
| Kit                                    | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 75 CRI Typical       | 80 CRI Minimum |
| ANSI Neutral White (3700 K – 5000 K)   |        |                                      |           |                      |                      |                |
| E3                                     | 5000 K | R2                                   | 114       |                      | XPEBWT-L1-0000-00EE3 |                |
|  |        | Q5                                   | 107       |                      | XPEBWT-L1-0000-00DE3 |                |
|  |        | Q4                                   | 100       |                      | XPEBWT-L1-0000-00CE3 |                |
| C1                                     | 5000 K | R3                                   | 122       | XPEBWT-01-0000-00FC1 |                      |                |
|  |        | R2                                   | 114       | XPEBWT-01-0000-00EC1 |                      |                |
|  |        | Q5                                   | 107       | XPEBWT-01-0000-00DC1 |                      |                |
|  |        | Q4                                   | 100       | XPEBWT-01-0000-00CC1 |                      |                |
| F4                                     | 4750 K | R2                                   | 114       |                      | XPEBWT-L1-0000-00EF4 |                |
|  |        | Q5                                   | 107       |                      | XPEBWT-L1-0000-00DF4 |                |
|  |        | Q4                                   | 100       |                      | XPEBWT-L1-0000-00CF4 |                |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E2 NEUTRAL WHITE, OUTDOOR WHITE, T<sub>j</sub> = 85 °C) - CONTINUED**

| XLamp XP-E2 Standard Kit Codes - White |        |                                      |           |                      |                      |                      |
|--|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|
| Chromaticity                           |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |
| Kit                                    | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 75 CRI Typical       | 80 CRI Minimum       |
| ANSI Neutral White (3700 K – 5000 K)   |        |                                      |           |                      |                      |                      |
| D1                                     | 4750 K | R3                                   | 122       | XPEBWT-01-0000-00FD1 |                      |                      |
|  |        | R2                                   | 114       | XPEBWT-01-0000-00ED1 |                      |                      |
|  |        | Q5                                   | 107       | XPEBWT-01-0000-00DD1 |                      |                      |
|  |        | Q4                                   | 100       | XPEBWT-01-0000-00CD1 |                      |                      |
| E4                                     | 4500 K | R2                                   | 114       |                      | XPEBWT-L1-0000-00EE4 |                      |
|  |        | Q5                                   | 107       |                      | XPEBWT-L1-0000-00DE4 |                      |
|  |        | Q4                                   | 100       |                      | XPEBWT-L1-0000-00CE4 |                      |
| D2                                     | 4500 K | R3                                   | 122       | XPEBWT-01-0000-00FD2 |                      |                      |
|  |        | R2                                   | 114       | XPEBWT-01-0000-00ED2 |                      |                      |
|  |        | Q5                                   | 107       | XPEBWT-01-0000-00DD2 |                      |                      |
|  |        | Q4                                   | 100       | XPEBWT-01-0000-00CD2 |                      |                      |
| C2                                     | 4500 K | R3                                   | 122       | XPEBWT-01-0000-00FC2 |                      |                      |
|  |        | R2                                   | 114       | XPEBWT-01-0000-00EC2 |                      |                      |
|  |        | Q5                                   | 107       | XPEBWT-01-0000-00DC2 |                      |                      |
|  |        | Q4                                   | 100       | XPEBWT-01-0000-00CC2 |                      |                      |
| C3                                     | 4300 K | R3                                   | 122       | XPEBWT-01-0000-00FC3 |                      |                      |
|  |        | R2                                   | 114       | XPEBWT-01-0000-00EC3 |                      |                      |
|  |        | Q5                                   | 107       | XPEBWT-01-0000-00DC3 |                      |                      |
|  |        | Q4                                   | 100       | XPEBWT-01-0000-00CC3 |                      |                      |
| F5                                     | 4250 K | R2                                   | 114       |                      | XPEBWT-L1-0000-00EF5 |                      |
|  |        | Q5                                   | 107       |                      | XPEBWT-L1-0000-00DF5 |                      |
|  |        | Q4                                   | 100       |                      | XPEBWT-L1-0000-00CF5 |                      |
|  |        | Q3                                   | 93.9      |                      | XPEBWT-L1-0000-00BF5 |                      |
| E5                                     | 4000 K | R2                                   | 114       |                      | XPEBWT-L1-0000-00EE5 |                      |
|  |        | Q5                                   | 107       |                      | XPEBWT-L1-0000-00DE5 | XPEBWT-H1-0000-00DE5 |
|  |        | Q4                                   | 100       |                      | XPEBWT-L1-0000-00CE5 | XPEBWT-H1-0000-00CE5 |
|  |        | Q3                                   | 93.9      |                      | XPEBWT-L1-0000-00BE5 | XPEBWT-H1-0000-00BE5 |
| Z5                                     | 4000 K | Q5                                   | 107       |                      | XPEBWT-L1-0000-00DZ5 |                      |
|  |        | Q4                                   | 100       |                      | XPEBWT-L1-0000-00CZ5 | XPEBWT-H1-0000-00CZ5 |
|  |        | Q3                                   | 93.9      |                      | XPEBWT-L1-0000-00BZ5 | XPEBWT-H1-0000-00BZ5 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

STANDARD ORDER CODES AND BINS (XP-E2 WARM WHITE, T<sub>j</sub> = 85 °C)

| XLamp XP-E2 Standard Kit Codes - White |        |                                      |           |                      |                      |                      |                      |
|--|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|----------------------|
| Chromaticity                           |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |                      |
| Kit                                    | CCT    | Code                                 | Flux (lm) | 80 CRI Typical       | 80 CRI Minimum       | 85 CRI Minimum       | 90 CRI Minimum       |
| ANSI Warm White (2700 K - 3750 K)      |        |                                      |           |                      |                      |                      |                      |
| F6                                     | 3750 K | Q5                                   | 107       | XPEBWT-L1-0000-00DF6 |                      |                      |                      |
|  |        | Q4                                   | 100       | XPEBWT-L1-0000-00CF6 | XPEBWT-H1-0000-00CF6 |                      |                      |
|  |        | Q3                                   | 93.9      | XPEBWT-L1-0000-00BF6 | XPEBWT-H1-0000-00BF6 |                      |                      |
|  |        | Q2                                   | 87.4      | XPEBWT-L1-0000-00AF6 | XPEBWT-H1-0000-00AF6 |                      |                      |
| E6                                     | 3500 K | Q5                                   | 107       | XPEBWT-L1-0000-00DE6 |                      |                      |                      |
|  |        | Q4                                   | 100       | XPEBWT-L1-0000-00CE6 | XPEBWT-H1-0000-00CE6 |                      |                      |
|  |        | Q3                                   | 93.9      | XPEBWT-L1-0000-00BE6 | XPEBWT-H1-0000-00BE6 |                      |                      |
|  |        | Q2                                   | 87.4      | XPEBWT-L1-0000-00AE6 | XPEBWT-H1-0000-00AE6 |                      |                      |
| Z6                                     | 3500 K | Q4                                   | 100       | XPEBWT-L1-0000-00CZ6 |                      |                      |                      |
|  |        | Q3                                   | 93.9      | XPEBWT-L1-0000-00BZ6 | XPEBWT-H1-0000-00BZ6 |                      |                      |
|  |        | Q2                                   | 87.4      | XPEBWT-L1-0000-00AZ6 | XPEBWT-H1-0000-00AZ6 |                      |                      |
| F7                                     | 3250 K | Q4                                   | 100       | XPEBWT-L1-0000-00CF7 |                      |                      |                      |
|  |        | Q3                                   | 93.9      | XPEBWT-L1-0000-00BF7 | XPEBWT-H1-0000-00BF7 |                      |                      |
|  |        | Q2                                   | 87.4      | XPEBWT-L1-0000-00AF7 | XPEBWT-H1-0000-00AF7 |                      |                      |
| E7                                     | 3000 K | Q4                                   | 100       | XPEBWT-L1-0000-00CE7 |                      |                      |                      |
|  |        | Q3                                   | 93.9      | XPEBWT-L1-0000-00BE7 | XPEBWT-H1-0000-00BE7 |                      |                      |
|  |        | Q2                                   | 87.4      | XPEBWT-L1-0000-00AE7 | XPEBWT-H1-0000-00AE7 | XPEBWT-P1-0000-00AE7 |                      |
|  |        | P4                                   | 80.6      |                      |                      | XPEBWT-P1-0000-009E7 | XPEBWT-U1-0000-009E7 |
|  |        | P3                                   | 73.9      |                      |                      | XPEBWT-P1-0000-008E7 | XPEBWT-U1-0000-008E7 |
|  |        | P2                                   | 67.2      |                      |                      | XPEBWT-P1-0000-007E7 | XPEBWT-U1-0000-007E7 |
| Z7                                     | 3000 K | Q3                                   | 93.9      | XPEBWT-L1-0000-00BZ7 | XPEBWT-H1-0000-00BZ7 |                      |                      |
|  |        | Q2                                   | 87.4      | XPEBWT-L1-0000-00AZ7 | XPEBWT-H1-0000-00AZ7 |                      |                      |
|  |        | P4                                   | 80.6      |                      |                      | XPEBWT-P1-0000-009Z7 |                      |
|  |        | P3                                   | 73.9      |                      |                      | XPEBWT-P1-0000-008Z7 | XPEBWT-U1-0000-008Z7 |
|  |        | P2                                   | 67.2      |                      |                      | XPEBWT-P1-0000-007Z7 | XPEBWT-U1-0000-007Z7 |
| F8                                     | 2850 K | Q3                                   | 93.9      | XPEBWT-L1-0000-00BF8 |                      |                      |                      |
|  |        | Q2                                   | 87.4      | XPEBWT-L1-0000-00AF8 | XPEBWT-H1-0000-00AF8 |                      |                      |
|  |        | P4                                   | 80.6      | XPEBWT-L1-0000-009F8 | XPEBWT-H1-0000-009F8 | XPEBWT-P1-0000-009F8 |                      |
|  |        | P3                                   | 73.9      |                      |                      | XPEBWT-P1-0000-008F8 | XPEBWT-U1-0000-008F8 |
|  |        | P2                                   | 67.2      |                      |                      | XPEBWT-P1-0000-007F8 | XPEBWT-U1-0000-007F8 |
|  |        | N4                                   | 62        |                      |                      | XPEBWT-P1-0000-006F8 | XPEBWT-U1-0000-006F8 |
| E8                                     | 2700 K | Q3                                   | 93.9      | XPEBWT-L1-0000-00BE8 |                      |                      |                      |
|  |        | Q2                                   | 87.4      | XPEBWT-L1-0000-00AE8 | XPEBWT-H1-0000-00AE8 |                      |                      |
|  |        | P4                                   | 80.6      | XPEBWT-L1-0000-009E8 | XPEBWT-H1-0000-009E8 | XPEBWT-P1-0000-009E8 |                      |
|  |        | P3                                   | 73.9      |                      |                      | XPEBWT-P1-0000-008E8 | XPEBWT-U1-0000-008E8 |
|  |        | P2                                   | 67.2      |                      |                      | XPEBWT-P1-0000-007E8 | XPEBWT-U1-0000-007E8 |
|  |        | N4                                   | 62        |                      |                      | XPEBWT-P1-0000-006E8 | XPEBWT-U1-0000-006E8 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E2 WARM WHITE, T<sub>j</sub> = 85 °C)**

| XLamp XP-E2 Standard Kit Codes - White |        |                                      |           |                      |                      |                      |                      |
|--|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|----------------------|
| Chromaticity                           |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |                      |
| Kit                                    | CCT    | Code                                 | Flux (lm) | 80 CRI Typical       | 80 CRI Minimum       | 85 CRI Minimum       | 90 CRI Minimum       |
| ANSI Warm White (2700 K - 3750 K)      |        |                                      |           |                      |                      |                      |                      |
| Z8                                     | 2700 K | Q2                                   | 87.4      | XPEBWT-L1-0000-00AZ8 | XPEBWT-H1-0000-00AZ8 |                      |                      |
|  |        | P4                                   | 80.6      | XPEBWT-L1-0000-009Z8 | XPEBWT-H1-0000-009Z8 |                      |                      |
|  |        | P3                                   | 73.9      |                      |                      | XPEBWT-P1-0000-008Z8 |                      |
|  |        | P2                                   | 67.2      |                      |                      | XPEBWT-P1-0000-007Z8 | XPEBWT-U1-0000-007Z8 |
|  |        | N4                                   | 62        |                      |                      | XPEBWT-P1-0000-006Z8 | XPEBWT-U1-0000-006Z8 |
| EA                                     | 2200 K | P2                                   | 67.2      | XPEBWT-L1-0000-007EA | XPEBWT-H1-0000-007EA |                      |                      |
|  |        | N4                                   | 62        | XPEBWT-L1-0000-006EA | XPEBWT-H1-0000-006EA |                      |                      |

**STANDARD ORDER CODES AND BINS (XP-E2 COLOR, T<sub>j</sub> = 25 °C)**

| XLamp XP-E2 LED Standard Order Codes - Royal Blue |                               |           |                          |          |       |          |                      |
|---|-------------------------------|-----------|--------------------------|----------|-------|----------|----------------------|
| Color   | Minimum Radiant Flux @ 350 mA |           | Dominant Wavelength (nm) |          |       |          | Order Codes          |
|   | Group                         | Flux (mW) | Min.                     |          | Max.  |          |                      |
|   |                               |           | Group                    | DWL (nm) | Group | DWL (nm) |                      |
| Royal Blue  | 30                            | 450       | D3                       | 450      | D5    | 465      | XPEBRY-L1-0000-00J01 |
|   |                               |           | D3                       | 450      | D4    | 460      | XPEBRY-L1-0000-00J02 |
|   |                               |           | D4                       | 455      | D5    | 465      | XPEBRY-L1-0000-00J03 |
|   | 31                            | 475       | D3                       | 450      | D5    | 455      | XPEBRY-L1-0000-00K01 |
|   |                               |           | D3                       | 450      | D4    | 460      | XPEBRY-L1-0000-00K02 |
|   |                               |           | D4                       | 455      | D5    | 465      | XPEBRY-L1-0000-00K03 |
|   | 32                            | 500       | D3                       | 450      | D5    | 455      | XPEBRY-L1-0000-00L01 |
|   |                               |           | D3                       | 450      | D4    | 460      | XPEBRY-L1-0000-00L02 |
|   |                               |           | D4                       | 455      | D5    | 465      | XPEBRY-L1-0000-00L03 |
|   | 33                            | 525       | D3                       | 450      | D5    | 455      | XPEBRY-L1-0000-00M01 |
|   |                               |           | D3                       | 450      | D4    | 460      | XPEBRY-L1-0000-00M02 |
|   |                               |           | D4                       | 455      | D5    | 465      | XPEBRY-L1-0000-00M03 |
|   | 34                            | 550       | D3                       | 450      | D5    | 455      | XPEBRY-L1-0000-00N01 |
|   |                               |           | D3                       | 450      | D4    | 460      | XPEBRY-L1-0000-00N02 |
|   |                               |           | D4                       | 455      | D5    | 465      | XPEBRY-L1-0000-00N03 |
|   | 35                            | 575       | D3                       | 450      | D5    | 465      | XPEBRY-L1-0000-00P01 |
|   |                               |           | D3                       | 450      | D4    | 460      | XPEBRY-L1-0000-00P02 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.



STANDARD ORDER CODES AND BINS (XP-E2 COLOR, T<sub>j</sub> = 25 °C, CONTINUED)

| XLamp XP-E2 LED Standard Order Codes - Color |                                   |           |                          |          |       |          |                      |
|--|-----------------------------------|-----------|--------------------------|----------|-------|----------|----------------------|
| Color  | Min. Luminous Flux (lm) @ 350 mA* |           | Dominant Wavelength (nm) |          |       |          | Order Codes          |
|  | Group                             | Flux (lm) | Min.                     |          | Max.  |          |                      |
|  |                                   |           | Group                    | DWL (nm) | Group | DWL (nm) |                      |
| Blue   | K2                                | 30.6      | B3                       | 465      | B6    | 485      | XPEBBL-L1-0000-00Y01 |
|  |                                   |           | B3                       | 465      | B5    | 480      | XPEBBL-L1-0000-00Y02 |
|  |                                   |           | B4                       | 470      | B5    | 480      | XPEBBL-L1-0000-00Y05 |
|  | K3                                | 35.2      | B3                       | 465      | B6    | 485      | XPEBBL-L1-0000-00Z01 |
|  |                                   |           | B3                       | 465      | B5    | 480      | XPEBBL-L1-0000-00Z02 |
|  |                                   |           | B4                       | 470      | B5    | 480      | XPEBBL-L1-0000-00Z05 |
|  | M2                                | 39.8      | B3                       | 465      | B6    | 485      | XPEBBL-L1-0000-00201 |
|  |                                   |           | B3                       | 465      | B5    | 480      | XPEBBL-L1-0000-00202 |
|  |                                   |           | B4                       | 470      | B5    | 480      | XPEBBL-L1-0000-00205 |
|  | M3                                | 45.7      | B3                       | 465      | B6    | 485      | XPEBBL-L1-0000-00301 |
|  |                                   |           | B3                       | 465      | B5    | 480      | XPEBBL-L1-0000-00302 |
|  |                                   |           | B4                       | 470      | B5    | 480      | XPEBBL-L1-0000-00305 |
| Green  | Q2                                | 87.4      | G2                       | 520      | G4    | 535      | XPEBGR-L1-0000-00A01 |
|  |                                   |           | G2                       | 520      | G3    | 530      | XPEBGR-L1-0000-00A02 |
|  |                                   |           | G3                       | 525      | G4    | 535      | XPEBGR-L1-0000-00A03 |
|  | Q3                                | 93.9      | G2                       | 520      | G4    | 535      | XPEBGR-L1-0000-00B01 |
|  |                                   |           | G2                       | 520      | G3    | 530      | XPEBGR-L1-0000-00B02 |
|  |                                   |           | G3                       | 525      | G4    | 535      | XPEBGR-L1-0000-00B03 |
|  | Q4                                | 100       | G2                       | 520      | G4    | 535      | XPEBGR-L1-0000-00C01 |
|  |                                   |           | G2                       | 520      | G3    | 530      | XPEBGR-L1-0000-00C02 |
|  |                                   |           | G3                       | 525      | G4    | 535      | XPEBGR-L1-0000-00C03 |
|  | Q5                                | 107       | G2                       | 520      | G4    | 535      | XPEBGR-L1-0000-00D01 |
|  |                                   |           | G2                       | 520      | G3    | 530      | XPEBGR-L1-0000-00D02 |
|  |                                   |           | G3                       | 525      | G4    | 535      | XPEBGR-L1-0000-00D03 |
|  | R2                                | 114       | G2                       | 520      | G4    | 535      | XPEBGR-L1-0000-00E01 |
|  |                                   |           | G2                       | 520      | G3    | 530      | XPEBGR-L1-0000-00E02 |
|  |                                   |           | G3                       | 525      | G4    | 535      | XPEBGR-L1-0000-00E03 |
|  | R3                                | 122       | G2                       | 520      | G4    | 535      | XPEBGR-L1-0000-00F01 |
|  |                                   |           | G2                       | 520      | G3    | 530      | XPEBGR-L1-0000-00F02 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E2 COLOR, T<sub>j</sub> = 25 °C, CONTINUED)**

| XLamp XP-E2 LED Standard Order Codes - Color |                                   |           |                          |          |       |          |                      |
|--|-----------------------------------|-----------|--------------------------|----------|-------|----------|----------------------|
| Color  | Min. Luminous Flux (lm) @ 350 mA* |           | Dominant Wavelength (nm) |          |       |          | Order Codes          |
|  | Group                             | Flux (lm) | Min.                     |          | Max.  |          |                      |
|  |                                   |           | Group                    | DWL (nm) | Group | DWL (nm) |                      |
| Amber  | N4                                | 62.0      | A2                       | 585      | A3    | 595      | XPEBAM-L1-0000-00601 |
|  |                                   |           | A2                       | 585      | A2    | 590      | XPEBAM-L1-0000-00602 |
|  |                                   |           | A3                       | 590      | A3    | 595      | XPEBAM-L1-0000-00603 |
|  | P2                                | 67.2      | A2                       | 585      | A3    | 595      | XPEBAM-L1-0000-00701 |
|  |                                   |           | A2                       | 585      | A2    | 590      | XPEBAM-L1-0000-00702 |
|  |                                   |           | A3                       | 590      | A3    | 595      | XPEBAM-L1-0000-00703 |
|  | P3                                | 73.9      | A2                       | 585      | A3    | 595      | XPEBAM-L1-0000-00801 |
|  |                                   |           | A2                       | 585      | A2    | 590      | XPEBAM-L1-0000-00802 |
|  |                                   |           | A3                       | 590      | A3    | 595      | XPEBAM-L1-0000-00803 |
|  | P4                                | 80.6      | A2                       | 585      | A3    | 595      | XPEBAM-L1-0000-00901 |
|  |                                   |           | A3                       | 590      | A3    | 595      | XPEBAM-L1-0000-00903 |
|  | Red-Orange                        | P2        | 67.2                     | O3       | 610   | O4       | 620                  |
| O3   |                                   |           |                          | 610      | O3    | 615      | XPEBRO-L1-0000-00702 |
| O4   |                                   |           |                          | 615      | O4    | 620      | XPEBRO-L1-0000-00703 |
| P3   |                                   | 73.9      | O3                       | 610      | O4    | 620      | XPEBRO-L1-0000-00801 |
|  |                                   |           | O3                       | 610      | O3    | 615      | XPEBRO-L1-0000-00802 |
|  |                                   |           | O4                       | 615      | O4    | 620      | XPEBRO-L1-0000-00803 |
| P4   |                                   | 80.6      | O3                       | 610      | O4    | 620      | XPEBRO-L1-0000-00901 |
|  |                                   |           | O3                       | 610      | O3    | 615      | XPEBRO-L1-0000-00902 |
|  |                                   |           | O4                       | 615      | O4    | 620      | XPEBRO-L1-0000-00903 |
| Q2   |                                   | 87.4      | O3                       | 610      | O4    | 620      | XPEBRO-L1-0000-00A01 |
|  |                                   |           | O3                       | 610      | O3    | 615      | XPEBRO-L1-0000-00A02 |
|  |                                   |           | O4                       | 615      | O4    | 620      | XPEBRO-L1-0000-00A03 |
| Q3   |                                   | 93.9      | O3                       | 610      | O4    | 620      | XPEBRO-L1-0000-00B01 |
|  |                                   |           | O3                       | 610      | O3    | 615      | XPEBRO-L1-0000-00B02 |
| Red  |                                   | N3        | 56.8                     | R2       | 620   | R3       | 630                  |
|  | R2                                |           |                          | 620      | R2    | 625      | XPEBRD-L1-0000-00502 |
|  | N4                                | 62        | R2                       | 620      | R3    | 630      | XPEBRD-L1-0000-00601 |
|  |                                   |           | R2                       | 620      | R2    | 625      | XPEBRD-L1-0000-00602 |
|  | P2                                | 67.2      | R2                       | 620      | R3    | 630      | XPEBRD-L1-0000-00701 |
|  |                                   |           | R2                       | 620      | R2    | 625      | XPEBRD-L1-0000-00702 |
|  | P3                                | 73.9      | R2                       | 620      | R3    | 630      | XPEBRD-L1-0000-00801 |
|  |                                   |           | R2                       | 620      | R2    | 625      | XPEBRD-L1-0000-00802 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E HEW ANSI COOL WHITE, T<sub>j</sub> = 25 °C)**

| XLamp XP-E High Efficiency White Order Codes - White |        |                                      |           |                      |
|--|--------|--------------------------------------|-----------|----------------------|
| Chromaticity   |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |
| Kit  | CCT    | Code                                 | Flux (lm) | 68 CRI Typical       |
| ANSI Cool White (5000 K – 8300 K)                    |        |                                      |           |                      |
| 51   | 6200 K | R5                                   | 139       | XPEHEW-L1-0000-00H51 |
|  |        | R4                                   | 130       | XPEHEW-L1-0000-00G51 |
|  |        | R3                                   | 122       | XPEHEW-L1-0000-00F51 |
| 53   | 6000 K | R5                                   | 139       | XPEHEW-L1-0000-00H53 |
|  |        | R4                                   | 130       | XPEHEW-L1-0000-00G53 |
|  |        | R3                                   | 122       | XPEHEW-L1-0000-00F53 |
| 50   | 6200 K | R5                                   | 139       | XPEHEW-L1-0000-00H50 |
|  |        | R4                                   | 130       | XPEHEW-L1-0000-00G50 |
|  |        | R3                                   | 122       | XPEHEW-L1-0000-00F50 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E HEW NEUTRAL WHITE, OUTDOOR WHITE, T<sub>j</sub> = 25 °C)**

| XLamp XP-E High Efficiency White Standard Kit Codes - White |        |                                      |           |                      |                      |                      |
|---|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|
| Chromaticity  |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |
| Kit   | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 75 CRI Typical       | 80 CRI Minimum       |
| ANSI Neutral White (3700 K – 5000 K)                        |        |                                      |           |                      |                      |                      |
| E3  | 5000 K | R3                                   | 122       | XPEHEW-01-0000-00FE3 | XPEHEW-L1-0000-00FE3 |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00EE3 | XPEHEW-L1-0000-00EE3 |                      |
|   |        | Q5                                   | 107       |                      | XPEHEW-L1-0000-00DE3 |                      |
| C1  | 5000 K | R4                                   | 130       | XPEHEW-01-0000-00GC1 |                      |                      |
|   |        | R3                                   | 122       | XPEHEW-01-0000-00FC1 |                      |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00EC1 |                      |                      |
| F4  | 4750 K | R3                                   | 122       | XPEHEW-01-0000-00FF4 | XPEHEW-L1-0000-00FF4 |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00EF4 | XPEHEW-L1-0000-00EF4 |                      |
|   |        | Q5                                   | 107       |                      | XPEHEW-L1-0000-00DF4 |                      |
| D1  | 4750 K | R4                                   | 130       | XPEHEW-01-0000-00GD1 |                      |                      |
|   |        | R3                                   | 122       | XPEHEW-01-0000-00FD1 |                      |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00ED1 |                      |                      |
| E4  | 4500 K | R3                                   | 122       | XPEHEW-01-0000-00FE4 | XPEHEW-L1-0000-00FE4 |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00EE4 | XPEHEW-L1-0000-00EE4 |                      |
|   |        | Q5                                   | 107       |                      | XPEHEW-L1-0000-00DE4 |                      |
| D2  | 4500 K | R4                                   | 130       | XPEHEW-01-0000-00GD2 |                      |                      |
|   |        | R3                                   | 122       | XPEHEW-01-0000-00FD2 |                      |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00ED2 |                      |                      |
| C2  | 4500 K | R4                                   | 130       | XPEHEW-01-0000-00GC2 |                      |                      |
|   |        | R3                                   | 122       | XPEHEW-01-0000-00FC2 |                      |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00EC2 |                      |                      |
| C3  | 4300 K | R4                                   | 130       | XPEHEW-01-0000-00GC3 |                      |                      |
|   |        | R3                                   | 122       | XPEHEW-01-0000-00FC3 |                      |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00EC3 |                      |                      |
| F5  | 4250 K | R3                                   | 122       | XPEHEW-01-0000-00FF5 | XPEHEW-L1-0000-00FF5 |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00EF5 | XPEHEW-L1-0000-00EF5 |                      |
|   |        | Q5                                   | 107       |                      | XPEHEW-L1-0000-00DF5 |                      |
| E5  | 4000 K | R3                                   | 122       | XPEHEW-01-0000-00FE5 | XPEHEW-L1-0000-00FE5 |                      |
|   |        | R2                                   | 114       | XPEHEW-01-0000-00EE5 | XPEHEW-L1-0000-00EE5 | XPEHEW-H1-0000-00EE5 |
|   |        | Q5                                   | 107       |                      | XPEHEW-L1-0000-00DE5 | XPEHEW-H1-0000-00DE5 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-E HEW NEUTRAL WHITE, OUTDOOR WHITE, TJ = 25 °C, CONTINUED)**

| XLamp XP-E High Efficiency White Standard Kit Codes - White |        |                                      |           |                      |                      |                      |                      |                      |
|---|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|----------------------|----------------------|
| Chromaticity  |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |                      |                      |
| Kit   | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 80 CRI Typical       | 80 CRI Minimum       | 85 CRI Minimum       | 90 CRI Minimum       |
| ANSI Warm White (2700 K - 3750 K)                           |        |                                      |           |                      |                      |                      |                      |                      |
| F6  | 3750 K | R2                                   | 114       | XPEHEW-01-0000-00EF6 | XPEHEW-L1-0000-00EF6 | XPEHEW-H1-0000-00EF6 |                      |                      |
|   |        | Q5                                   | 107       | XPEHEW-01-0000-00DF6 | XPEHEW-L1-0000-00DF6 | XPEHEW-H1-0000-00DF6 |                      |                      |
|   |        | Q4                                   | 100       |                      | XPEHEW-L1-0000-00CF6 | XPEHEW-H1-0000-00CF6 |                      |                      |
| E6  | 3500 K | R2                                   | 114       | XPEHEW-01-0000-00EE6 | XPEHEW-L1-0000-00EE6 |                      |                      |                      |
|   |        | Q5                                   | 107       | XPEHEW-01-0000-00DE6 | XPEHEW-L1-0000-00DE6 | XPEHEW-H1-0000-00DE6 |                      |                      |
|   |        | Q4                                   | 100       |                      | XPEHEW-L1-0000-00CE6 | XPEHEW-H1-0000-00CE6 |                      |                      |
| F7  | 3250 K | R2                                   | 114       | XPEHEW-01-0000-00EF7 |                      |                      |                      |                      |
|   |        | Q5                                   | 107       | XPEHEW-01-0000-00DF7 | XPEHEW-L1-0000-00DF7 | XPEHEW-H1-0000-00DF7 |                      |                      |
|   |        | Q4                                   | 100       | XPEHEW-01-0000-00CF7 | XPEHEW-L1-0000-00CF7 | XPEHEW-H1-0000-00CF7 |                      |                      |
|   |        | Q3                                   | 93.9      |                      | XPEHEW-L1-0000-00BF7 | XPEHEW-H1-0000-00BF7 |                      |                      |
|   |        | P3                                   | 73.9      |                      |                      |                      |                      |                      |
| E7  | 3000 K | R2                                   | 114       | XPEHEW-01-0000-00EE7 |                      |                      |                      |                      |
|   |        | Q5                                   | 107       | XPEHEW-01-0000-00DE7 | XPEHEW-L1-0000-00DE7 |                      |                      |                      |
|   |        | Q4                                   | 100       | XPEHEW-01-0000-00CE7 | XPEHEW-L1-0000-00CE7 | XPEHEW-H1-0000-00CE7 |                      |                      |
|   |        | Q3                                   | 93.9      |                      | XPEHEW-L1-0000-00BE7 | XPEHEW-H1-0000-00BE7 | XPEHEW-P1-0000-00BE7 |                      |
|   |        | Q2                                   | 87.4      |                      |                      |                      | XPEHEW-P1-0000-00AE7 | XPEHEW-U1-0000-00AE7 |
|   |        | P4                                   | 80.6      |                      |                      |                      | XPEHEW-P1-0000-009E7 | XPEHEW-U1-0000-009E7 |
| F8  | 2850 K | Q5                                   | 107       | XPEHEW-01-0000-00DF8 |                      |                      |                      |                      |
|   |        | Q4                                   | 100       | XPEHEW-01-0000-00CF8 | XPEHEW-L1-0000-00CF8 | XPEHEW-H1-0000-00CF8 |                      |                      |
|   |        | Q3                                   | 93.9      |                      | XPEHEW-L1-0000-00BF8 | XPEHEW-H1-0000-00BF8 |                      |                      |
|   |        | Q2                                   | 87.4      |                      | XPEHEW-L1-0000-00AF8 | XPEHEW-H1-0000-00AF8 | XPEHEW-P1-0000-00AF8 | XPEHEW-U1-0000-00AF8 |
|   |        | P4                                   | 80.6      |                      |                      |                      | XPEHEW-P1-0000-009F8 | XPEHEW-U1-0000-009F8 |
|   |        | P3                                   | 73.9      |                      |                      |                      | XPEHEW-P1-0000-008F8 | XPEHEW-U1-0000-008F8 |
| E8  | 2700 K | Q5                                   | 107       | XPEHEW-01-0000-00DE8 |                      |                      |                      |                      |
|   |        | Q4                                   | 100       | XPEHEW-01-0000-00CE8 | XPEHEW-L1-0000-00CE8 |                      |                      |                      |
|   |        | Q3                                   | 93.9      |                      | XPEHEW-L1-0000-00BE8 | XPEHEW-H1-0000-00BE8 |                      |                      |
|   |        | Q2                                   | 87.4      |                      | XPEHEW-L1-0000-00AE8 | XPEHEW-H1-0000-00AE8 | XPEHEW-P1-0000-00AE8 |                      |
|   |        | P4                                   | 80.6      |                      |                      |                      | XPEHEW-P1-0000-009E8 | XPEHEW-U1-0000-009E8 |
|   |        | P3                                   | 73.9      |                      |                      |                      | XPEHEW-P1-0000-008E8 | XPEHEW-U1-0000-008E8 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-G ANSI COOL WHITE,  $T_j = 25\text{ }^\circ\text{C}$ )**

| XLamp XP-G Standard Order Codes - White |        |                                      |           |                      |
|---|--------|--------------------------------------|-----------|----------------------|
| Chromaticity                            |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |
| Kit                                     | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       |
| ANSI Cool White (5000 K - 8300 K)       |        |                                      |           |                      |
| 51                                      | 6200 K | R5                                   | 139       | XPGWHT-L1-0000-00H51 |
|   |        | R4                                   | 130       | XPGWHT-L1-0000-00G51 |
|   |        | R3                                   | 122       | XPGWHT-L1-0000-00F51 |
| 53                                      | 6000 K | R5                                   | 139       | XPGWHT-L1-0000-00H53 |
|   |        | R4                                   | 130       | XPGWHT-L1-0000-00G53 |
|   |        | R3                                   | 122       | XPGWHT-L1-0000-00F53 |
| 50                                      | 6200 K | R5                                   | 139       | XPGWHT-L1-0000-00H50 |
|   |        | R4                                   | 130       | XPGWHT-L1-0000-00G50 |
|   |        | R3                                   | 122       | XPGWHT-L1-0000-00F50 |
| E1                                      | 6500 K | R5                                   | 139       | XPGWHT-L1-0000-00HE1 |
|   |        | R4                                   | 130       | XPGWHT-L1-0000-00GE1 |
|   |        | R3                                   | 122       | XPGWHT-L1-0000-00FE1 |
| E2                                      | 5700 K | R5                                   | 139       | XPGWHT-L1-0000-00HE2 |
|   |        | R4                                   | 130       | XPGWHT-L1-0000-00GE2 |
|   |        | R3                                   | 122       | XPGWHT-L1-0000-00FE2 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-G NEUTRAL WHITE, OUTDOOR WHITE, T<sub>j</sub> = 25 °C)**

| XLamp XP-G Standard Kit Codes - White |        |                                      |           |                      |                      |                |
|---------------------------------------|--------|--------------------------------------|-----------|----------------------|----------------------|----------------|
| Chromaticity                          |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                |
| Kit                                   | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 75 CRI Typical       | 80 CRI Minimum |
| ANSI Neutral White (3700 K – 5000 K)  |        |                                      |           |                      |                      |                |
| E3                                    | 5000 K | R5                                   | 139       | XPGWHT-01-0000-00HE3 |                      |                |
|                                       |        | R4                                   | 130       | XPGWHT-01-0000-00GE3 |                      |                |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FE3 | XPGWHT-L1-0000-00FE3 |                |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EE3 | XPGWHT-L1-0000-00EE3 |                |
|                                       |        | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DE3 |                |
| C1                                    | 5000 K | R5                                   | 139       | XPGWHT-01-0000-00HC1 |                      |                |
|                                       |        | R4                                   | 130       | XPGWHT-01-0000-00GC1 |                      |                |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FC1 |                      |                |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EC1 |                      |                |
| F4                                    | 4750 K | R5                                   | 139       | XPGWHT-01-0000-00HF4 |                      |                |
|                                       |        | R4                                   | 130       | XPGWHT-01-0000-00GF4 |                      |                |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FF4 | XPGWHT-L1-0000-00FF4 |                |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EF4 | XPGWHT-L1-0000-00EF4 |                |
|                                       |        | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DF4 |                |
| D1                                    | 4750 K | R5                                   | 139       | XPGWHT-01-0000-00HD1 |                      |                |
|                                       |        | R4                                   | 130       | XPGWHT-01-0000-00GD1 |                      |                |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FD1 |                      |                |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00ED1 |                      |                |
| E4                                    | 4500 K | R5                                   | 139       | XPGWHT-01-0000-00HE4 |                      |                |
|                                       |        | R4                                   | 130       | XPGWHT-01-0000-00GE4 |                      |                |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FE4 | XPGWHT-L1-0000-00FE4 |                |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EE4 | XPGWHT-L1-0000-00EE4 |                |
|                                       |        | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DE4 |                |
| D2                                    | 4500 K | R5                                   | 139       | XPGWHT-01-0000-00HD2 |                      |                |
|                                       |        | R4                                   | 130       | XPGWHT-01-0000-00GD2 |                      |                |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FD2 |                      |                |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00ED2 |                      |                |
| C2                                    | 4500 K | R5                                   | 139       | XPGWHT-01-0000-00HC2 |                      |                |
|                                       |        | R4                                   | 130       | XPGWHT-01-0000-00GC2 |                      |                |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FC2 |                      |                |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EC2 |                      |                |
| C3                                    | 4300 K | R4                                   | 130       | XPGWHT-01-0000-00GC3 |                      |                |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FC3 |                      |                |
| D3                                    | 4300 K | R4                                   | 130       | XPGWHT-01-0000-00GD3 |                      |                |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FD3 |                      |                |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00ED3 |                      |                |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-G NEUTRAL WHITE, OUTDOOR WHITE, T<sub>j</sub> = 25 °C, CONTINUED)**

| XLamp XP-G Standard Kit Codes - White |        |                                      |           |                      |                      |                      |
|---------------------------------------|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|
| Chromaticity                          |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |
| Kit                                   | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 75 CRI Typical       | 80 CRI Minimum       |
| ANSI Neutral White (3700 K – 5000 K)  |        |                                      |           |                      |                      |                      |
| F5                                    | 4250 K | R4                                   | 130       | XPGWHT-01-0000-00GF5 |                      |                      |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FF5 | XPGWHT-L1-0000-00FF5 |                      |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EF5 | XPGWHT-L1-0000-00EF5 |                      |
|                                       |        | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DF5 |                      |
| C4                                    | 4100 K | R3                                   | 122       | XPGWHT-01-0000-00FC4 |                      |                      |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EC4 |                      |                      |
|                                       |        | Q5                                   | 107       | XPGWHT-01-0000-00DC4 |                      |                      |
| D4                                    | 4000 K | R3                                   | 122       | XPGWHT-01-0000-00FD4 |                      |                      |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00ED4 |                      |                      |
|                                       |        | Q5                                   | 107       | XPGWHT-01-0000-00DD4 |                      |                      |
| E5                                    | 4000 K | R4                                   | 130       | XPGWHT-01-0000-00GE5 |                      |                      |
|                                       |        | R3                                   | 122       | XPGWHT-01-0000-00FE5 | XPGWHT-L1-0000-00FE5 |                      |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EE5 | XPGWHT-L1-0000-00EE5 | XPGWHT-H1-0000-00EE5 |
|                                       |        | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DE5 | XPGWHT-H1-0000-00DE5 |
| Z5                                    | 4000 K | R2                                   | 114       |                      | XPGWHT-L1-0000-00EZ5 | XPGWHT-H1-0000-00EZ5 |
|                                       |        | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DZ5 | XPGWHT-H1-0000-00DZ5 |
| C5                                    | 3800 K | R3                                   | 122       | XPGWHT-01-0000-00FC5 |                      |                      |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EC5 |                      |                      |
|                                       |        | Q5                                   | 107       | XPGWHT-01-0000-00DC5 |                      |                      |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.



**STANDARD ORDER CODES AND BINS (XP-G WARM WHITE T<sub>j</sub> = 25 °C)**

| XLamp XP-G Standard Kit Codes - White |        |                                      |           |                      |                      |                      |                      |                      |
|---------------------------------------|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|----------------------|----------------------|
| Chromaticity                          |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |                      |                      |
| Kit                                   | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 80 CRI Typical       | 80 CRI Minimum       | 85 CRI Minimum       | 90 CRI Minimum       |
| ANSI Warm White (2700 K - 3750 K)     |        |                                      |           |                      |                      |                      |                      |                      |
| F6                                    | 3750 K | R3                                   | 122       | XPGWHT-01-0000-00FF6 |                      |                      |                      |                      |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EF6 | XPGWHT-L1-0000-00EF6 | XPGWHT-H1-0000-00EF6 |                      |                      |
|                                       |        | Q5                                   | 107       | XPGWHT-01-0000-00DF6 | XPGWHT-L1-0000-00DF6 | XPGWHT-H1-0000-00DF6 |                      |                      |
|                                       |        | Q4                                   | 100       |                      | XPGWHT-L1-0000-00CF6 | XPGWHT-H1-0000-00CF6 |                      |                      |
| D5                                    | 3700 K | R3                                   | 122       | XPGWHT-01-0000-00FD5 |                      |                      |                      |                      |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00ED5 |                      |                      |                      |                      |
|                                       |        | Q5                                   | 107       | XPGWHT-01-0000-00DD5 |                      |                      |                      |                      |
| C6                                    | 3600 K | R3                                   | 122       | XPGWHT-01-0000-00FC6 |                      |                      |                      |                      |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EC6 |                      |                      |                      |                      |
|                                       |        | Q5                                   | 107       | XPGWHT-01-0000-00DC6 |                      |                      |                      |                      |
| E6                                    | 3500 K | R3                                   | 122       | XPGWHT-01-0000-00FE6 |                      |                      |                      |                      |
|                                       |        | R2                                   | 114       | XPGWHT-01-0000-00EE6 | XPGWHT-L1-0000-00EE6 |                      |                      |                      |
|                                       |        | Q5                                   | 107       | XPGWHT-01-0000-00DE6 | XPGWHT-L1-0000-00DE6 | XPGWHT-H1-0000-00DE6 |                      |                      |
|                                       |        | Q4                                   | 100       |                      | XPGWHT-L1-0000-00CE6 | XPGWHT-H1-0000-00CE6 |                      |                      |
| Z6                                    | 3500 K | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DZ6 | XPGWHT-H1-0000-00DZ6 |                      |                      |
|                                       |        | Q4                                   | 100       |                      | XPGWHT-L1-0000-00CZ6 | XPGWHT-H1-0000-00CZ6 |                      |                      |
| F7                                    | 3250 K | R2                                   | 114       |                      | XPGWHT-L1-0000-00EF7 |                      |                      |                      |
|                                       |        | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DF7 | XPGWHT-H1-0000-00DF7 |                      |                      |
|                                       |        | Q4                                   | 100       |                      | XPGWHT-L1-0000-00CF7 | XPGWHT-H1-0000-00CF7 |                      |                      |
|                                       |        | Q3                                   | 93.9      |                      | XPGWHT-L1-0000-00BF7 | XPGWHT-H1-0000-00BF7 |                      |                      |
| E7                                    | 3000 K | R2                                   | 114       |                      | XPGWHT-L1-0000-00EE7 |                      |                      |                      |
|                                       |        | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DE7 | XPGWHT-H1-0000-00DE7 |                      |                      |
|                                       |        | Q4                                   | 100       |                      | XPGWHT-L1-0000-00CE7 | XPGWHT-H1-0000-00CE7 |                      |                      |
|                                       |        | Q3                                   | 93.9      |                      | XPGWHT-L1-0000-00BE7 | XPGWHT-H1-0000-00BE7 | XPGWHT-P1-0000-00BE7 |                      |
|                                       |        | Q2                                   | 87.4      |                      |                      |                      | XPGWHT-P1-0000-00AE7 | XPGWHT-U1-0000-00AE7 |
|                                       |        | P4                                   | 80.6      |                      |                      |                      | XPGWHT-P1-0000-009E7 | XPGWHT-U1-0000-009E7 |
|                                       |        | P3                                   | 73.9      |                      |                      |                      | XPGWHT-P1-0000-008E7 | XPGWHT-U1-0000-008E7 |
| Z7                                    | 3000 K | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DZ7 | XPGWHT-H1-0000-00DZ7 |                      |                      |
|                                       |        | Q4                                   | 100       |                      | XPGWHT-L1-0000-00CZ7 | XPGWHT-H1-0000-00CZ7 |                      |                      |
|                                       |        | Q3                                   | 93.9      |                      | XPGWHT-L1-0000-00BZ7 | XPGWHT-H1-0000-00BZ7 |                      |                      |
|                                       |        | Q2                                   | 87.4      |                      |                      |                      | XPGWHT-P1-0000-00AZ7 |                      |
|                                       |        | P4                                   | 80.6      |                      |                      |                      | XPGWHT-P1-0000-009Z7 | XPGWHT-U1-0000-009Z7 |
|                                       |        | P3                                   | 73.9      |                      |                      |                      | XPGWHT-P1-0000-008Z7 | XPGWHT-U1-0000-008Z7 |
| F8                                    | 2850 K | Q5                                   | 107       |                      | XPGWHT-L1-0000-00DF8 |                      |                      |                      |
|                                       |        | Q4                                   | 100       |                      | XPGWHT-L1-0000-00CF8 | XPGWHT-H1-0000-00CF8 |                      |                      |
|                                       |        | Q3                                   | 93.9      |                      | XPGWHT-L1-0000-00BF8 | XPGWHT-H1-0000-00BF8 |                      |                      |
|                                       |        | Q2                                   | 87.4      |                      | XPGWHT-L1-0000-00AF8 | XPGWHT-H1-0000-00AF8 | XPGWHT-P1-0000-00AF8 |                      |
|                                       |        | P4                                   | 80.6      |                      |                      |                      | XPGWHT-P1-0000-009F8 | XPGWHT-U1-0000-009F8 |
|                                       |        | P3                                   | 73.9      |                      |                      |                      | XPGWHT-P1-0000-008F8 | XPGWHT-U1-0000-008F8 |
|                                       |        | P2                                   | 67.2      |                      |                      |                      | XPGWHT-P1-0000-007F8 | XPGWHT-U1-0000-007F8 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-G WARM WHITE, T<sub>j</sub> = 25 °C, CONTINUED)**

| XLamp XP-G Standard Kit Codes - White |        |                                      |           |                |                      |                      |                      |                      |
|---------------------------------------|--------|--------------------------------------|-----------|----------------|----------------------|----------------------|----------------------|----------------------|
| Chromaticity                          |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes    |                      |                      |                      |                      |
| Kit                                   | CCT    | Code                                 | Flux (lm) | 70 CRI Typical | 80 CRI Typical       | 80 CRI Minimum       | 85 CRI Minimum       | 90 CRI Minimum       |
| ANSI Warm White (2700 K - 3750 K)     |        |                                      |           |                |                      |                      |                      |                      |
| E8                                    | 2700 K | Q5                                   | 107       |                | XPGWHT-L1-0000-00DE8 |                      |                      |                      |
|                                       |        | Q4                                   | 100       |                | XPGWHT-L1-0000-00CE8 | XPGWHT-H1-0000-00CE8 |                      |                      |
|                                       |        | Q3                                   | 93.9      |                | XPGWHT-L1-0000-00BE8 | XPGWHT-H1-0000-00BE8 |                      |                      |
|                                       |        | Q2                                   | 87.4      |                | XPGWHT-L1-0000-00AE8 | XPGWHT-H1-0000-00AE8 | XPGWHT-P1-0000-00AE8 |                      |
|                                       |        | P4                                   | 80.6      |                |                      |                      | XPGWHT-P1-0000-009E8 | XPGWHT-U1-0000-009E8 |
|                                       |        | P3                                   | 73.9      |                |                      |                      | XPGWHT-P1-0000-008E8 | XPGWHT-U1-0000-008E8 |
|                                       |        | P2                                   | 67.2      |                |                      |                      | XPGWHT-P1-0000-007E8 | XPGWHT-U1-0000-007E8 |
| Z8                                    | 2700 K | Q4                                   | 100       |                | XPGWHT-L1-0000-00CZ8 | XPGWHT-H1-0000-00CZ8 |                      |                      |
|                                       |        | Q3                                   | 93.9      |                | XPGWHT-L1-0000-00BZ8 | XPGWHT-H1-0000-00BZ8 |                      |                      |
|                                       |        | Q2                                   | 87.4      |                | XPGWHT-L1-0000-00AZ8 | XPGWHT-H1-0000-00AZ8 |                      |                      |
|                                       |        | P4                                   | 80.6      |                |                      |                      | XPGWHT-P1-0000-009Z8 |                      |
|                                       |        | P3                                   | 73.9      |                |                      |                      | XPGWHT-P1-0000-008Z8 | XPGWHT-U1-0000-008Z8 |
|                                       |        | P2                                   | 67.2      |                |                      |                      | XPGWHT-P1-0000-007Z8 | XPGWHT-U1-0000-007Z8 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-G2 ANSI COOL WHITE,  $T_j = 85\text{ }^\circ\text{C}$ )**

| XLamp XP-G2 Standard Order Codes - White |        |                                      |           |                      |
|--|--------|--------------------------------------|-----------|----------------------|
| Chromaticity                             |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |
| Kit                                      | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       |
| ANSI Cool White (5000 K – 8300 K)        |        |                                      |           |                      |
| 51                                       | 6200 K | R5                                   | 139       | XPGBWT-L1-0000-00H51 |
|  |        | R4                                   | 130       | XPGBWT-L1-0000-00G51 |
|  |        | R3                                   | 122       | XPGBWT-L1-0000-00F51 |
| 53                                       | 6000 K | R5                                   | 139       | XPGBWT-L1-0000-00H53 |
|  |        | R4                                   | 130       | XPGBWT-L1-0000-00G53 |
|  |        | R3                                   | 122       | XPGBWT-L1-0000-00F53 |
| 50                                       | 6200 K | R5                                   | 139       | XPGBWT-L1-0000-00H50 |
|  |        | R4                                   | 130       | XPGBWT-L1-0000-00G50 |
|  |        | R3                                   | 122       | XPGBWT-L1-0000-00F50 |
| E1                                       | 6500 K | R5                                   | 139       | XPGBWT-L1-0000-00HE1 |
|  |        | R4                                   | 130       | XPGBWT-L1-0000-00GE1 |
|  |        | R3                                   | 122       | XPGBWT-L1-0000-00FE1 |
| E2                                       | 5700 K | R5                                   | 139       | XPGBWT-L1-0000-00HE2 |
|  |        | R4                                   | 130       | XPGBWT-L1-0000-00GE2 |
|  |        | R3                                   | 122       | XPGBWT-L1-0000-00FE2 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-G2 NEUTRAL WHITE, OUTDOOR WHITE, T<sub>j</sub> = 85 °C)**

| XLamp XP-G2 Standard Kit Codes - White |        |                                      |           |                      |                      |                |
|--|--------|--------------------------------------|-----------|----------------------|----------------------|----------------|
| Chromaticity                           |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                |
| Kit                                    | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 75 CRI Typical       | 80 CRI Minimum |
| ANSI Neutral White (3700 K – 5000 K)   |        |                                      |           |                      |                      |                |
| E3                                     | 5000 K | R5                                   | 139       | XPGBWT-01-0000-00HE3 |                      |                |
|  |        | R4                                   | 130       | XPGBWT-01-0000-00GE3 |                      |                |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FE3 | XPGBWT-L1-0000-00FE3 |                |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EE3 | XPGBWT-L1-0000-00EE3 |                |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DE3 |                |
| C1                                     | 5000 K | R5                                   | 139       | XPGBWT-01-0000-00HC1 |                      |                |
|  |        | R4                                   | 130       | XPGBWT-01-0000-00GC1 |                      |                |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FC1 |                      |                |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EC1 |                      |                |
| F4                                     | 4750 K | R5                                   | 139       | XPGBWT-01-0000-00HF4 |                      |                |
|  |        | R4                                   | 130       | XPGBWT-01-0000-00GF4 |                      |                |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FF4 | XPGBWT-L1-0000-00FF4 |                |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EF4 | XPGBWT-L1-0000-00EF4 |                |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DF4 |                |
| D1                                     | 4750 K | R5                                   | 139       | XPGBWT-01-0000-00HD1 |                      |                |
|  |        | R4                                   | 130       | XPGBWT-01-0000-00GD1 |                      |                |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FD1 |                      |                |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00ED1 |                      |                |
| E4                                     | 4500 K | R5                                   | 139       | XPGBWT-01-0000-00HE4 |                      |                |
|  |        | R4                                   | 130       | XPGBWT-01-0000-00GE4 |                      |                |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FE4 | XPGBWT-L1-0000-00FE4 |                |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EE4 | XPGBWT-L1-0000-00EE4 |                |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DE4 |                |
| D2                                     | 4500 K | R5                                   | 139       | XPGBWT-01-0000-00HD2 |                      |                |
|  |        | R4                                   | 130       | XPGBWT-01-0000-00GD2 |                      |                |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FD2 |                      |                |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00ED2 |                      |                |
| C2                                     | 4500 K | R5                                   | 139       | XPGBWT-01-0000-00HC2 |                      |                |
|  |        | R4                                   | 130       | XPGBWT-01-0000-00GC2 |                      |                |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FC2 |                      |                |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EC2 |                      |                |
| C3                                     | 4300 K | R4                                   | 130       | XPGBWT-01-0000-00GC3 |                      |                |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FC3 |                      |                |
| D3                                     | 4300 K | R4                                   | 130       | XPGBWT-01-0000-00GD3 |                      |                |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FD3 |                      |                |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00ED3 |                      |                |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-G2 NEUTRAL WHITE, OUTDOOR WHITE, T<sub>j</sub> = 85 °C, CONTINUED)**

| XLamp XP-G2 Standard Kit Codes - White |        |                                      |           |                      |                      |                      |
|--|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|
| Chromaticity                           |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |
| Kit                                    | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 75 CRI Typical       | 80 CRI Minimum       |
| ANSI Neutral White (3700 K – 5000 K)   |        |                                      |           |                      |                      |                      |
| F5                                     | 4250 K | R4                                   | 130       | XPGBWT-01-0000-00GF5 |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FF5 | XPGBWT-L1-0000-00FF5 |                      |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EF5 | XPGBWT-L1-0000-00EF5 |                      |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DF5 |                      |
| C4                                     | 4100 K | R4                                   | 130       | XPGBWT-01-0000-00GC4 |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FC4 |                      |                      |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EC4 |                      |                      |
| D4                                     | 4000 K | R4                                   | 130       | XPGBWT-01-0000-00GD4 |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FD4 |                      |                      |
|  |        | R2                                   | 1114      | XPGBWT-01-0000-00ED4 |                      |                      |
| E5                                     | 4000 K | R4                                   | 130       | XPGBWT-01-0000-00GE5 |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FE5 | XPGBWT-L1-0000-00FE5 |                      |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EE5 | XPGBWT-L1-0000-00EE5 | XPGBWT-H1-0000-00EE5 |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DE5 | XPGBWT-H1-0000-00DE5 |
| Z5                                     | 4000 K | R2                                   | 114       |                      | XPGBWT-L1-0000-00EZ5 | XPGBWT-H1-0000-00EZ5 |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DZ5 | XPGBWT-H1-0000-00DZ5 |
| C5                                     | 3800 K | R4                                   | 130       | XPGBWT-01-0000-00GC5 |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FC5 |                      |                      |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EC5 |                      |                      |
|  |        | Q5                                   | 107       | XPGBWT-01-0000-00DC5 |                      |                      |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-G2 WARM WHITE  $T_j = 85\text{ }^\circ\text{C}$ )**

| XLamp XP-G2 Standard Kit Codes - White |        |                                      |           |                      |                      |                      |                      |                      |
|--|--------|--------------------------------------|-----------|----------------------|----------------------|----------------------|----------------------|----------------------|
| Chromaticity                           |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes          |                      |                      |                      |                      |
| Kit                                    | CCT    | Code                                 | Flux (lm) | 70 CRI Typical       | 80 CRI Typical       | 80 CRI Minimum       | 85 CRI Minimum       | 90 CRI Minimum       |
| ANSI Warm White (2700 K - 3750 K)      |        |                                      |           |                      |                      |                      |                      |                      |
| F6                                     | 3750 K | R4                                   | 130       | XPGBWT-01-0000-00GF6 |                      |                      |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FF6 | XPGBWT-L1-0000-00FF6 |                      |                      |                      |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EF6 | XPGBWT-L1-0000-00EF6 | XPGBWT-H1-0000-00EF6 |                      |                      |
|  |        | Q5                                   | 107       | XPGBWT-01-0000-00DF6 | XPGBWT-L1-0000-00DF6 | XPGBWT-H1-0000-00DF6 |                      |                      |
| D5                                     | 3700 K | R4                                   | 130       | XPGBWT-01-0000-00GD5 |                      |                      |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FD5 |                      |                      |                      |                      |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00ED5 |                      |                      |                      |                      |
|  |        | Q5                                   | 107       | XPGBWT-01-0000-00DD5 |                      |                      |                      |                      |
| C6                                     | 3600 K | R4                                   | 130       | XPGBWT-01-0000-00GC6 |                      |                      |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FC6 |                      |                      |                      |                      |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EC6 |                      |                      |                      |                      |
|  |        | Q5                                   | 107       | XPGBWT-01-0000-00DC6 |                      |                      |                      |                      |
| E6                                     | 3500 K | R4                                   | 130       | XPGBWT-01-0000-00GE6 |                      |                      |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FE6 | XPGBWT-L1-0000-00FE6 |                      |                      |                      |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EE6 | XPGBWT-L1-0000-00EE6 | XPGBWT-H1-0000-00EE6 |                      |                      |
|  |        | Q5                                   | 107       | XPGBWT-01-0000-00DE6 | XPGBWT-L1-0000-00DE6 | XPGBWT-H1-0000-00DE6 |                      |                      |
| Z6                                     | 3500 K | R2                                   | 114       |                      | XPGBWT-L1-0000-00EZ6 | XPGBWT-H1-0000-00EZ6 |                      |                      |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DZ6 | XPGBWT-H1-0000-00DZ6 |                      |                      |
| F7                                     | 3250 K | R3                                   | 122       |                      | XPGBWT-L1-0000-00FF7 |                      |                      |                      |
|  |        | R2                                   | 114       |                      | XPGBWT-L1-0000-00EF7 | XPGBWT-H1-0000-00EF7 |                      |                      |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DF7 | XPGBWT-H1-0000-00DF7 |                      |                      |
|  |        | Q4                                   | 100       |                      |                      | XPGBWT-H1-0000-00CF7 |                      |                      |
| E7                                     | 3000 K | R4                                   | 130       | XPGBWT-01-0000-00GE7 | XPGBWT-L1-0000-00GE7 |                      |                      |                      |
|  |        | R3                                   | 122       | XPGBWT-01-0000-00FE7 | XPGBWT-L1-0000-00FE7 | XPGBWT-H1-0000-00FE7 |                      |                      |
|  |        | R2                                   | 114       | XPGBWT-01-0000-00EE7 | XPGBWT-L1-0000-00EE7 | XPGBWT-H1-0000-00EE7 |                      |                      |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DE7 | XPGBWT-H1-0000-00DE7 |                      |                      |
|  |        | Q4                                   | 100       |                      | XPGBWT-L1-0000-00CE7 | XPGBWT-H1-0000-00CE7 |                      |                      |
|  |        | Q3                                   | 93.9      |                      |                      |                      | XPGBWT-P1-0000-00BE7 |                      |
|  |        | Q2                                   | 87.4      |                      |                      |                      | XPGBWT-P1-0000-00AE7 | XPGBWT-U1-0000-00AE7 |
|  |        | P4                                   | 80.6      |                      |                      |                      | XPGBWT-P1-0000-009E7 | XPGBWT-U1-0000-009E7 |
|  |        | P3                                   | 73.9      |                      |                      |                      | XPGBWT-P1-0000-008E7 | XPGBWT-U1-0000-008E7 |
| Z7                                     | 3000 K | R3                                   | 122       |                      | XPGBWT-L1-0000-00FZ7 | XPGBWT-H1-0000-00FZ7 |                      |                      |
|  |        | R2                                   | 114       |                      | XPGBWT-L1-0000-00EZ7 | XPGBWT-H1-0000-00EZ7 |                      |                      |
|  |        | Q5                                   | 107       |                      | XPGBWT-L1-0000-00DZ7 | XPGBWT-H1-0000-00DZ7 |                      |                      |
|  |        | Q4                                   | 100       |                      | XPGBWT-L1-0000-00CZ7 | XPGBWT-H1-0000-00CZ7 |                      |                      |
|  |        | Q3                                   | 93.9      |                      |                      |                      |                      |                      |
|  |        | Q2                                   | 87.4      |                      |                      |                      | XPGBWT-P1-0000-00AZ7 |                      |
|  |        | P4                                   | 80.6      |                      |                      |                      | XPGBWT-P1-0000-009Z7 | XPGBWT-U1-0000-009Z7 |
|  |        | P3                                   | 73.9      |                      |                      |                      | XPGBWT-P1-0000-008Z7 | XPGBWT-U1-0000-008Z7 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.

**STANDARD ORDER CODES AND BINS (XP-G2 WARM WHITE T<sub>j</sub> = 85 °C, CONTINUED)**

| XLamp XP-G2 Standard Kit Codes - White |        |                                      |           |                |                      |                      |                      |                      |
|--|--------|--------------------------------------|-----------|----------------|----------------------|----------------------|----------------------|----------------------|
| Chromaticity                           |        | Minimum Luminous Flux (lm) @ 350 mA* |           | Order Codes    |                      |                      |                      |                      |
| Kit                                    | CCT    | Code                                 | Flux (lm) | 70 CRI Typical | 80 CRI Typical       | 80 CRI Minimum       | 85 CRI Minimum       | 90 CRI Minimum       |
| ANSI Warm White (2700 K - 3750 K)      |        |                                      |           |                |                      |                      |                      |                      |
| F8                                     | 2850 K | R2                                   | 114       |                | XPGBWT-L1-0000-00EF8 | XPGBWT-H1-0000-00EF8 |                      |                      |
|  |        | Q5                                   | 107       |                | XPGBWT-L1-0000-00DF8 | XPGBWT-H1-0000-00DF8 |                      |                      |
|  |        | Q4                                   | 100       |                | XPGBWT-L1-0000-00CF8 | XPGBWT-H1-0000-00CF8 |                      |                      |
|  |        | Q3                                   | 93.9      |                | XPGBWT-L1-0000-00BF8 | XPGBWT-H1-0000-00BF8 |                      |                      |
|  |        | Q2                                   | 87.4      |                |                      |                      | XPGBWT-P1-0000-00AF8 |                      |
|  |        | P4                                   | 80.6      |                |                      |                      | XPGBWT-P1-0000-009F8 | XPGBWT-U1-0000-009F8 |
|  |        | P3                                   | 73.9      |                |                      |                      | XPGBWT-P1-0000-008F8 | XPGBWT-U1-0000-008F8 |
|  |        | P2                                   | 67.2      |                |                      |                      | XPGBWT-P1-0000-007F8 | XPGBWT-U1-0000-007F8 |
| E8                                     | 2700 K | R2                                   | 114       |                | XPGBWT-L1-0000-00EE8 | XPGBWT-H1-0000-00EE8 |                      |                      |
|  |        | Q5                                   | 107       |                | XPGBWT-L1-0000-00DE8 | XPGBWT-H1-0000-00DE8 |                      |                      |
|  |        | Q4                                   | 100       |                | XPGBWT-L1-0000-00CE8 | XPGBWT-H1-0000-00CE8 |                      |                      |
|  |        | Q3                                   | 93.9      |                | XPGBWT-L1-0000-00BE8 | XPGBWT-H1-0000-00BE8 |                      |                      |
|  |        | Q2                                   | 87.4      |                |                      |                      | XPGBWT-P1-0000-00AE8 |                      |
|  |        | P4                                   | 80.6      |                |                      |                      | XPGBWT-P1-0000-009E8 | XPGBWT-U1-0000-009E8 |
|  |        | P3                                   | 73.9      |                |                      |                      | XPGBWT-P1-0000-008E8 | XPGBWT-U1-0000-008E8 |
|  |        | P2                                   | 67.2      |                |                      |                      | XPGBWT-P1-0000-007E8 | XPGBWT-U1-0000-007E8 |
| Z8                                     | 2700 K | Q5                                   | 107       |                | XPGBWT-L1-0000-00DZ8 | XPGBWT-H1-0000-00DZ8 |                      |                      |
|  |        | Q4                                   | 100       |                | XPGBWT-L1-0000-00CZ8 | XPGBWT-H1-0000-00CZ8 |                      |                      |
|  |        | Q3                                   | 93.9      |                | XPGBWT-L1-0000-00BZ8 | XPGBWT-H1-0000-00BZ8 |                      |                      |
|  |        | Q2                                   | 87.4      |                |                      |                      |                      |                      |
|  |        | P4                                   | 80.6      |                |                      |                      | XPGBWT-P1-0000-009Z8 |                      |
|  |        | P3                                   | 73.9      |                |                      |                      | XPGBWT-P1-0000-008Z8 | XPGBWT-U1-0000-008Z8 |
|  |        | P2                                   | 67.2      |                |                      |                      | XPGBWT-P1-0000-007Z8 | XPGBWT-U1-0000-007Z8 |

\* Cree XLamp XP Family order codes specify only a minimum flux bin and not a maximum. Cree may ship reels in flux bins higher than the minimum specified by the order code without advance notice. Shipments will always adhere to the chromaticity or DWL bin restrictions specified by the order code.