

# Primary lithium battery system

## BA 5372

6 V Primary lithium manganese dioxide (Li-MnO<sub>2</sub>) battery

The battery consists of 2 LM 17130 cells connected in series, arranged in a cylindrical construction with nickel plated button terminals at either end.

### Key Features

- No passivation delay effect
- Low self-discharge rate
- Long shelf life
- Nickel plated button terminals
- Mylar sleeve
- Non-restricted to Class 9

### Typical applications

- Memory hold
- AN/GRC-210
- AN/PRC-119
- AN/PSQ-4
- PATRIOT
- Others



### Electrical characteristics

Nominal OCV	6.5 V
Operating voltage	5.6 V
Cut-off voltage	4 V
Maximum constant current	300 mA
Maximum pulse current	400 mA
Typical capacity at 20 mA to 4V cut-off	
at 70°F(21°C)	560 mA at 4.5 mA at 4V cut-off
at -4°F(-20°C)	450 mA at 4.5 mA at 4V cut-off
Operating temperature	-29°C to +71°C / -20°F to +160°F
Storage temperature	
Recommended maximum	+35°C / +95°F
Possible	-40°C to + 71°C / -40°F to +160°F

### Physical characteristics

	Metric	Imperial
Maximum weight	20 g	0.7 oz
Weight of Li metal content	0.4 g	—
Diameter (max) body	16.8mm	0.66 in
Length (max)	33 mm	1.3 in



### References

Reference specifications	MIL-PRF-32271 or Saft standard specification
NATO Stock Number	6135-01-214-6441



**SAFT**

# BA 5372





## Storage

- Store in dry area not >30°C

## Handling

- Do not disassemble
- Do not short circuit
- Do not charge
- Do not incinerate



## Saft

12, rue Sadi Carnot  
93170 Bagnole France  
Tel.: +33 (0)1 49 93 19 18  
Fax: +33 (0)1 49 93 19 69  
www.saftbatteries.com

## Saft America, Inc.

313 Crescent St.  
Valdese, NC 28690 - USA  
Tel.: +1 (828) 874 4111  
Fax: +1 (828) 874 3981  
www.saftbatteries.com

Doc N° 32043-2-0713  
Edition: July 2013  
Information in this document is subject to change  
without notice and becomes contractual only after  
written confirmation by Saft.  
Published by the Communications Department  
Photo credit: Saft