



Mighty Vue Magnifying Lamp-LED ESD Safe • Product # 26505-ESL



Overview : Mighty Vue magnifying lamp with 36 high powered LEDs(18 per side), 3 Diopter lens and 32" spring balanced arm. ESD safe housing

The Mighty Vue features a large 7" x 6", 3-diopter (1.75x), distortion free Crystal Clear lens mounted in a high tech mar-resistant engineered ESD plastic housing with dual light sources. The large, rectangular viewing area enables comfortable viewing with both eyes and provides shadow-free magnification with light coming from both sides. The housing is mounted to an internal spring balanced arm with a 32" reach that will set in any position. Unit operates at 115 VAC and comes complete with mounting camp and a 5-foot power cord. 1 year warranty (excludes bulb).

- Durable ESD safe mar-resistant plastic housing
- Large 7"x 6" 1.75x (3 diopter) lens
- 36 high powered energy efficient SMD LEDs provide shadow-free illumination
- 32" spring balanced arm stays put in any position
- Unit operates at 115 VAC
- Heavy-duty metal mounting clamp with 3.5" opening

Mighty Vue Magnifying Lamp - Black, LED, ESD Safe, 3-Diopter

Magnification	1.75X (3-Diopter)
Lens Diameter	7 x 6in
Adjustable Arm Length	32in
Color	Black ESD Safe
Lighting	36 SMD LEDs (18 per side)
Magnifying Lamp Accessories	26501-SLA, Swing-Away Lens - 5 Diopter (2.25x)
Weight	10 lb