

STA-200D - Amplifier



Digital stereo PA amplifier, with 5 switchable line inputs.

- Class D concept
- Silent operation due to fanless cooling concept
- High power reserves due to generously dimensioned toroidal core transformer
- High-efficiency power amplifiers
- 3.5 mm stereo connection with adjustable sensitivity on the front panel
- 2 level controls
- Protected against short circuit, overvoltage and overtemperature
- LEDs for indicating power, protect, overload (clip) and overheating
- Extra slim and robust design, 1 RS

Technical data

Output power	:
RMS power	:
4 Ohm	: 2 x 125 W _{RMS}
8 Ohm	: 2 x 75 W _{RMS}
8 Ohm bridge operation	: -
Max. power	: 300 W _{MAX}
General information	:
Inputs	: 1 V/23 k Ohm (RCA), 90 mV-1 V (jack)
Frequency range	: 20-20,000 Hz
S/N ratio	: ? 100 dB, A-weighted
Crosstalk attenuation	: ? 56 dB
THD	: < 0.05 %
Power supply	: 230 V~/50 Hz/350 VA
Admiss. ambient temp.	: 0-40 °C
Dimensions	: 483x44x268 mm, 1 RS
Weight	: 4.7 kg
Connections	: 1 x 3.5 mm stereo jack 4 x RCA L/R 1 x SPEAKER L/R 1 x spring-load. speaker term. L/R