

RoHS  
Compliant



## Benefits:

- Pre-perforated for rapid removal from backing sheet
- Print using ordinary standard office laser printer and the pro-Power software
- Print up to 54 labels in 15 seconds

## Description:

This label sheet offers by far the easiest and fastest way to produce tie-on cable labels. No special equipment needed. Use a standard office laser printer. Print up to 54 labels in just 15 seconds, the time it takes for the sheet to run through your laser printer. And removing the labels is easy too, just fold backwards and forwards along the perforation lines.

The free pro-Power software is downloadable from:

<http://www.silverfox.co.uk/store/software-solutions/pro-power/pro-power-software.aspx>

TIP: If you only need a few labels, prior to printing use the variable start position in the pro-Power software and print the labels at the bottom of the sheet to keep the leading edge of the sheet intact for future runs

Recommended printing via straight printer path

## Technical Data

Material	175 micron polyester
Printer Type	Laser printers only

## Product Testing

Test	Method
Moisture Resistance	MIL-STD-202G Method 106G
Low Temperature 72 hours @ -40°C	MIL-STD-810F Method 502.4
High Temperature 2000 hours @ 70°C to 100°C*	MIL-STD-202G Method 108A
Hydrogen Sulphide	H <sub>2</sub> S Sour Gas Exposure (2% H <sub>2</sub> S)
UV Weathering 500 hours**	ISO 4982 Part 3 Method A Cycle 1
Salt Mist Spray	IEC60068-2-52 Test Kb Salt Mist (Cyclic)

### Note:

\* Samples were subjected to 500 hours @ 70°C, followed by 500 hours @ 85°C followed by 1,000 hours @ 100°C.

\*\*Limited external applications generally away from direct sunlight but may be suitable in control boxes etc. Labels generally for use internally such as: data centres, control rooms, sub-stations, power stations etc. Other applications may include banks, hotels airports etc.


## How to Apply Labels

STEP 1




After printing, fold the label along the perforations

STEP 2



Firmly crease along the fold

STEP 3



Tear along the crease to remove the label

## Specification Table

Label Dimension (mm)	Printable Area (mm)	Sheet Size	Labels per Sheet	Sheets per Pack	Colour	Part Number	
62 × 14	51 × 13	A4	54	10	Yellow	2075092	
						White	2075091
88 × 16	77 × 15		30		Yellow	2075094	
88 × 22	77 × 21		22		Yellow	2075096	

## Part Number Table

Description	Part Number
Label, Wht, 62 × 14mm, 54/Sheet, PK10	2075091
Label, Yel, 62 × 14mm, 54/Sheet, PK10	2075092
Label, Yel, 88 × 16mm, 30/Sheet, PK10	2075094
Label, Yel, 88 × 22mm, 22/Sheet, PK10	2075096

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. pro-POWER is the registered trademark of the Group. © Premier Farnell plc 2012.