

## Limit Comparator Operation Instructions



Made in the  
United States of America



Figure 1. EMIT 50424 Limit Comparator

### Description

Frequency of recalibration should be based on the critical nature of those ESD sensitive items handled and the risk of failure for the ESD protective equipment and materials. In general, EMIT recommends that calibration be performed annually.

Use the EMIT 50424 Limit Comparator to perform periodic testing (once every 6-12 months) of the EMIT SmartLog V4™, SmartLog V5™ and Dual Independent Testers. It may also be used to verify the calibration of the Desco and Vermason Combo Tester X3. The Limit Comparator can be used on the shop floor within a few minutes virtually eliminating downtime, verifying that the tester is operating within tolerances.

The EMIT 50424 Limit Comparator is to be used with the following items:

Brand	Item	Description
EMIT	50404	Dual Independent Footwear Tester, North America
EMIT	50412	Dual Independent Footwear Tester, No Power Adapter
EMIT	50407	Dual Independent Footwear and Wrist Strap Tester, North America
EMIT	50413	Dual Independent Footwear and Wrist Strap Tester, No Power Adapter
EMIT	50562	Dual Independent Footwear and Wrist Strap Tester, Europe
EMIT	50741	SmartLog V4™, North America
EMIT	50743	SmartLog V4™, Asia
EMIT	50747	SmartLog V4™, Europe
EMIT	50751	SmartLog V4™, Europe, with 10mm Adapter
EMIT	50766	SmartLog V5™, North America
EMIT	50767	SmartLog V5™, Asia
EMIT	50768	SmartLog V5™, Europe
EMIT	50769	SmartLog V5™, Europe, with 10mm Adapter
EMIT	50772	SmartLog V5™ with Turnstile, 220VAC
EMIT	50773	SmartLog V5™ with Turnstile, 120VAC
EMIT	50774	Combo Tester X3 with Turnstile, 120VAC
EMIT	50775	Combo Tester X3 with Turnstile, 220VAC
Desco	19278	Combo Tester X3
Desco	19279	Combo Tester X3 with Stand
Vermason	222550	Combo Tester X3
Vermason	222551	Combo Tester X3 with Stand
Vermason	222553	Combo Tester X3 with 10mm Adapter
Vermason	222554	Combo Tester X3 with Stand and 10mm Adapter

NOTE: The 50424 Limit Comparator also calibrates the following discontinued items:

Desco	19276, 19277
EMIT	50760, 50761, 50762, 50763

## Packaging

- 1 Limit Comparator
- 2 Test Leads with Banana Plug Terminals
- 1 RJ11 Foot Plate Cable
- 1 Certificate of Calibration

## Tester Configuration

The resistance limits for footwear and wrist strap tests are controlled by the DIP switches located on the sides of the tester. Use the following tables for the DIP switch settings and their corresponding test values.



Figure 2. Locating the DIP switch on the SmartLog V4™ Tester, Dual Independent Tester and Combo Tester X3



Figure 3. Locating the DIP switch on the SmartLog V5™

### EMIT SMARTLOG V4™, DUAL INDEPENDENT TESTER

#### FOOTWEAR RESISTANCE

DIP switches 1 and 2 control the HIGH test limit.

Switch 1	Switch 2	HIGH Limit Resistance
ON	ON	10 Megohms (1 x 10 <sup>7</sup> )
OFF	OFF	35 Megohms (3.5 x 10 <sup>7</sup> )
ON	OFF	100 Megohms (1 x 10 <sup>8</sup> )
OFF	ON	1 Gigohm (1 X 10 <sup>9</sup> )

DIP switches 3 and 4 control the LOW test limit.

Switch 3	Switch 4	LOW Limit Resistance
ON	OFF	100 Kilohms (1 x 10 <sup>5</sup> )
OFF	ON	1 Megohm (1 x 10 <sup>6</sup> )

default setting

NOTE: At 1 Gigohm high limit resistance, a dirty foot plate could result in a false pass. Be sure to keep the foot plate clean particularly when using this setting. This setting is not suitable for relative humidity greater than 50%.

#### WRIST STRAP RESISTANCE

DIP switches 5 and 6 control the HIGH test limit.

Switch 5	Switch 6	HIGH Limit Resistance
OFF	OFF	wrist strap test disabled
ON	ON	10 Megohms (1 x 10 <sup>7</sup> )
ON	OFF	35 Megohms (3.5 x 10 <sup>7</sup> )

default USA setting

default Europe & Asia setting

DIP switch 5 must be ON (default setting) for the wrist strap test to be active. The wrist strap test will be disabled if DIP switch 5 is set to OFF.

The LOW limit for the wrist strap test is set to 1 Megohm and cannot be modified by the user.

### EMIT SMARTLOG V5™

(ITEMS 50766 - 50769, 50772, 50773)

### DESCO AND VERMASON COMBO TESTER X3

#### FOOTWEAR RESISTANCE

DIP switches 1 and 2 control the HIGH test limit.

Switch 1	Switch 2	HIGH Limit Resistance
ON	ON	10 Megohms (1 x 10 <sup>7</sup> )
OFF	OFF	35 Megohms (3.5 x 10 <sup>7</sup> )
ON	OFF	100 Megohms (1 x 10 <sup>8</sup> )
OFF	ON	1 Gigohm (1 x 10 <sup>9</sup> )

DIP switches 3 and 4 control the LOW test limit.

Switch 3	Switch 4	LOW Limit Resistance
ON	OFF	100 Kilohms (1 x 10 <sup>5</sup> )
OFF	ON	750 Kilohms (7.5 x 10 <sup>5</sup> )

default setting

NOTE: At 1 Gigohm high limit resistance, a dirty foot plate could result in a false pass. Be sure to keep the foot plate clean particularly when using this setting. This setting is not suitable for relative humidity greater than 50%.

## WRIST STRAP RESISTANCE

DIP switches 5 and 6 control the HIGH test limit.

Switch 5	Switch 6	HIGH Limit Resistance
OFF	OFF	wrist strap test disabled
ON	ON	10 Megohms ( $1 \times 10^7$ )
ON	OFF	35 Megohms ( $3.5 \times 10^7$ )

default setting

DIP switch 5 must be ON (default setting) for the wrist strap test to be active. The wrist strap test will be disabled if DIP switch 5 is set to OFF.

The LOW limit for the wrist strap test is set to 750 Kilohms and cannot be modified by the user.

## Operation

### EMIT SMARTLOG V4™ AND DUAL INDEPENDENT TESTER

#### Testing the Wrist Strap Circuit

1. Plug the two included test leads into each yellow banana jack located at the top of the Limit Comparator.
2. Connect one of the test leads from the Limit Comparator to the "SINGLE-WIRE" jack located on the face of the tester. Connect the other lead from the Limit Comparator to the ground jack located on the bottom of the tester.
3. Select "1M LOW" with the Limit Comparator's rotary switch.
4. Touch and hold the test plate of the tester until the test is completed. The tester should indicate a wrist strap FAIL LOW condition.
5. Select "1M PASS" on the Limit Comparator and repeat the test. The tester should indicate a wrist strap PASS condition.
6. Select either the "10M PASS" or "35M PASS" setting, whichever one is appropriate, on the Limit Comparator and repeat the test. The tester should indicate a wrist strap PASS condition.
7. Select either the "10M HIGH" or "35M HIGH" setting, whichever one is appropriate, on the Limit Comparator and repeat the test. The tester should indicate a wrist strap FAIL HIGH condition.

#### Testing the Footwear Circuit

1. Insert the Limit Comparator's stereo plug into the jack labeled "FOOT PLATE" on the bottom of the tester.
2. Select the appropriate FAIL LOW setting on the Limit Comparator.
3. Touch and hold the test plate of the tester until the test is completed. The tester should indicate a FAIL LOW condition for both feet.

4. Select the appropriate PASS LOW setting on the Limit Comparator and repeat the test. The tester should indicate a PASS condition for both feet.
5. Select the appropriate PASS HIGH setting on the Limit Comparator and repeat the test. The tester should indicate a PASS condition for both feet.
6. Select the appropriate FAIL HIGH setting on the Limit Comparator and repeat the test. The tester should indicate a FAIL HIGH condition for both feet.

### EMIT SMARTLOG V5™ (ITEMS 50766 - 50769, 50772, 50773)

#### Testing the Wrist Strap Circuit

1. Plug the two included test leads into each yellow banana jack located at the top of the Limit Comparator.
2. Connect one of the test leads from the Limit Comparator to the "SINGLE WIRE" jack located on the face of the tester. Connect the other lead from the Limit Comparator to the ground jack located on the right-hand side of the SmartLog V5.
3. Select "750K LOW" with the Limit Comparator's rotary switch.
4. Touch and hold the test plate of the tester until the test is completed. The tester should indicate a wrist strap FAIL LOW condition.
5. Select "750K PASS" on the Limit Comparator and repeat the test. The tester should indicate a wrist strap PASS condition.
6. Select either the "10M PASS" or "35M PASS" setting, whichever one is appropriate, on the Limit Comparator and repeat the test. The tester should indicate a wrist strap PASS condition.
7. Select either the "10M HIGH" or "35M HIGH" setting, whichever one is appropriate, on the Limit Comparator and repeat the test. The tester should indicate a wrist strap FAIL HIGH condition.

#### Testing the Footwear Circuit

1. Plug the included foot plate cable into the RJ11 jack located at the top of the Limit Comparator.
2. Insert the opposite end of the foot plate cable into the foot plate jack located on the right-hand side of the SmartLog V5.
3. Select the appropriate FAIL LOW setting on the Limit Comparator.
4. Toggle the Limit Comparator's switch to LEFT FOOT. Touch and hold the test plate of the tester until the test is completed. The tester should indicate a FAIL LOW condition for the left foot. Toggle the switch to RIGHT FOOT and retest. The tester should indicate a FAIL LOW condition for the right foot.

5. Select the appropriate PASS LOW setting on the Limit Comparator and repeat the test for the LEFT FOOT and RIGHT FOOT. The tester should indicate a PASS condition for both feet.
6. Select the appropriate PASS HIGH setting on the Limit Comparator and repeat the test for the LEFT FOOT and RIGHT FOOT. The tester should indicate a PASS condition for both feet.
7. Select the appropriate FAIL HIGH setting on the Limit Comparator and repeat the test for the LEFT FOOT and RIGHT FOOT. The tester should indicate a FAIL HIGH condition for both feet.

**EMIT SMARTLOG V5™  
(DISC. ITEMS 50760 - 50763)**

**Testing the Wrist Strap Circuit**

1. Plug the two included test leads into each yellow banana jack located at the top of the Limit Comparator.
2. Connect one of the test leads from the Limit Comparator to the "SINGLE WIRE" jack located on the face of the tester. Connect the other lead from the Limit Comparator to the ground jack located on the right-hand side of the SmartLog V5.
3. Select "1M LOW" with the Limit Comparator's rotary switch.
4. Touch and hold the test plate of the tester until the test is completed. The tester should indicate a wrist strap FAIL LOW condition.
5. Select "1M PASS" on the Limit Comparator and repeat the test. The tester should indicate a wrist strap PASS condition.
6. Select either the "10M PASS" or "35M PASS" setting, whichever one is appropriate, on the Limit Comparator and repeat the test. The tester should indicate a wrist strap PASS condition.
7. Select either the "10M HIGH" or "35M HIGH" setting, whichever one is appropriate, on the Limit Comparator and repeat the test. The tester should indicate a wrist strap FAIL HIGH condition.

**Testing the Footwear Circuit**

1. Plug the included foot plate cable into the RJ11 jack located at the top of the Limit Comparator.
2. Insert the opposite end of the foot plate cable into the foot plate jack located on the right-hand side of the SmartLog V5.
3. Select the appropriate FAIL LOW setting on the Limit Comparator.
4. Toggle the Limit Comparator's switch to LEFT FOOT. Touch and hold the test plate of the tester until the test is completed. The tester should indicate a FAIL LOW condition for the left foot. Toggle the switch to RIGHT FOOT and retest. The tester should indicate a FAIL LOW condition for the right foot.

5. Select the appropriate PASS LOW setting on the Limit Comparator and repeat the test for the LEFT FOOT and RIGHT FOOT. The tester should indicate a PASS condition for both feet.
6. Select the appropriate PASS HIGH setting on the Limit Comparator and repeat the test for the LEFT FOOT and RIGHT FOOT. The tester should indicate a PASS condition for both feet.
7. Select the appropriate FAIL HIGH setting on the Limit Comparator and repeat the test for the LEFT FOOT and RIGHT FOOT. The tester should indicate a FAIL HIGH condition for both feet.

**DESCO AND VERMASON COMBO TESTER X3**

**Testing the Wrist Strap Circuit**

1. Plug the two included test leads into each yellow banana jack located at the top of the Limit Comparator.
2. Connect one of the test leads from the Limit Comparator to the "SINGLE-WIRE" jack located on the face of the tester. Connect the other lead from the Limit Comparator to the ground jack located on the bottom of the tester.
3. Select "750K LOW" with the Limit Comparator's rotary switch.
4. Touch and hold the test plate of the tester until the test is completed. The tester should indicate a wrist strap FAIL LOW condition.
5. Select "750K PASS" on the Limit Comparator and repeat the test. The tester should indicate a wrist strap PASS condition.
6. Select either the "10M PASS" or "35M PASS" setting, whichever one is appropriate, on the Limit Comparator and repeat the test. The tester should indicate a wrist strap PASS condition.
7. Select either the "10M HIGH" or "35M HIGH" setting, whichever one is appropriate, on the Limit Comparator and repeat the test. The tester should indicate a wrist strap FAIL HIGH condition.

**Testing the Footwear Circuit**

1. Insert the Limit Comparator's stereo plug into the jack labeled "FOOT PLATE" on the bottom of the tester.
2. Select the appropriate FAIL LOW setting on the Limit Comparator.
3. Touch and hold the test plate of the tester until the test is completed. The tester should indicate a FAIL LOW condition for both feet.
4. Select the appropriate PASS LOW setting on the Limit Comparator and repeat the test. The tester should indicate a PASS condition for both feet.
5. Select the appropriate PASS HIGH setting on the Limit Comparator and repeat the test. The tester should indicate a PASS condition for both feet.

6. Select the appropriate FAIL HIGH setting on the Limit Comparator and repeat the test. The tester should indicate a FAIL HIGH condition for both feet.

## Specifications

### Dimensions:

3.8" L x 2.4" W x .9" H  
(9.7 cm x 6.1 cm x 2.3 cm)

### Weight:

.2 lbs  
(.1 kg)

### Resistance Values:

Setting	Nominal Resistance	% Tolerance of Nominal Resistance
100K LOW	90K	±2%
100K PASS	110K	±2%
750K LOW	675K	±2%
750K PASS	825K	±2%
1M LOW	909K	±2%
1M PASS	1.10M	±2%
10M PASS	9.09M	±2%
10M HIGH	11.09M	±2%
35M PASS	31.09M	±2%
35M HIGH	37.89M	±2%
100M PASS	90.9M	±5%
100M HIGH	112.9M	±5%
1G PASS	812.9M	±5%
1G HIGH	1.213G	±5%

These resistance values may be verified using a digital voltmeter by setting it to read Ohms ( $\Omega$ ). Connect your voltmeter's test leads into each of the Limit Comparator's yellow banana jacks. If any value is out of specification, the Limit Comparator must be returned to the manufacturer for repair.

## Limited Warranty, Warranty Exclusions, Limit of Liability and RMA Request Instructions

See EMIT's Warranty -

<http://emit.descoindustries.com/Warranty.aspx>