

Product data sheet

Characteristics

8910DPA73V09

Definite Purpose Contactor Type DPA 75A, 3-Pole, 208...240VAC@60Hz - 220VAC@50Hz

Main

Commercial Status	Commercialised
Product or component type	Definite Purpose Contactor
[In] rated current	75 A
Motor power hp	40 hp 575 V AC 3 phases 40 hp 460 V AC 3 phases 15 hp 230 V AC 1 phase 25 hp 230 V AC 3 phases 5 hp 115 V AC 1 phase
Poles description	3P
Pole contact composition	3 NO
Control circuit voltage	220 V AC 50 Hz 208...240 V AC 60 Hz

Complementary

Product certifications	CE CSA UL listed
Locked rotor rated current	300 A 575 V AC 375 A 460 V AC 450 A 277 V AC
[Ue] rated operational voltage	600 V AC
Network number of phases	3 phases
Electrical connection	Quick connect terminals
Range of product	DPA

Ordering and shipping details

Category	21347 - 8910 DPA 7_(70 AMP)
Discount Schedule	CP1B
GTIN	00785901118374
Nbr. of units in pkg.	1
Package weight(Lbs)	3.66
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	CN

Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS	Will not be Compliant
REACH	Reference not containing SVHC above the threshold

Contractual warranty

Period	18 months
--------	-----------