

AD4113ZTL



TECHNICAL SPECIFICATIONS

Interface	USB 2.0
Product Resolution	1.3 Mpixels (SXGA)
Magnification Rate	20x~90x
Sensor	Color CMOS
Frame Rate	Up to 30 fps
Save Formats	Image: DinoCapture2.0: BMP, GIF, PNG, MNG, TIF, TGA, PCX, WBMP, JP2, JPC, JPG, PGX, RAS, PNM DinoXscope: PNG, JPEG Movie: DinoCapture2.0: WMV, FLV, SWF DinoXscope: MOV
Microtouch	Touch sensitive trigger on the microscope for taking pictures
Lighting	8 white LED lights switched on/off by software
Polarizer	Yes
Measurement Function	Yes
Calibration Function	Yes
Operating System Supported	Windows 8, 7, Vista, XP MAC OS 10.4 or later
Detachable front covers	FC-L-OC1, FC-L-OC1, FL-L-OZ2
Unit Dimension	10.5cm (H) x 3.2cm (D)
Unit Weight	105(g)

NEW FEATURES OF THE STRUCTURE

Scroll lock

Improved smooth and precise scroll wheel movement for better control

Cable strain relief

INFORMATION ABOUT WORKING DISTANCE AND FIELD OF VIEW

M	WD1	WD2	FOV (X)	FOV (Y)
20	151.0	160.5	19.6	15.6
30	101.0	110.4	13.0	10.4
40	77.2	86.7	9.8	7.8
50	64.1	73.6	7.8	6.3
60	56.2	65.7	6.5	5.2
70	51.3	60.8	5.6	4.5
80	48.3	57.8	4.9	3.9
90	46.6	56.1	4.3	3.5

M = magnification rate

WD1 = working distance

WD2 = working distance without front cap

FOV = field of view

Unit = mm