



# Agilent 82357B USB/GPIB Interface for Windows<sup>®</sup>

Data Sheet



## GET HOOKED!

with Agilent GPIB and  
Instrument Control Products



**Agilent Technologies**

## Features

- Fast and easy connection to GPIB instruments
- Uses standard USB interface
- Interface with up to 14 GPIB instruments
- IEEE-488 compatible
- Transfer over 1.15 MB/s with large block transfers
- Uses industry standard software
- Parallel polling capability



### The Fastest and Easiest Connection

Gain the ultimate speed and efficiency by connecting your PC or laptop to your test and measurement instruments. The Agilent 82357B USB/GPIB Interface provides direct connection from the USB port of your PC to GPIB Instruments.

USB (Universal Serial Bus) is built into most of today's desktop and laptop computers, offering fast and easy plug-and-play connection and auto configuration. Furthermore, the 82357B USB/GPIB Interface makes connectivity easier as there are no switches to set, and no PC cards to install.

Getting connected has never been easier with the 82357B USB/GPIB Interface, thanks to automatic configuration and use of industry standards. Your applications will be up and running in an instant.

### Totally Transparent, Fully Compatible

The USB/GPIB Interface software allows transparent communication between a PC and one or more GPIB instruments. The bundled VISA (Virtual Instrument Software Architecture) software provides GPIB emulation so that your existing GPIB programs work immediately, without any modification needed. You also do not need to learn a new programming language to make the connection.

USB support is standard in Windows XP/Vista/ Windows 7. These operating systems support the automatic plug-and-play configurations, thus it is easy to install, configure, and use the USB devices. Standard plug-and-play devices, like the 82357B are automatically detected as soon as they are connected to the computer's USB port.

This capability provides convenience and reduces setup time. It is also hot

pluggable, making it easy to connect and disconnect without having to shut down the computer. No external power supplies are necessary.

### **Full Assurance for Interoperability**

The USB/GPIB Interface comes with the Agilent I/O Libraries Suite that includes VISA and SICL. VISA enables interoperability among different instrument and software vendors. The IO Libraries Suite also provides robust instrument control and works with the software development of your choice.

Standard GPIB functionality is provided by implementing the IEEE 488.1 and IEEE 488.2 specifications. These specifications provide defined mechanical and electrical characteristics, and a basic set of instrument commands and common data formats.

Using industry standards gives you the assurance and confidence that your programs will work with multiple hardware and software vendors, and migrate to new standards in the future.

### **Standard Computer IO**

In the past, RS-232 and GPIB have been the primary interfaces used for connecting instruments to PCs in test and measurement applications. Although RS-232 offers a low-cost solution, RS-232's lower baud rate and connection limitations are cumbersome and too slow for many of today's measurement needs.

GPIB has provided a high performance, cost effective, and also reliable solution for more than 25 years. Today, however, computers have fewer available IO slots, leaving engineers with little options but to use more

expensive solutions such as industrial PCs.

With USB and LAN built into most of today's PCs, standard computer IO has evolved into a solution that is acceptable for automation and control of test and measurement instruments.

Early USB devices that were initially developed for connecting PCs to peripherals such as keyboard, mouse and so forth offered little bandwidth. Today, USB offers bandwidths up to 12 Mbits/s for USB 1.1 and 480 Mbits/s for USB 2.0. The 82357B USB/GPIB Interface runs at USB 2.0.

The 82357B USB/GPIB Interface uses a thin, flexible, high-quality USB cable that is USB 1.1 and 2.0 compliant. This cable is shielded and specified to 1,500 insertions, ensuring a durable connection and reliable data transfer.

The 82357B is capable of transfer rates over 1.15 MB/s with large block transfers. The performance is better than typical GPIB cards for block sizes over 32KB. Small block transfers are limited by the USB implementation and the overhead associated with setting up the transfer. However, since instrument setup time can dominate the overall test time, this impact may be minimal.

If small block transfer performance is critical, then you may consider the Agilent 82350A PCI GPIB interface.

### **Make the Connection**

You may connect directly to one instrument with no additional GPIB cables required with the 82357B USB/GPIB Interface.

For multiple instruments connection, use a daisy chain or star configuration with your GPIB instruments using standard GPIB cables. Once the instruments are connected, connect the USB/GPIB Interface as the last connection on one of the instruments. One 82357B USB/GPIB Interface supports up to 14 GPIB instruments. Multiple 82357B USB/GPIB Interfaces can be connected to improve system performance.

Another additional significant feature would be the parallel polling capability of the 82357B USB/GPIB Interface. This allows you to easily check up to eight individual devices at once, corresponding to the number of data lines on the GPIB.



## Software Included

The VISA standard is a system-level industry standard supported by a multi-vendor foundation for instrument software. It offers an easy-to-use set of IO control functions and provides a migration path to new standards such as IVI (Interchangeable Virtual Instruments). IVI is a new driver standard developed by instrument and software vendors to define software standards for instrument interchangeability. This new standard is layered on Agilent VISA and offers interchangeability and high performance.

The Interactive IO software is also included and it provides utility for sending commands and queries to an instrument to help view the response returned by the instrument.

## Take a Look for Yourself

To see the 82357B USB/GPIB Interface in action, check out the demo at [www.agilent.com/find/82357B](http://www.agilent.com/find/82357B).

## Ordering Information

**82357B** USB/GPIB Interface for Windows

### Options

Option 0B1 – Add Paper Manual Set

### Accessories

None

For more information on Agilent GPIB and instrument control products, visit [www.agilent.com/find/gpib](http://www.agilent.com/find/gpib).

## Technical Specifications

### GENERAL REQUIREMENTS

Minimum system requirements

<b>Operating System</b>	Microsoft Windows XP Service Pack 3 (or later)	Microsoft Windows Vista SP1 and SP2 (32-bit and 64-bit), Business, Ultimate, Enterprise, Home Basic, and Home Premium	Microsoft Windows 7 (32- and 64-bits), Home Basics, Home Premium, Professional, Ultimate, Enterprise
<b>Processor</b>	600 MHz Pentium II or higher required. 800 MHz recommended	1 GHz 32-bit (x86), 1 GHz 64-bit (x64)	1 GHz 32-bit (x86), 1 GHz 64-bit (x64)
<b>Available memory</b>	256 MB minimum (1 GB or greater recommended)	1 GB minimum	1 GB minimum
<b>Available hard disk space*</b>	1.5 GB available hard disk space includes: • 1 GB available for Microsoft .NET Framework 2.0 • 65 MB for Agilent IO Libraries Suite	1.5 GB available hard disk space includes: • 1 GB available for Microsoft .NET Framework 2.0 • 65 MB for Agilent IO Libraries Suite	1.5 GB available hard disk space includes: • 1 GB available for Microsoft .NET Framework 2.0 • 65 MB for Agilent IO Libraries Suite
<b>Video</b>	Super VGA (800x600) 256 colors or more	Support for DirectX 9 graphics with 128 MB graphics memory recommended (Super VGA graphics is supported)	Support for DirectX 9 graphics with 128 MB graphics memory recommended (Super VGA graphics is supported)
<b>Browser</b>	Microsoft Internet Explorer 5.01 or greater	Microsoft Internet Explorer 7 or greater	Microsoft Internet Explorer 7 or greater
	Support USB 2.0 high speed and full speed • Standard USB endpoints supported • IEEE-488.1 and IEEE-488.2 compatible • SICL and VISA 2.2		

## SUPPORTED LANGUAGES AND APPLICATIONS

---

Applications (with Intui Link)	<ul style="list-style-type: none"><li>• Microsoft Excel 97 and 2000</li><li>• Microsoft Word 97 and 2000</li><li>• Check the Web for latest supported applications</li></ul>
Software development applications	<ul style="list-style-type: none"><li>• Agilent VEE 6.0 or greater</li><li>• Visual Basic 6.0</li><li>• Visual C++ 6.0</li><li>• Visual Studio .NET</li><li>• BASIC for Windows</li><li>• LabVIEW 6.0 or greater</li></ul>

## GENERAL CHARACTERISTICS

---

Power	USB bus-powered device, +5 V, 500 mA(max), 200 mA(typ)
GPIO transfer rate	1.15 MB/s or better
Connectors	Standard 24-pin IEEE-488, Standard USB A
USB Hubs	Self-powered hubs
Parallel polling	A single parallel poll can check up to 8 individual devices at once, corresponding to the number of data lines on the GPIO.
Dimensions	105 mm (L) x 64 mm (W) x 30 mm (H) (includes connectors)
Weight	215 grams
Cable	2.5 meters, shielded, connector rated for 1500 insertions
LED Indicators	Ready, Access, Fail
Warranty	1 year
Maximum connections	Maximum 4 converters can be connected to the PC
Instrument connection	14 instruments – daisy chain via GPIO
Configuration	Plug-and-play

## ENVIRONMENTAL SPECIFICATIONS

---

Operating environment	0 °C to 55 °C
Storage environment	– 40 °C to +70 °C
Operating humidity	Up to 90 % at 40 °C non-condensing
Storage humidity	Up to 90 % at 65 °C non condensing

NOTE: If possible, you should always use the current version of the Agilent IO Libraries (spacing) Suite. This version supports the newest interfaces and operating systems, and has the most advanced features. The Agilent 82357B USB/GPIB Interface is supported for PCs with Windows XP Professional, Windows Vista or Windows 7 operating systems only. However, you may need an earlier version of the IO Libraries Suite to support an older interface or operating system. If you need an earlier version of Agilent IO Libraries, go to

 <http://www.agilent.com/find/iosuite> to locate the version you need.



### Agilent Email Updates

[www.agilent.com/find/emailupdates](http://www.agilent.com/find/emailupdates)  
Get the latest information on the products and applications you select.



[www.lxistandard.org](http://www.lxistandard.org)  
LXI is the LAN-based successor to GPIB, providing faster, more efficient connectivity. Agilent is a founding member of the LXI consortium.

### Agilent Channel Partners

[www.agilent.com/find/channelpartners](http://www.agilent.com/find/channelpartners)  
Get the best of both worlds: Agilent's measurement expertise and product breadth, combined with channel partner convenience.



*Microsoft, Windows, and Visual Studio are registered trademarks of Microsoft Corporation in the United States and/or other countries.*

## Remove all doubt

Our repair and calibration services will get your equipment back to you, performing like new, when promised. You will get full value out of your Agilent equipment through-out its lifetime. Your equipment will be serviced by Agilent-trained technicians using the latest factory calibration procedures, automated repair diagnostics and genuine parts. You will always have the utmost confidence in your measurements. For information regarding self maintenance of this product, please contact your Agilent office.

Agilent offers a wide range of additional expert test and measurement services for your equipment, including initial start-up assistance, onsite education and training, as well as design, system integration, and project management.

For more information on repair and calibration services, go to:

[www.agilent.com/find/removealldoubt](http://www.agilent.com/find/removealldoubt)

For more information on Agilent Technologies' products, applications or services, please contact your local Agilent office. The complete list is available at:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

#### Americas

Canada	(877) 894-4414
Latin America	305 269 7500
United States	(800) 829-4444

#### Asia Pacific

Australia	1 800 629 485
China	800 810 0189
Hong Kong	800 938 693
India	1 800 112 929
Japan	0120 (421) 345
Korea	080 769 0800
Malaysia	1 800 888 848
Singapore	1 800 375 8100
Taiwan	0800 047 866
Thailand	1 800 226 008

#### Europe & Middle East

Austria	43 (0) 1 360 277 1571
Belgium	32 (0) 2 404 93 40
Denmark	45 70 13 15 15
Finland	358 (0) 10 855 2100
France	0825 010 700*
	*0.125€/minute
Germany	49 (0) 7031 464 6333
Ireland	1890 924 204
Israel	972-3-9288-504/544
Italy	39 02 92 60 8484
Netherlands	31 (0) 20 547 2111
Spain	34 (91) 631 3300
Sweden	0200-88 22 55
Switzerland	0800 80 53 53
United Kingdom	44 (0) 118 9276201

Other European Countries:

[www.agilent.com/find/contactus](http://www.agilent.com/find/contactus)

Revised: October 1, 2009

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2010  
Printed in USA, June 8, 2010  
5989-5983EN

