

RoHS

Compliant

New TRIM TRIO®



• Secure

High Performance



Company Profile



SOURIAU

Connectors and interconnect systems for harsh environments

The company designs, manufactures and markets high performance interconnect solutions for severe environments from industrial broadline and universal ranges to complex system with integrated functions: filtering, high speed data transmission, hermetic seal, separation mechanism, remote handling, underwater mating, ...



Industrial



Aeronautical



Equipment & system

The dedicated end markets for SOURIAU's products are aeronautical, defense-space and industrial



SOURIAU was established in 1917 and has been created by successive acquisitions of the industrial, aeronautical, defense and space activities of SOURIAU, JUPITER and BURNDY.

The Group's products are engineered and manufactured in the USA and Dominican Republic, Europe and Morocco, Japan and India, and sold by a worldwide sales and marketing organization, and in addition to SOURIAU's offices, a large network of licensed distibutors and agents.

SOURIAU complies with most of national and international Quality Assurance Standards, production unit with ISO 14001

Quality Certificate Management System Environment Certificate Management System Quality Certificate Management System

ISO 9001

ISO 14001

Aeronautic Industry : EN 9100





Contents

| 2 3 3 4 |
|------------------|
| 5-9 |
| 5 |
| 6 |
| 6 |
| 7 |
| 8 |
| j 9 |
| 9 |
| |

| Ergonomic plug Backshells Sealing caps | 10 |
|--|-------|
| | 11-16 |
| Technical characteristics | 11 |
| Cable plug | 12 |
| Jam nut receptacle | 13 |
| PCB jam nut receptacle | 14 |
| Accessories | 15 |
| What sealing is | 16 |
| Industrial applications | 17 |
| | |

Description

IP68 / IP69K plastic circular connector with rapid locking system

"UTS" is the latest addition to the well known TRIM TRIO® interconnect system.

'UTS' is a range of Industrial circular multiway connectors available in 3 shell sizes and 9 contact arrangements.

The keywords for the new UTS are: Rapid – Secure – High performance



Secure

Rapid refers to the locking system and the total installed cost starting with the wiring & cabling and ending with the installation to the customers equipment. Rapid also refers to the total service on price request, samples and production deliveries.

The secure locking system together with the secure and versatile TRIM TRIO[®] contacts are giving confidence to both the connection and the customers equipment.


Moreover UTS is part of the well known TRIM TRIO[®] interconnect system with its more then 40 years of field experience.


High Performance

Extreme performance on water protection even in dynamic situations this in combination with a rapid and secure locking system makes UTS suitable for any high performance application.


UTS provides a connection that performs faster, easier, safer and more reliable, it makes : UTS : Your first choice in waterproof connectors !

UTS - Part of TRIM TRIO® interconnect system
















Multiple contact arrangements with VDE 0110 performances

Multiple contact arrangements within same connector size

- Different levels of current and rated voltages per VDE 0110
- Available in male and female gender
- Custom version upon request such as:
 - Mixed contact sizes
 - Power versions


High Performance


- High speed versions (RJ45, USB, BNC), upon request

UTS insert arrangements, contact size, rated voltage per VDE 0110 & current ratings

| Contact size | # 16 (dia. | #20 (dia. 1.0mm) | |
|---------------------------|--------------------------|--------------------------|--|
| Rated voltage | 250 V | 125 V | 125 V |
| Overvoltage category | III | III | III |
| Pollution degree | 3 | 3 | 3 |
| Size 10 | | | |
| Number of contacts | 3 (2+ grounding) | 4 | 6 |
| Max current (per contact) | 13A (machined + stamped) | 13A (machine + stamped) | 7.5A (machnied) / 5A (stamped) |
| Size 12 | | | |
| Number of contacts | 4 (3 + grounding) | 8 | 10 |
| Max current (per contact) | 13A (machined + stamped) | 13A (machine + stamped) | 7.5A (machined)/ 5A (stamped) |
| Size 14 | | | $ \begin{array}{c} 14-19\\ \hline \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\$ |
| Number of contacts | 7 (6 + grounding) | 12 | 19 |
| | | 13A (machined + stamped) | 7.5A (machined)/ 5A (stamped) |








UTS : Your first choice in waterproof connectors !






CONTACT ACCOMMODATION

- "UTS" connectors accept TRIM TRIO[®] size 16 or size 20 (depending on arrangement) removable snap-lock contacts
- Refer to TRIM TRIO[®] catalog for details
- Contacts to be ordered separately (except PCB versions)

In accordance with UL requirements


UTS : Your first choice in waterproof connectors !





Cable plug with backshell for pin and socket contacts UTS6JC...P / UTS6JC...S)





Each plug has 2 seals to cover the specified cable range (See table below). The stabdard seal is preassembled

The second seal is supplied as loose piece togoether with a plug.

| PN pin contact | PN socket | NB contacts | Shell size | L | ØA | Ø Cable range | |
|----------------|-------------|-------------|---------------|------|------|---------------------------------------|--------------------------------------|
| UTS6JC103P | UTS6JC103S | 3 4 10 | | | | | |
| UTS6JC104P | UTS6JC104S | | 10 | 63.2 | 26.2 | 1.5 to 5.0 2.5 to 8.00 (standard) | |
| UTS6JC106P | UTS6JC106S | 6 | | | | | 2.0 to 0.00 (standard) |
| UTS6JC124P | UTS6JC124S | 4 | 12 | 12 | | | |
| UTS6JC128P | UTS6JC128S | 8 | | | 66.7 | 29.7 | 3.0 to 9.0 5.0 to 12.0 (standard) |
| UTS6JC1210P | UTS6JC1210S | 10 | | | | | 0.0 to 12.0 (Standard) |
| UTS6JC147P | UTS6JC147S | 7 | 14 | | | | |
| UTS6JC1412P | UTS6JC1412S | 12 | | 71.5 | 34.6 | 5.0 to 12.0 7.0 to 14.0 (standard) | |
| UTS6JC1419P | UTS6JC1419S | 19 | | | | | |

Coloured ring supplied as optional extra (See page 15).

Notes : All dimensions are in mm. Dimensions are not contractual and may be subject to modifications.

UTS : Your first choice in waterproof connectors !

Jam nut receptacle (wire version) for pin and socket contacts



(UTS7...P / UTS7...S) MATING FACE F max (Panel thickness) 9 Ø A±0.15 B±0.2 H+0.3 D max G±0.25 PANEL CUT OUT ±0.2 ØM±0.2 Shell D F Ø **PN** pin contact PN socket **NB** contacts В G Н κ L ØМ size Α Max Max UTS7103P **UTS7103S** 3 UTS7104P UTS7104S 4 10 14.9 19.3 33.9 3.2 27.0 22.2 16.6 16.5 17.7 UTS7106P UTS7106S 6 **UTS7124P UTS7124S** 4 **UTS7128P UTS7128S** 8 19.0 12 19.3 33.9 3.2 31.8 27.0 20.8 21.2 22.5 UTS71210S UTS71210P 10 **UTS7147P UTS7147S** 7 UTS71412P UTS71412S 12 14 22.2 19.3 33.9 3.2 34.9 30.2 23.9 24.3 25.7 UTS71419P UTS71419S 19

Coloured ring supplied as optional extra (See page 15).

Notes : All dimensions are in mm Dimensions are not contractual and may be subject to modifications.

UTS : Your first choice in waterproof connectors !



PCB jam nut receptacle for male contacts UTS714PSE4K9 MATING FACE G±0.25 F max H±0.3 (Panel thickness) 8 Ø A±0.15 B±0.2 J±0.2 C±0.2 D Max **DRILLING PATTERN** PANEL CUT OUT ±0.2 3,02 2.98 ø1.2(x7) ØM±0.2 Contact area of —/ receptacle on PCB ø 3,1(x2) Shell D ØΑ в С Е F G н J L ØМ size Max 22.2 19.3 24.5 14 3 3.6 3.2 34.9 30.2 24.3 4 25.7 Other arrangements upon request. Stamped and formed contacts. Plating: K9 (std) = Min 0.4µ Gold in contact area, 3 - 5µ Tin on solder tail $T = 3 - 5\mu$ Tin all over Notes : All dimensions are in mm. Dimensions are not contractual and may be subject to modifications.

UTS

UTS : Your first choice in waterproof connectors !



Accessories

Receptacle sealing cap

Plug sealing cap





Part numbers Size 10: UTS10DCG Size 12: UTS12DCG Size 14: UTS14DCG Part numbers Size 10: UTS610DCG Size 12: UTS612DCG Size 14: UTS614DCG

Colour coding rings



Size 10: UTS710CCR* Size 12: UTS712CCR* Size 14: UTS714CCR* * Add G for Green, Y for Yellow, R for Red

Part numbers for receptacle Size 10: UTS610CCR* Size 12: UTS612CCR* Size14: UTS614CCR* * Add G for Green, Y for Yellow, R for Red

UTS : Your first choice in waterproof connectors !





What is sealing and how it is specified

- The connector's housing, sealing and locking mechanism protect the connection from external influences such as mechanical shocks, foreign bodies, humidity, dust, water and other fluids.
- The degree of protection is explained in IEC 60529, DIN EN60529 (DIN 40050) standards that categorize connections according to foreign body and water protection.
- The degree of protection is indicated by IP (International Protection) followed by 2 digits (See example below):

First index figure (foreign bodies protection)

IP 6 8

Second index figure (water protection)

Code letters (International Protection)


| Index figure | Degree of protection | Index figure | Degree of protection |
|-----------------|--|-----------------|---|
| 0 | No protection against accidental contact. No protection against solid foreign bodies. | 0 | No protection against water. |
| 1 | Protection against contacts with any large area by hand and against large solid foreign bodies with a diameter bigger than 50mm. | 1 | Drip-proof. Protection against vertical water drips. |
| 2 | Protection against contacts with the fingers. Protection against solid foreign bodies with a dia- meter bigger than 12mm. | 2 | Drip-proof. Protection against water drips up to a 15° angle. |
| 3 | Protection against tools, wires or similar objects with a diameter bigger than 2.5mm Protection against small solid bodies with a diame- ter bigger than 2.5mm. | 3 | Spray-proof. Protection against diagonal water drips up to a 60° angle. |
| 4 | As 3 however diameter is bigger than 1mm. | 4 | Splash-proof. Protection against splashed water from all directions. |
| 5 | Full protection against contacts. Protection against interior injurious dust deposits. | 5 | Hose-proof. Protection against water (out of a nozzle) from all directions. |
| 6 | Total protection against contacts. Protection against penetration of dust. | 6 | Protection against temporary flooding. |
| | | 7 | Protection against temporary immersions. |
| | | 8 | Protection against water pressure. Pressure to be specified by supplier. |
| | UTS offers high sealing performance IP68 / IP69K Even in dynamic situations. | 9K | High pressure hose-proof. Protection against high pressure water (out of a nozzle) from all directions. |

SOURIAU reserves the right to make any engineering refinments, alterations or improvements deemed necessary on its products. The dimensions appearing in this catalogue are thus subject to change without notice. When dimensions are critical detailed drawings should be requested

UTS : Your first choice in waterproof connectors !




Notes






Notes





UTS - Suitable for a broad range of applications





Its uses are endless! here are a few...





graphic

SUOIR


systems peoperative systems





and there is more ...: coast guar

street maintenance, Wind mills, Off road equipment, Antenna dish, Solar technology, Machine tools, Lightning / theatre, Outdoor advertising, Food processing Elevators & lifts Measuring / Test / Inspection Wheel chairs, Medical applications, etc...





www.souriau.com