

Specialist tape cassettes

In addition to the extensive range of TZe tapes in various colours and sizes, specialist tapes for industrial use have been developed for specific labelling tasks.

Flexible-ID Tape


Use on: Curved surfaces or itself



- Wrapping/flagging individual wires
- Sharp bends
- Cylindrical surfaces

Strong Adhesive Tape

Use on: Uneven, rough and textured surfaces



- Painted metal
- Powder-coated surfaces
- Utility cabinets

Heat-shrink tube

Use on: Wires and cables



- Shrinks and grips cable when heat is applied
- Permanent
- Durable

Technical Specifications

Items included

PT-E300 labelling machine
Lithium-ion battery
AC adapter
18mm black on yellow strong adhesive laminated label cassette (8m)
User guide
Wrist strap
Carry case

Hardware

Housing dimensions (mm) 133 (w) x 220 (h) x 74 (d)
Housing weight 740g
Tape size/type TZe tape: 3.5, 6, 9, 12, 18mm
Print resolution 180 dpi
Max. print height 15.8mm
Max. print speed 20mm / sec
Cutter type Manual: Cutter blade
Keyboard type PC style with numeric keypad
Number of keys 64
LCD display 15 characters x 3 line graphic
LCD backlight Yes
LCD size 67mm x 40mm
Print preview Yes
Text buffer Max. 200 chrs
Label memory 50 memory locations with up to 2,400 characters total
Power Lithium-ion battery (supplied)
AC adapter (supplied)
6 x AA (LR6/HR6) alkaline batteries (not supplied)

Built-in software

Built-in fonts 7
Built-in symbols 384
Character sizes 7: (6, 9, 12, 18, 24, 36, 42 pt)
Character widths 3: (extended, medium, condensed)
Font styles 9
Frames 7
Underline Yes
Max. number of lines 5
Horizontal alignment Automatic length labels: left aligned
Pre-set label length: centre aligned
Yes (25-300mm)
Tape length setting Narrow, half, full, chain print
Tape margin setting Yes
Tab function Yes
Specialist labelling functions Cable wrap, cable flag, face place, sequential numbering, patch panel, punch block
Automatic numbering Yes
Mirror printing No
Vertical printing Yes
Barcode creation Yes: (CODE39, CODE 128, EAN13, EAN8, ITF 2/5, UPC-A, UPC-E, CODABAR, GS1-128/UCC/EAN128)
Yes: (1-9)
Copy (repeat) printing Yes: (graphic preview)
Print preview Yes
Auto power off Yes
Unit change Yes: (inch/mm)
Language change 20 languages: (English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Turkish, Brazilian Portuguese)

Contact:

brother
at your side



Brother UK Ltd, Audenshaw, Manchester M34 5JD
Tel:+44(0)8444 999 444 Fax:+44(0)161 931 2218
Web: www.brother.co.uk

All specifications correct at time of printing. Brother is a registered trademark of Brother Industries Ltd. Brand product names are registered trademarks or trademarks of their respective companies.



P-touch
E300VP

brother
at your side



Industrial Labelling Machine

With dedicated functions for common labelling applications, easily create durable labels for faceplates, cables, consumer units and other electrical and datacom installations.

www.brother.co.uk/electrician

- Large backlit graphic display
- Dedicated function keys to easily create labels
- Includes tape cassette, AC adapter and carry case
- Prints 3.5, 6, 9, 12 & 18mm labels



The P-touch E300VP with its easy-to-use features ensures that your work is labelled professionally.



P-touch
E300VP

P-touch E300VP

The P-touch E300VP is an indispensable tool for all electricians and datacom installers and comes complete with a lithium-ion rechargeable battery and AC adapter, all housed in a durable carry case. The large backlit graphic LCD, standard PC style keyboard and specialised functions have been developed to make common industrial labelling tasks quick and easy. Leave a professional impression by creating high quality durable labels for your installations.



Prints labels 3.5 to 18mm in width

Print labels in various widths from 3.5 to 18mm to suit any space.



Face plate

Label socket outlets, network points and telephone extension faceplates for quick identification.



Cable wrap ; Cable flag

Identify cables quickly with easy-to-read labels.



9 barcode protocols

Include barcodes for added security and safety.




Large backlit graphic LCD

Easily view symbols and preview your label before printing.



Patch Panel

Create perfectly sized port identification labels.



Sequential numbering

Print labels containing a sequence of numbers or letters.



384 built-in symbols

Includes common electrical, datacom, AV, security and safety symbols.

P-touch laminated labels – designed to last

Brother P-touch laminated TZe tapes are available in many different colours and sizes. The thermal transfer ink is sandwiched between two protective layers of PET (polyester film), protecting the text against the effects of liquids, abrasion, temperature, chemicals and sunlight. As the labels have been tested to the extreme, you can be confident of a professional quality label that has been designed to last.



Laminated



Temperature Resistant



Water Resistant



Fade Resistant



Abrasion Resistant



Chemical Resistant



Easy Peel



Strong Adhesion