

# PRODUCT DATASHEET



# **Solid Fatigue-Step**

# Ultra-comfortable interlocking tiles in nitrile and rubber

- Interlocking solid surface tiles in two options:-
- 1. Solid Fatigue-Step (a blend of natural rubber and nitrile)
- 2. Solid Fatigue-Step Nitrile (100% nitrile)
- Nitrile option has excellent resistance to oils, chemicals and grease.
- Tiles link together to provide a very comfortable anti-fatigue flooring.
- Can withstand temperatures of up to 160°C and spillage of molten glass.
- Individual tiles can be moved and replaced with ease.
- Conforms to Slip Resistance Test EN13552 Category R10.
- · Optional bevelled edging in yellow or black.

Product height: 16mm

Dimensions (m.)	Weight Kg	Packaging Dimensions (cm.)	Packaging Type	Packaging Volume (m.)	Packaging Quantity	Colour	Part Code
0.9 x 0.9	8	17.5 x 17.5 x 105	Boxed	1	50/Pallet	Black	ST010001
Bevelled Edge / Corner Male	1.5	17.5 x 17.5 x 105	Boxed	1		Black	SS010002M
Bevelled Edge / Corner Male	1.5	17.5 x 17.5 x 105	Boxed	1		Yellow	SS070002M
Bevelled Edge / Corner Female	1.5	17.5 x 17.5 x 75	Boxed	1		Black	SS010002F
Bevelled Edge / Corner Female	1.5	17.5 x 17.5 x 105	Boxed	1		Yellow	SS070002F

Material: Tile - Natural Rubber/20% Nitrile mix

Accessories - Natural Rubber

Surface Finish: Solid textured
Product Height: 16mm nominal

Operating Temperature: -20° to +160° C

Resistance to Chemicals: Natural rubber with 25% Nitrile offers limited resistance to chemicals and oils

Environmental Resistance: Suitable for wet and dry environments. Will withstand welding splatter and spillages of other hot materials.

UV Resistance: Yes

Typical Applications: Ideal for non-slip and fatigue relief in all industrial areas.

Installation Method: Loose lay interlocking tiles.

Continued on next page

### **United Kingdom**

COBA Europe Ltd Marlborough Drive Fleckney, Leicestershire LE8 8UR

+44 (0)116 240 1088

sales@cobaeurope.com

www.cobaeurope.com

### Germany

COBA Europe GmbH Pullenweg 1 - 3 41352 Korschenbroich

r +49 (2161) 2945-0
⊠ verkauf@cobaeurope.de
𝔻 www.cobaeurope.de

#### Slovakia

COBA Europe s.r.o. Terchová - Vyšné Kamence 11 SK-013 06

/\* +421 41 507 11 12

⊠ sales@cobaeurope.sk

ॐ www.cobaeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.



# PRODUCT DATASHEET

Accessories: Bevelled edge / corners (installation guide below)

Cleaning Method: Pressure hose with detergent if required.

Product Performance: Conforms to Slip Resistance Test EN 13552 Category R10

Product Performance: Fatigue: ● ● ●

Slip Resistance:

Wear:

Low  $\ddagger$  High  $\longrightarrow \bigcirc \bigcirc \bigcirc \bigcirc$ 


Country of Origin: Sri Lanka


Other: Silicone is used in the production process of the mats and a residue will possibly be left on the

product.









Continued on next page

### **United Kingdom**

COBA Europe Ltd Marlborough Drive Fleckney, Leicestershire LE8 8UR

/\* +44 (0)116 240 1088☑ sales@cobaeurope.comع www.cobaeurope.com

## Germany

COBA Europe GmbH Pullenweg 1 - 3 41352 Korschenbroich

#49 (2161) 2945-0
werkauf@cobaeurope.de

www.cobaeurope.de

## Slovakia

COBA Europe s.r.o. Terchová - Vyšné Kamence 11 SK-013 06

/\* +421 41 507 11 12

Sales@cobaeurope.sk


www.cobaeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.



# DATASHEET


# **Configuration Examples**



#### Example 1


- 1 x Tile
- 2 x Femail Edge
- 2 x Male Edge

Area covered = 0.81m<sup>2</sup>



- Example 2
- 2 x Tile
- 3 x Femail Edge
- 3 x Male Edge

Area covered = 1.62m<sup>2</sup>





- 4 x Femail Edge
- 4 x Male Edge

Area covered = 3.25m<sup>2</sup>

# **Uniquely Flexible**

Every tile can be cut along the dividing (30mm) lines and still retain it's ability to be linked to another tile or edge.





### Example 4

- 2 x Tile (1 x Cut)
- 3 x Femail Edge
- 3 x Male Edge

Area covered = 1.08m<sup>2</sup>

#### **End of document**

### **United Kingdom**

COBA Europe Ltd Marlborough Drive Fleckney, Leicestershire LE8 8UR

- +44 (0)116 240 1088
- □ sales@cobaeurope.com

## Germany

COBA Europe GmbH Pullenweg 1 - 3 41352 Korschenbroich

- **/** +49 (2161) 2945-0
- □ verkauf@cobaeurope.de

### +421 41 507 11 12

COBA Europe s.r.o.

Terchová - Vyšné Kamence 11

Slovakia

SK-013 06

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.