

Chip-Lok™ LED COB Array Holder



Flange provides strength & thermal path to allow chip to run cooler

Hardened stainless prevents creep over time/temperature



Daisy chaining capable


- *Daisy chain up to 250 volts and 4 amps*
- *Metal acts as heatsink and allows chip to run cooler*
- *Hardened SS holder provides great thermal force over time/temperature*
- *Keyway and spring leg ease assembly*
- *Holders compatible with commercially available reflectors*



Designed to achieve Zhaga dimensions

Keyways allow easier assembly

Spring holds PCB in position to ease assembly



Contact IDEAL to learn about LED technology developments for other lighting applications.

US & Foreign Patents Pending



 **Zhaga**
Member



Chip-Lok™ LED COB Array Holder


Part Number	LED Part	Voltage	Holder Height (mm)	Holder Diameter (mm)	Screw Spacing (mm)	Temp (C)	Wire Sizes		50-2100AN Ledil Angela	50-2100LN Ledil Lena	50-2100MR Ledil Mirella-PF
							AWG	MM			
50-2002CT	Citizen CLL020/CLL022	CLASS 2/ SELV	3.5	35	25/35	110°	20-24 AWG	0.25-0.75 MM²			
50-2103CT	Citizen CLL030/CLL032	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2204CT	Citizen CLL040/CLL042	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2000CR	Cree CXA13	CLASS 2/ SELV	3.5	35	25/35	110°	20-24 AWG	0.25-0.75 MM²			
50-2001CR	Cree CXA15	CLASS 2/ SELV	3.5	35	25/35	110°	20-24 AWG	0.25-0.75 MM²			
50-2101CR	Cree CXA18	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	+
50-2102CR	Cree CXA25	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2234C	Cree CXA30	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2303CR	Cree CXA35	250V(cUL) 150V(ENEC)	7.2	65	50	110°	18-24 AWG	0.25-0.75 MM²			
50-2002CT	Edison 2PHM05/2PHM09	CLASS 2/ SELV	3.5	35	25/35	110°	20-24 AWG	0.25-0.75 MM²			
50-2103CT	Edison 2PHM16/2PHM30*	CLASS 2*/ SELV*	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2204CT	Edison 2PHM40*	CLASS 2*/ SELV*	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2002CT	Lextar Nimbus 1000	CLASS 2/ SELV	3.5	35	25/35	110°	18-24 AWG	0.25-0.75 MM²			
50-2204CT	Lextar Nimbus 2000/3000/5000*	CLASS 2*/ SELV*	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2100LG	LG Innotek LEMWM18*	CLASS 2*/ SELV*	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2204CT	LG Innotek LEMWM24*	CLASS 2*/ SELV*	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2100NC	Nichia 110/121/204	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	+
50-2103NC	Nichia 216/360	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2100NC	Philips 1203	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	+
50-2100SH	Philips 1204/1205/1208	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2002CT	Seoul SDWx1	CLASS 2/ SELV	3.5	35	25/35	110°	20-24 AWG	0.25-0.75 MM²			
50-2103CT	Seoul SDWx2/SDWx3	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2204CT	Seoul SDWx4/SDWx5	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	
50-2100SH	Sharp MegaZenigata	250V(cUL) 150V(ENEC)	7.2	50	35	110°	18-24 AWG	0.25-0.75 MM²	+	+	

*Array has exposed live components; Class 2/SELV applications only unless LUMINAIRE provided with sufficient electrical protection.

Citizen® is a registered trademark of Citizen Holdings Co., LTD. Japan
 Cree® is a registered trademark of Cree, Inc.
 Edison® is a registered trademark of Edison-Opto Corporation.
 LG® Innotek is a registered trademark of LG Innotek.
 Lextar® is a registered trademark of Lextar Electronics Corporation.

NICHIA® is a registered trademark of Nichia Corporation.
 Philips Lumileds and LUXEON are registered trademarks of Philips Lumileds Lighting Company.
 Seoul® is a registered trademark of Seoul Semiconductor Co., LTD, Korea.
 Sharp® and Zenigata® are registered trademarks of Sharp Electronics Corporation.

50-2100AN Adaptor shown with Ledil Lena.



IDEAL INDUSTRIES, INC.
 www.idealindustries.com/products/oem

U.S.: oem@idealindustries.com • 1-800-324-9571
 Brazil: ideal_brazil@idealindustries.com • +55-11-4314-9930
 Canada: ideal_canada@idealindustries.com • +1-(800) 824-3325
 China: ideal_china@idealindustries.com • +86-21-31263188, Ext. 209
 German: germanysales@idealnwd.com • +49-89-996886-0
 India: oem@idealindustries.com • +91 0124 4495106
 Mexico: oem@idealindustries.com • +1-815-899-7796
 UK: enquiries@idealnwd.com • +44 (0)1925 444 446