


## Slide - White



### INTRODUCTION

Transfer data without fuss with the Integral Slide. The USB has a capless design with a smooth thumb slide and is available in three eye-catching colours.

### FEATURES

- Stylish slider USB
- Capless design with a smooth thumb slide
- Available in three eye-catching colours
- Quality durable casing, assembled in the UK

### PRODUCT TYPE

USB Flash Drive

### INTERFACE TYPE

Hi-Speed USB

### INTERFACE CONNECTIVITY

1x Hi-Speed USB - 4 Pin USB Type A

### COMPATIBILITY

Windows, XP, Vista, 7 and 8.  
Mac OS 09 and Later.  
Linux v2.4.0 and above.

### ENVIRONMENTAL PARAMETERS

Min Operating Temperature 0°C  
Max Operating Temperature 70°C

### COMPLIANT STANDARD

Plug and Play

	LENGTH	WIDTH	DEPTH	WEIGHT
<b>PRODUCT</b>	54mm	21mm	10mm	10g
<b>PACKED</b>	170mm	105 mm	12mm	21g

CAPACITY	PART CODE	BARCODE (EAN)
4GB	INFD4GBSLDWH	5055288412651
8GB	INFD8GBSLDWH	5055288412712
16GB	INFD16GBSLDWH	5055288412682
32GB	INFD32GBSLDWH	5055288416734

This device should not be used as your sole backup.  
Product design and specification subject to change or modification without notice. E&OE. All trademarks acknowledged.  
2 year warranty