




(2,54 mm) .100"



IPT1 SERIES

SHROUDED POWER CONNECTOR SET

SPECIFICATIONS

For complete specifications see www.samtec.com?IPT1

Insulator Material:

Black LCP

Contact Material:

Phosphor Bronze

Plating:

Sn or Au over 50µ" (1,27 µm) Ni

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

Insertion Depth:

(3,81 mm) .150" to

(6,48 mm) .255"

Wiping Distance:

(0,38 mm) .015"

Insertion Force (SMT):

3.0 oz (0,83 N) avg.

Withdrawal Force (SMT):

2.6 oz (0,72 N) avg.

Insertion Force (T/H):

6.0 oz (1,67 N) avg.

Withdrawal Force (T/H):

5.0 oz (1,39 N) avg.

Voltage Rating:

550 VAC/777 VDC

RoHS Compliant: Yes

Processing:

Lead-Free Solderable: Yes


SMT Lead Coplanarity:

(0,13 mm) .005" max (05-10)

(0,15 mm) .006" max (15-25)

Mates with:
IPS1

IPT1/IPS1	
PINS	CURRENT RATING (PER CONTACT)
1	5.9 A
2	4.8 A
3	4.1 A
4	3.6 A
ALL	2.3 A




- Individually shrouded contacts
- Locking clip option

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality



APPLICATION



ALSO AVAILABLE (MOQ Required)

- Other sizes
- Other platings
- Latching feature
- No. 1 position polarized Contact Samtec.

Note: Some sizes, styles and options are non-standard, non-returnable.

IPT1

1

NO. PINS PER ROW

05, 10, 15, 20, 25

(Standard sizes)

LEAD STYLE

Specify **LEAD STYLE** from chart

PLATING OPTION

-L

= 10µ" (0,25 µm) Gold on contact, Matte Tin on tail

D

TAIL OPTION

Requires **-01** Lead Style (Leave blank for Through-Hole)

OTHER OPTION

-A

= Alignment Pin (-VS only) (N/A with -LC)

-LC

= Locking Clip (Manual placement required) (-VS only) (N/A with -A)

-K

= (6,00 mm) .236" DIA Polyimide film Pick & Place Pad (-VS only)

-TR

= Tape & Reel Packaging (-VS only)

LEAD STYLE	MATED HEIGHT	A	B
-01	(11,05) .435	(6,35) .250	(2,16) .085
-01-VS	(13,59) .535	(6,35) .250	N/A
-02	(14,00) .551	(9,30) .366	(2,64) .104
-03	(16,00) .630	(11,30) .445	(2,16) .085
-04	(17,00) .669	(12,30) .484	(2,69) .106
-05	(19,00) .748	(14,30) .563	(2,46) .097
-06	(20,00) .787	(15,30) .602	(2,35) .093
-07	(25,00) .984	(20,30) .799	(2,31) .091
-08	(30,00) .1181	(25,30) .996	(2,39) .094
-09	(35,00) .1378	(30,30) .1193	(2,46) .097

Through-hole **Surface Mount**

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM