

Black Box Products

Cabinets & Racks > Cabinet Accessories



Cable Duct, Corrugated, 1.25" (3.17-cm) Diameter, Orange, 250-ft. (76.2-m) Coil



Organize your short or plenum cable runs.

JPD002

Extended Double Diamond™ Warranty Available
(Lifetime)

Product Highlights

- The convenient and safe way to run cable.
- Use in short runs or couple together for longer runs.
- Strong, crush-resistant HDPE is lightweight.
- Internal corrugated wall provides less surface contact, reducing friction.
- Guaranteed for life!

Details

Description

Cable Duct, Corrugated, 1.25" (3.17-cm) Diameter, Orange, 250-ft. (76.2-m) Coil

Quick Facts

- The convenient and safe way to run cable.
- Use in short runs or couple together for longer runs.
- Strong, crush-resistant HDPE is lightweight.
- Internal corrugated wall provides less surface contact, reducing friction.
- Guaranteed for life!

Tech Spec

Technical Specifications for Cable Duct, Corrugated, 1.25" (3.17-cm) Diameter, Orange, 250-ft. (76.2-m) Coil:

Bend Radius	11" (27.9 cm)
Diameter	Inside: 1.25"; Outside: 1.33" ± .020"
Tensile Pull Strength	500 lb. (226.8 kg) min.
Pull Tape	1000-lb. polyester
Weight	33 lb. (15 kg)

NOTE: Not recommended for direct burial or riser applications. Also not for use in older duct structures.
Technical specification weight is the unit weight. It is not the packaged shipping weight.