

549945 Composite - CCTV Plus Audio or Power or Pan and Tilt CCTV Control Applications

For more Information
please call

1-800-Belden1



General Description:

PTZ (CCTV+Power/Audio) Cable, Rated-CMG, 1-RG59 20 AWG solid bare copper with foam polyolefin, 95% bare copper braid, 1-18 AWG stranded bare copper pair with polyolefin insulation, Siamese with PVC jacket

Usage (Overall)

Suitable Applications: CCTV plus Audio, Pan and Tilt CCTV Control

Coax

Physical Characteristics

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	Solid	BC - bare Copper	0.813

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	3.683

Inner Shield

Inner Shield Material:

Type	Inner Shield Material	% Coverage (%)
Braid	BC - Bare Copper	95.000

Applicable Specifications and Agency Compliance

Applicable Standards & Environmental Programs

EU CE Mark: Yes

RG Type: 59/U

Electrical Characteristics

Nom. Characteristic Impedance:

Impedance (Ohm)
75

Nom. Inductance:

Inductance (µH/m)
0.318

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
53.480

Nominal Velocity of Propagation:

VP (%)
83.000

Nominal Delay:

Delay (ns/m)
4.003

Nom. Conductor DC Resistance:

METRIC MEASUREMENT VERSION

549945 Composite - CCTV Plus Audio or Power or Pan and Tilt CCTV Control Applications

DCR @ 20°C (Ohm/km)

32.810

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/km)

11.484

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1.000	0.984
5.000	2.133
10.000	2.953
50.000	6.234
100.000	8.531
200.000	11.812
400.000	16.405
700.000	22.967
900.000	26.248
1000.000	27.889

Max. Operating Voltage - UL:

350 V RMS

Twisted Pair

Physical Characteristics

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
1	18	7x26	BC - Bare Copper	1.168

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PP - Polypropylene	1.499

Twisted Pair Color Code Chart:

Number	Color
1	Black and Red

Electrical Characteristics

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
73.823

Physical Characteristics (Overall)

Conductor

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter:

5.893 x 11.430 mm

Mechanical Characteristics (Overall)

Operating Temperature Range:

-30°C To +80°C

UL Temperature Rating:

75°C

METRIC MEASUREMENT VERSION

549945 Composite - CCTV Plus Audio or Power or Pan and Tilt CCTV Control Applications

Bulk Cable Weight:	80.363 Kg/Km
Max. Recommended Pulling Tension:	453.716 N
Min. Bend Radius/Minor Axis:	63.500 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
NEC Articles:	800
CEC/C(UL) Specification:	CMG
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
C(UL) Flame Test:	FT4

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Aerial:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	649948

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
549945 0091000	305 MT	24.041 KG	WHITE	C	1 #18 PR, 1 RG-59/U COAX
549945 009500	152 MT	12.927 KG	WHITE	C	1#18,1RG-59/U COAX
549945 0101000	305 MT	24.041 KG	BLACK	C	1#18,1RG-59/U COAX
549945 010500	152 MT	12.927 KG	BLACK	C	1#18,1RG-59/U COAX

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 5 Revision Date: 03-13-2013

© 2013 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge,

METRIC MEASUREMENT VERSION

549945 Composite - CCTV Plus Audio or Power or Pan and Tilt CCTV Control Applications

information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.