


FREEDM® LST™ Loose-Tube, Gel-Free Cable, Riser

12 F, 62.5 µm multimode (OM1)

CORNING

Corning FREEDM® LST™ gel-free cables are flame-retardant, indoor/outdoor, riser-rated cables designed for interbuilding and intrabuilding backbones in aerial, duct and riser applications. With a riser rating, there is no need for a transition splice when entering the building. Available in a compact design, these cables are protected against water penetration by innovative waterblocking tapes and yarns that swell to absorb water. Waterblocking without the use of messy gels provides more efficient and craft-friendly cable preparation, allows easier cable access and simplifies the use of buffer tube fan-out kits. The buffer tubes and fibers in each tube are color coded for quick, easy identification.

Note: This cable is available in 12 different jacket colors – blue, orange, green, brown, slate, white, red, black, yellow, violet, rose and aqua. The colored jacket allows for easy visual identification of the cables while still providing all of the required environmental protection of an indoor/outdoor cable jacket. Black is the standard jacket color using the part numbers shown here. Contact Customer Care at 1-800-743-2675 to order other color options.



Features and Benefits

Riser rating

No transition splices when entering buildings

Gel-free waterblocking technology

Craft-friendly cable preparation

Color-coded fibers


Quick and easy identification

All-dielectric construction

Requires no grounding or bonding

UV-resistant, flame-retardant jacket

Rugged, durable and easy to strip



Standards

Approval and Listings

National Electrical Code® (NEC®) OFNR, CSA OFN FT-4

Common Installations

Outdoor lashed aerial and duct; indoor vertical riser and general purpose horizontal according to National Electrical Code (NEC) Article 770

CORNING

FREEDM[®] LST[™] Loose-Tube, Gel-Free Cable, Riser

12 F, 62.5 µm multimode (OM1)



Standards

Design and Test Criteria ANSI/ICEA S-104-696

Specifications

General Specifications	
Environment	Indoor/Outdoor Cables
Application	Aerial, Direct Buried, Duct, General Purpose Horizontal, (Vertical Riser)
Cable Type	Loose Tube
Product Type	Dielectric
Flame Rating	Riser (OFNR)
Fiber Category	62.5 µm MM (OM1)

Temperature Range	
Storage	-40 °C to 70 °C (-40 °F to 158 °F)
Installation	-10 °C to 60 °C (14 °F to 140 °F)
Operation	-40 °C to 70 °C (-40 °F to 158 °F)

Cable Design	
Fiber Count	12
Fiber Coloring	Blue, Orange, Green, Brown, Slate, White, Red, Black, Yellow, Violet, Rose, Aqua
Fibers per Tube	12
Number of Tube Positions	1
Number of Active Tubes	1
Tensile Strength Elements and/or Armoring - Layer 1	Dielectric strength members
Tensile Strength Elements and/or Armoring - Layer 2	Water-swellable dielectric strength members
Number of Ripcords	1
Outer Jacket Material	Flame-Retardant, UV-Resistant
Outer Jacket Color	Black

FREEDM® LST™ Loose-Tube, Gel-Free Cable, Riser

12 F, 62.5 µm multimode (OM1)

CORNING

Mechanical Characteristics Cable

Weight	56 kg/km (38 lb/1000 ft)
Nominal Outer Diameter	7.4 mm (0.29 in)
Max. Tensile Strength, Short-Term	1350 N (300 lbf)
Max. Tensile Strength, Long-Term	400 N (90 lbf)
Min. Bend Radius Installation	111 mm (4.4 in)
Min. Bend Radius Operation	37 mm (1.5 in)

Chemical Characteristics

RoHS	Free of hazardous substances according to RoHS 2002/95/EG
------	---

Fiber Specifications

Optical Characteristics (cabled)

Fiber Core Diameter	62.5 µm
Fiber Category	OM1
Fiber Code	K
Performance Option Code	30
Wavelengths	850 nm / 1300 nm
Maximum Attenuation	3.4 dB/km / 1.0 dB/km
Serial 1 Gigabit Ethernet	300 m / 550 m
Serial 10 Gigabit Ethernet	33 m / -
Min. Overfilled Launch (OFL) Bandwidth	200 MHz*km / 500 MHz*km
Minimum Effective Modal Bandwidth (EMB)	220 MHz*km / -

- Notes: 1) Improved attenuation and bandwidth options available.
2) Bend-insensitive single-mode fibers available on request.
3) Contact a Corning Customer Care Representative for additional information.

Ordering Information

Part Number	012KSF-T4130D20
Product Description	FREEDM® LST™ Single-Tube, Gel-Free Cable, Riser, 12 F, 62.5 µm multimode (OM1)

FREEDM[®] LST[™] Loose-Tube, Gel-Free Cable, Riser

12 F, 62.5 μm multimode (OM1)

The CORNING logo is a blue square with the word "CORNING" in white, uppercase, sans-serif font centered inside.

Notes



Corning Optical Communications LLC • PO Box 489 • Hickory, NC 28603-0489 USA

800-743-2675 • FAX: 828-325-5060 • International: +1-828-901-5000 • www.corning.com/opcomm

A complete listing of the trademarks of Corning Optical Communications is available at www.corning.com/opcomm/trademarks.
Corning Optical Communications is ISO 9001 certified. © 2014 Corning Optical Communications. All rights reserved.