

## EL100F

Is a fast curing hydrophobic polyurethane supplied in a unique single cartridge delivery system

### Application

- Sealing
- Potting
- Encapsulation

### Key Properties

- Good electrical properties
- Good gap filling properties
- Good adhesion to various substrate
- Low embedment stress
- Flame retardant

### Description

- Basic Two component polyurethane system
- Resin RL100F
- Hardener HL100F

Physical Data (approx. – values)	Resin	Hardener	Mixed
Colour	Red	Natural	Red
Specific Gravity	0.97	1.1	1.02
Viscosity (poise @ RT)	25	20	Semi-thixotropic

### Cure Schedule (150ml sample)

Temperature	Working Life (minutes)	Gel Time (minutes)	Light Handling (hours)	Full Cure (hours)
RT*	1-2	3-6	4-6	48
60°C	-	-	2	4
80°C	-	-	1	2

\*RT is defined as 20-25°C

The above are typical values and will vary depending on the cured mass and application. Hotter temperatures may be used for faster cure but will result in higher post cure shrinkage and higher cure exotherm. Experimentation and testing is suggested to avoid side effects. For maximum properties a post cure may be required – Contact our technical service department for advice.

### Processing

Mix ratio by volume 1:1

### Typical Properties

Test	Result	Unit
Hardness (24hrs @ RT)	65-75	Shore A
Operating Temperature	- 55 to + 120	°C (application & geometry dependent)
Tensile Strength	5	MPa
Elongation at Break	60	%
Peak Exotherm (150ml sample)	70	°C
Coefficient of Linear Expansion	80-100	ppm/°C
Volume Resistivity	$1.3 \times 10^{12}$	ohm.cm
Surface Resistivity	$1.6 \times 10^{11}$	ohm
Electric Strength	24	kV/mm
Loss Tangent (@ 20°C)	0.04	50Hz
(@ 20°C)	0.03	1kHz
(@ 20°C)	0.02	1MHz
Permittivity (@ 20°C)	4.5	50Hz
(@ 20°C)	4.4	1kHz
(@ 20°C)	4.3	1MHz

## Approvals

RoHS compliant	Yes
UL94-V0	No (self extinguishing)
REACH (SVHC concentration)	0%

## Packaging

EL100F is available in cartridges, bulk and kits

## Availability

Available through sales@robnor.co.uk

## Cartridge Mixing Part Numbers

EL100F/RD/250TC	
-----------------	--

It is essential for best results that the cartridge is 'balanced' before use to ensure correct mixing. Loading the cartridge into the gun before attaching the mixer element and pumping the gun to push a small amount of the contents forward will achieve this. Wipe the excess from the cartridge tip and add the static mixer. The cartridge is now ready for use.

## Twinpacks Part Numbers

Not available	
---------------	--

## Bulk Materials Part Numbers

Available on application	
--------------------------	--

Both resin and hardener are supplied in 5kg, 25kg and 200ltr drums and fully evacuated and ready for use. Care should be taken to ensure when mixing the resins air is not entrained in the mixture. If this is unavoidable the mixed resin and hardener should be re-evacuated before dispensing. The bulk resin and hardener materials can be dispensed from suitable dispensing machinery and Robnor Resins produce a range of these machines, details that can be provided on request.

## Kits and Sets Part Numbers

Available on application	
--------------------------	--

Kits and Sets are provided in separate containers to the correct ratio. In Kit form, pour the hardener into the larger resin container and use it as a mixing vessel. Stir well using an appropriate mixer until homogeneous.

Note: Incomplete mixing will be characterised by erratic or partially incomplete cure even after extended time periods.

## Cleaning

All equipment contaminated with mixed material should be cleaned before the material has hardened. TS130 is a suitable non-flammable cleaning agent, although other solvents may be found suitable. TS130 will also remove cured material provided it is allowed to soak for a number of hours.

## Storage and Shelf Life

Material stored in the original unopened containers under cool dry condition between 15° and 25°C will have a shelf life of at least 12 months. Once used the containers must be kept sealed to prevent effects from water, air or contaminants.

## Health and Safety

Polyurethane resin systems may cause sensitisation by skin contact or inhalation may be corrosive, harmful or toxic. It is therefore strongly recommended that skin and eye contact is avoided by the using of appropriate personal protective equipment such as gloves, safety glasses or goggles and overalls. Wash any contamination from the skin immediately and thoroughly and do not eat, smoke or drink in the working vicinity.

Under normal working conditions a good source of ventilation is adequate, however if the material is heated, or where vapour levels are likely to exceed the occupational exposure limits appropriate respiratory protection must be worn. Local exhaust ventilation (LEV) may be required especially for curing ovens or where large volumes of material are curing. The above is given as a guide only; please refer to RL/HL100F Health and Safety data or our Technical Service Department for individual/specific advice.

## Copyright & Warranty - Robnor Resins Limited

The results and information above does not constitute a specification and is given in good faith and without warranty. The information is derived from test/or extrapolations believed to be reliable and is quoted for guidance only. The product is offered for evaluation on the understanding the customer satisfies himself that the product is suitable for his intended by proper evaluation and testing.

## Contact Details

Robnor Resins Limited  
Hunts Rise  
South Marston Park  
Swindon SN3 4TE  
United Kingdom

Tel: +44 (0) 1793 823741

Fax: +44 (0) 1793 827033

Email: [support@robnor.co.uk](mailto:support@robnor.co.uk)

Web: [www.robnor.co.uk](http://www.robnor.co.uk)

Buy Online: [www.resins-online.com](http://www.resins-online.com) (UK only)