

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 16.04.2014

Version number 1

Revision: 16.04.2014

SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name:** *Détachant perchlorure de fer Réf : AR36-AR95 – AR955*
Perchlorure detaching iron Ref : AR36-AR95 – AR955
- **1.2 Relevant identified uses of the substance or mixture and uses advised against commercial and / or industrial use**
- **Application of the substance / the preparation :** Reagent
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**
CIF
240 rue Hélène Boucher
78530 BUC
Tél : 01.39.66.96.83 – Fax 01.33.66.97.78
E-mail : cif@cif.fr – Web : www.cif.fr
- **1.4 Emergency telephone number:**
France (ORFILA 24h/24) - Tel : +33 (0)1 45 42 59 59
Ireland - Tel : 00 353 1 8092568 - 00 353 1 8379964 (24h/24)
EU Tel : 112

SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008 :**




GHS05

Skin Corr. 1C H314 Causes severe skin burns and eye damage.

GHS07

Acute Tox. 4 H302 Harmful if swallowed.
Acute Tox. 4 H312 Harmful in contact with skin.

- **Classification according to Directive 67/548/EEC or Directive 1999/45/EC :**



Xn; Harmful

- *R21/22: Harmful in contact with skin and if swallowed.*
- **Information concerning particular hazards for human and environment:**
The product has to be labelled in the latest valid version according to the calculation procedure of the "General Classification guideline for preparations of the EU" .
- **Classification system:**
The classification is according to the latest editions of the EU-lists, and extended by company and literature data.

- **2.2 Label elements**

- **Labelling according to EU guidelines:**
The product has been marked in accordance with EU Directives / respective national laws.
2008/58/CE (30eme ATP) ; 2009/2/CE (31eme ATP) ; 2006/8/CE

(Contd. on page 2)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 16.04.2014

Version number 1

Revision: 16.04.2014

Trade name: Détachant perchlorure de fer Réf : AR36-AR95 – AR955
Perchlorure detaching iron Ref : AR36-AR95 – AR955

(Contd. of page 1)

· **Code letter and hazard designation of product:**



Xn Harmful

· **Hazard-determining components of labelling:**

oxalic acid

· **Risk phrases:**

21/22 Harmful in contact with skin and if swallowed.

· **Safety phrases:**

25 Avoid contact with eyes.

36/37 Wear suitable protective clothing and gloves.

60 This material and its container must be disposed of as hazardous waste.

· **2.3 Other hazards**

· **Results of PBT and vPvB assessment**

· **PBT:** Not applicable.



· **vPvB:** Not applicable.

SECTION 3: Composition/information on ingredients

· **3.2 Chemical characterization: Mixtures**

· **Description:** Mixture: consisting of the following components.

· **Dangerous components:**

CAS: 144-62-7 EINECS: 205-634-3 Index number: 607-006-00-8 RTECS: RO 2450000	oxalic acid	 Xn R21/22  Acute Tox. 4, H302; Acute Tox. 4, H312	50-100%
---	-------------	---	---------

· **Additional information:** For the wording of the listed risk phrases, refer to section 16.

SECTION 4: First aid measures

· **4.1 Description of first aid measures**

· **General information:**

Symptoms of poisoning may even occur after several hours; therefore medical observation for at least 48 hours after the accident.

· **After excessive inhalation:** Supply fresh air; consult a doctor in case of complaints.

· **After skin contact:** Generally the product does not irritate the skin.

· **After eye contact:** Rinse opened eye for several minutes under running water.

· **After swallowing:** Call for a doctor immediately.

· **4.2 Most important symptoms and effects, both acute and delayed :**

No further relevant information available.

· **4.3 Indication of any immediate medical attention and special treatment needed :**

No further relevant information available.

GB

(Contd. on page 3)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 16.04.2014

Version number 1

Revision: 16.04.2014

Trade name: Détachant perchlorure de fer Réf : AR36-AR95 – AR955
Perchlorure detaching iron Ref : AR36-AR95 – AR955

(Contd. of page 2)

SECTION 5: Firefighting measures

- **5.1 Suitable extinguishing agents:**
CO₂, powder or water spray. Fight larger fires with water spray or alcohol resistant foam.
- **5.2 Special hazards arising from the substance or mixture :**
Formation of toxic gases is possible during heating or in case of fire.
- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures :** Not required.
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**
Dispose contaminated material as waste according to item 13.
- **6.4 Reference to other sections :**
See Section 7 for information on safe handling.
See Section 8 for information on personal protective equipment.
See Section 13 for disposal information.

SECTION 7: Handling and storage

- **7.1 Precautions for safe handling :** No special precautions are necessary if used correctly.
- **Information about fire - and explosion protection:** No special measures required.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** No special requirements.
- **Information about storage in one common storage facility:**
Store away from foodstuffs.
Store away from oxidizing agents.
- **Further information about storage conditions:** None.
- **7.3 Specific end use(s) :** No further relevant information available.

SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see section 7.
- **8.1 Control parameters**

· **Ingredients with limit values that require monitoring at the workplace:**

144-62-7 oxalic acid (50-100%)

WEL (Great Britain)	Short-term value: 2 mg/m ³ Long-term value: 1 mg/m ³
IOELV (EU)	Long-term value: 1 mg/m ³
MAK (Switzerland)	Long-term value: 1 e mg/m ³

· **Additional information:**

As a basis for the production of this document, the most current valid lists were used.

(Contd. on page 4)

GB

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 16.04.2014

Version number 1

Revision: 16.04.2014

Trade name: Détachant perchlorure de fer Réf : AR36-AR95 – AR955
Perchlorure detaching iron Ref : AR36-AR95 – AR955

(Contd. of page 3)

- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**
Keep away from food, beverages and petfood.
Wash hands before breaks and at the end of work.
Avoid contact with the eyes and skin.
- **Respiratory protection:** Not required.
- **Protection of hands:**



Protective gloves

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

- **Gloves material :**
The selection of suitable gloves does not only depend on the material, but also on further marks of quality which may vary from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked before use.
- **Eye protection:** Not required.

SECTION 9: Physical and chemical properties

· 9.1 Information on basic physical and chemical properties

· General Information

· Appearance:

Form:	Solid
Colour:	White
Odour:	Odourless
Odour threshold:	Not determined.

· **pH-value (126.1 g/l) at 20 °C:** 1.5

· Change in condition

Melting point/Melting range:	101.5 °C
Boiling point/Boiling range:	Undetermined.

· **Flash point:** Not applicable.

· **Flammability (solid, gaseous):** Not determined.

· **Ignition temperature:** Not applicable.

· **Decomposition temperature:** Not determined.

· **Self-igniting:** Product is not self igniting.

· **Danger of explosion:** Product does not present an explosion hazard.

· Explosion limits:

Lower:	Not determined.
Upper:	Not determined.

· **Vapour pressure at 40 °C:** 0.4 hPa

· **Density at 20 °C:** 1.65 g/cm³

(Contd. on page 5)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 16.04.2014

Version number 1

Revision: 16.04.2014

Trade name: Détachant perchlorure de fer Réf : AR36-AR95 – AR955
Perchlorure detaching iron Ref : AR36-AR95 – AR955

(Contd. of page 4)

- | | |
|---|--|
| · Relative density : | Not determined. |
| · Vapour density : | Not applicable. |
| · Evaporation rate : | Not applicable. |
| · Solubility in / Miscibility with water: | Soluble. |
| · Segregation coefficient (n-octanol/water): | -0.81 log POW |
| · Viscosity: | |
| Dynamic: | Not applicable. |
| Kinematic: | Not applicable. |
| · Solvent content: | |
| VOC (EC) | 0.00 % |
| · 9.2 Other information : | No further relevant information available. |

SECTION 10: Stability and reactivity

- **10.1 Reactivity**
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:** To avoid thermal decomposition do not overheat.
- **10.3 Possibility of hazardous reactions :** Reacts with strong oxidizing agents.
- **10.4 Conditions to avoid :** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** Carbon dioxide

SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity:**

- **LD/LC50 values relevant for classification:**

144-62-7 oxalic acid

Oral	LD50	375 mg/kg (rat)
------	------	-----------------

- **Primary irritant effect:**
- **On the skin:** No irritant effect.
- **On the eyes:** No irritant effect.
- **Sensitization:** No sensitizing effects known.
- **Additional toxicological information:**

The product shows the following hazards according to the calculation method of the General EU Classification Guidelines for Preparations as issued in the latest version:
Harmful

SECTION 12: Ecological information

- **12.1 Toxicity**

- **Aquatic toxicity:**

6153-56-6 Acide oxalique, dihydrate

CE 50 48h	137 mg/l (daphnia)
-----------	--------------------

(Contd. on page 6)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 16.04.2014

Version number 1

Revision: 16.04.2014

Trade name: Détachant perchlorure de fer Réf : AR36-AR95 – AR955
Perchlorure detaching iron Ref : AR36-AR95 – AR955

(Contd. of page 5)

CL50	160 mg/l (fish)
------	-----------------

- **12.2 Persistence and degradability** : No further relevant information available.
- **12.3 Bioaccumulative potential** : No further relevant information available.
- **12.4 Mobility in soil** : No further relevant information available.
- **Additional ecological information:**
- **General notes:**
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water.
Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT**: Not applicable.
- **vPvB**: Not applicable.
- **12.6 Other adverse effects** : No further relevant information available.

SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**
- **Recommendation** :



Must not be disposed of together with household garbage. Do not allow product to reach sewage system.

- **Uncleaned packaging:**
- **Recommendation:** Disposal must be made according to official regulations.

SECTION 14: Transport information

- | | |
|---|---|
| · 14.1 UN-Number
· ADR, ADN, IMDG, IATA | Not classified as hazardous for transport |
| · 14.2 UN proper shipping name
· ADR, ADN, IMDG, IATA | Not classified as hazardous for transport |
| · 14.3 Transport hazard class(es)
· ADR, ADN, IMDG, IATA
· Class | Not classified as hazardous for transport |
| · 14.4 Packing group
· ADR, IMDG, IATA | Not classified as hazardous for transport |
| · 14.5 Environmental hazards:
· Marine pollutant: | No |
| · 14.6 Special precautions for user | Not applicable. |
| · 14.7 Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | Not applicable. |
| · UN "Model Regulation": | - |

GB

(Contd. on page 7)

Safety data sheet
according to 1907/2006/EC, Article 31

Printing date 16.04.2014

Version number 1

Revision: 16.04.2014

Trade name: Détachant perchlorure de fer Réf : AR36-AR95 – AR955
Perchlorure detaching iron Ref : AR36-AR95 – AR955

(Contd. of page 6)

SECTION 15: Regulatory information

- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**

H302 Harmful if swallowed.

H312 Harmful in contact with skin.

R21/22 Harmful in contact with skin and if swallowed.

- **Abbreviations and acronyms:**

ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)

IMDG: International Maritime Code for Dangerous Goods

IATA: International Air Transport Association

GHS: Globally Harmonized System of Classification and Labelling of Chemicals

EINECS: European Inventory of Existing Commercial Chemical Substances

ELINCS: European List of Notified Chemical Substances

CAS: Chemical Abstracts Service (division of the American Chemical Society)

VOC: Volatile Organic Compounds (USA, EU)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent