

Tenma 72-10208 Combustible Gas Leak Detector

Features

Higher Sensitivity

Adjustable tick rate to locate leaks quickly and easily

Visual leak detection by LED indicators

Precision sensor detects even the smallest leaks.

Fast response of less than two seconds to 40% LEL.

Includes earphone Jack

16" gooseneck

Specifications

Sensitivity	50 ppm methane
Sensor Type	Low power semiconductor
Warm Up Time	Approx. 60 seconds
Response Time	Less than 2 sec. (up to 40%LEL)
Duty Cycle	Continuous
Probe Length	16"
Power Supply	3 "C" cell batteries
Battery Life	8 hours continuous use, typical
Alarm	Visible & Audible at 10% LEL for Methane. Can be calibrated for other concentrations or gases
Warranty	1 year

Operating Conditions

To ensure accurate readings use it only when ambient air is within this range:

Temperature	32 to 120°F
Humidity	10 to 90% RH (non condensing)

