



## Niptec TR 20 50M Cutter • Product # 10525



**Overview :** TR 20 50M- 1000-Series. Has the same features as our TR 20 M but the cutting angle is 48° instead of 21°. Ideal for reaching into difficult places. Has ESD safe handles.

TR 20 50M- 1000-Series. Has the same features as our TR 20 M but the cutting angle is 48° instead of 21°. Ideal for reaching into difficult places. Has ESD safe handles.



### Niptec TR 20 50M Cutter

Series	1000
Cutting Jaw Type	Flush
Cutting Capacity	22 AWG
Angle	48°
Weight	0.15 lb



