

8620 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1



General Description:

16 AWG stranded (19x29) tinned copper conductors, conductors cabled, PVC insulation, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	16	19x29	TC - Tinned Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.7874

Insulation Resistance: 500 Megaohms/1000 ft.

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.0668

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	Green
3	White
4	Red

Overall Nominal Diameter: 9.550 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 80°C

Bulk Cable Weight: 120.544 Kg/Km

Max. Recommended Pulling Tension: 538.232 N

Min. Bend Radius/Minor Axis: 101.600 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

METRIC MEASUREMENT VERSION

8620 Multi-Conductor - Audio, Control and Instrumentation Cable

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/1/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

Other Flame Test:	VW-1, FT1
-------------------	-----------

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

63.9795

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

14.4364

Max. Operating Voltage - UL:

Voltage

600 V RMS

Max. Recommended Current:

Current

5.5 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8620 060100	30 MT	4.037 KG	CHROME		4 #16 PVC FRPVC
8620 0601000	305 MT	39.916 KG	CHROME	C	4 #16 PVC FRPVC
8620 060500	152 MT	19.958 KG	CHROME	C	4 #16 PVC FRPVC
8620 0605000	1,524 MT	226.797 KG	CHROME		4 #16 PVC FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 08-22-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.