

8722 Multi-Conductor - Special Audio, Communication and Instrumentation Cable



For more Information
please call

1-800-Belden1



General Description:

20 AWG stranded (7x28) TC conductors, PVC insulation, conductors cabled, Beldfoil® shield as noted (100% coverage), 22 AWG stranded TC drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
2	20	7x28	TC - Tinned Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PVC - Polyvinyl Chloride	1.727

Inner Shield

Inner Shield Material:

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: Stranded

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 5.740 mm

Pair

Pair Color Code Chart:

Number	Color
1	Shielded: Red & Black
2	Unshielded: Green & White

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 80°C

Bulk Cable Weight: 49.111 Kg/Km

Max. Recommended Pulling Tension: 249.099 N

Min. Bend Radius/Minor Axis: 57.150 mm

8722 Multi-Conductor - Special Audio, Communication and Instrumentation Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMG

CEC/C(UL) Specification: CMG

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 10/01/2005

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

C(UL) Flame Test: FT4

Plenum/Non-Plenum

Plenum (Y/N): No

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.6562

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
196.86

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
324.819

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
32.81

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C: 41.013 Ohm/km

Max. Operating Voltage - UL:

Voltage
350 V RMS

Max. Recommended Current:

Current
3.1 Amps per conductor @ 25°C

Notes (Overall)

Notes: Beldfoil® shield over Red and Black conductors only. Request Technical Bulletin T/8-21 before planning high and low level circuits in the same cable.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8722 060U1000	305 MT	15.876 KG	CHROME		2#20FS PVC,2#20 PVC PVC
8722 060U500	152 MT	8.165 KG	CHROME		2#20 FS PVC,2#20 PVC PVC
8722 0601000	305 MT	16.329 KG	CHROME	C	2#20 FS PVC,2#20 PVC PVC

METRIC MEASUREMENT VERSION

8722 Multi-Conductor - Special Audio, Communication and Instrumentation Cable

8722 060500	152 MT	8.391 KG	CHROME	C	2#20 FS PVC,2#20 PVC PVC
-------------	--------	----------	--------	---	--------------------------

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 10-15-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.