

8741 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1



General Description:

22 AWG solid tinned copper conductors, PVC insulation, twisted pairs, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
2	22	Solid	TC - Tinned Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.254

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.8128

Overall Cable

Overall Nominal Diameter: 5.842 mm

Pair

Pair Color Code Chart:

Number	Color
1	Black & Red
2	Black & White

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 80°C (UL AWM Style 2576)

Bulk Cable Weight: 34.229 Kg/Km

Max. Recommended Pulling Tension: 133.446 N

Min. Bend Radius/Minor Axis: 63.500 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMG, MPG

CEC/C(UL) Specification: CMG

AWM Specification: UL Style 2576 (150 V 80°C)

EU Directive 2011/65/EU (ROHS II): Yes

8741 Multi-Conductor - Audio, Control and Instrumentation Cable

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	88741 or 82741 (Stranded conductors)

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
98.43

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
54.1365

Max. Operating Voltage - UL:

Voltage	Description
300 V RMS	CMG
150 V RMS	UL AWM Style 2576

Max. Recommended Current:

Current
2.24 Amps per conductor @ 20°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8741 060U1000	305 MT	11.340 KG	CHROME		2 #22 TW PR FRPVC
8741 060U500	152 MT	6.124 KG	CHROME		2 #22 TW PR FRPVC
8741 0601000	305 MT	12.247 KG	CHROME	C	2 #22 TW PR FRPVC
8741 0605000	1,524 MT	149.686 KG	CHROME	C	2 #22 TW PR FRPVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 09-27-2012

© 2013 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and

8741 Multi-Conductor - Audio, Control and Instrumentation Cable

the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product. Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.