

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

22-01-3057

Status:

Active

Overview:

KK® Interconnect System - Molex

Description:

KK® 254 Crimp Housing, Friction Ramp, 5 Circuits



Series

image - Reference only

Documents:

- 3D Model

Packaging Specification PK-2695-001 (PDF)
- Drawing (PDF)

RoHS Certificate of Compliance (PDF)
- Product Specification PS-10-07 (PDF)

Agency Certification

- CSA

LR19980
- UL

E29179

General

- Product Family

Crimp Housings
- Series

2695
- Application

Signal, Wire-to-Board
- Overview

KK® Interconnect System - Molex
- Product Name

KK® 254
- UPC

800753593855

Physical

- Circuits (maximum)

5
- Color - Resin

Natural (White)
- Flammability

94V-0
- Gender

Female
- Glow-Wire Compliant

No
- Lock to Mating Part

Yes
- Material - Resin

Nylon
- Net Weight

0.520/g
- Number of Rows

1
- Packaging Type

Bag
- Panel Mount

No
- Pitch - Mating Interface

2.54mm
- Pitch - Termination Interface

2.54mm
- Polarized to Mating Part

Yes
- Stackable

No
- Temperature Range - Operating

See Product Specification

Material Info

- Old Part Number

2695-05RP

Reference - Drawing Numbers

- Packaging Specification

PK-2695-001
- Product Specification

PS-10-07
- Sales Drawing

SD-2695

EU RoHS

ELV and RoHS
Compliant
REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

2695Series

Mates With

KK®254 PCB Headers [42375](#) , [42377](#) ,
[42376](#) , [4030](#) , [6373](#) , [6410](#)

Use With

[2759](#) , [4809](#) KK® Crimp terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION