

9927 Multi-Conductor - Low-Capacitance Computer Cable for EIA RS-232/423



For more Information
please call

1-800-Belden1



General Description:

24 AWG stranded (7x32) TC conductors, Datalene® insulation, overall Beldfoil® (100% coverage) + TC braid shield (65% coverage), drain wire, PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
4	24	7x32	TC - Tinned Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Wall Thickness (mm)
Datalene®	FPE - Foam Polyethylene	0.381

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100
2		Braid	TC - Tinned Copper	65

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	Stranded	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.889

Overall Cable

Overall Cabling Color Code Chart:

Number	Color
1	Black
2	White
3	Red
4	Green

Overall Nominal Diameter: 5.563 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +80°C

UL Temperature Rating: 80°C (UL AWM Style 2919)

Bulk Cable Weight: 43.158 Kg/Km

Min. Bend Radius/Minor Axis: 53.975 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

9927 Multi-Conductor - Low-Capacitance Computer Cable for EIA RS-232/423

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM
AWM Specification:	UL Style 2919 (30 V 80°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)
0.68901

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
39.372

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
72.182

Nominal Velocity of Propagation:

VP (%)
78

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
78.744

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
17.4221

Max. Operating Voltage - UL:

Voltage	Description
30 V RMS	UL AWM Style 2919
300 V RMS	CM

Max. Recommended Current:

Current
1.8 Amps per conductor @ 25°C

Notes (Overall)

Notes: Datalene® insulation features include a low dielectric constant and a low dissipation factor for high-speed, low-distortion data handling. Physical properties include good crush resistance and light weight.

Put Ups and Colors:

METRIC MEASUREMENT VERSION

9927 Multi-Conductor - Low-Capacitance Computer Cable for EIA RS-232/423

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9927 060100	30 MT	1.588 KG	CHROME		4 #24 FHDPE SH PVC
9927 0601000	305 MT	13.154 KG	CHROME	C	4 #24 FHDPE SH PVC
9927 060500	152 MT	6.804 KG	CHROME	C	4 #24 FHDPE SH PVC
9927 0605000	1,524 MT	65.771 KG	CHROME		4 #24 FHDPE SH PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 11-15-2013

© 2013 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.