## INTELLIGENT BATTERY CHARGER SERIES



This new charger has built-in intelligence
Designed to deliver exactly the right amount of
charge automatically every time
Manufactured to BS3456, IEC335, UL1236,
EN60335, CE mark to ENB5008 - 1

- · Microprocessor controlled
- · Short circuit protection
- · Reverse polarity protection
- · High temperature protection
- · Soft start current control
- · Fast constant current bulk charge
- 3-Stage charging C1-CV-Float
- · Constant voltage float/standby
- Proportional timing
- Flexibility to match battery specification
- Output leads: 1.5m long fitted with crocodile clips
- Dimensions: 130 x 90 x 65mm
- Weight: 1.3kg (approx)
- UK manufactured
- LED indication of float charge, bulk charge, short circuit, reverse polarity, thermal shutdown.



## Reverse Polarity Protection - Prevents

damage to the charger if the battery is connected in

reverse. Visual indication is by a continuous flashing red indicator.

**High Temperature Protection** – If the internal case temperature rises to an unusually high level then the system will shut down. When the temperature has settled to a safe level the full charge current will be available. The visual warning for high temperature is by simultaneous flashing red and green indicators.

**Soft Start** – On power up the system will enter a "soft start" mode. This means that the charge current will build up slowly. During this time the charger will scan intensely for possible faults i.e. reverse battery, short circuit etc.

**Constant Current Bulk Charge & 3 Stage Charging** – Provides the fastest possible way to recharge the battery without overcharging.

Constant Voltage Float – Compensates for self discharge to hold the battery at peak charge ready for use. The battery can be left on charge until required, there will be no overcharging. Proportional Timing – Varies the second (constant voltage) stage in proportion to the time taken for the first stage (constant current). This allows optimal charging by eliminating the compromise of fixing charge timers. When the charger enters float charge mode the battery is 100% fully charged.

Current	Voltage	Voltage (bulk)	Voltage (float)	Input Voltage (options)	YUASA Part No.
			romago (moat)		
1Amp	12V	14.5V	13.65V	230/110VAC	YCP1A12
1Amp	24V	29.0	27.3V	230/110VAC	YCP1A24
1.5Amp	6V	7.25V	6.83V	230/110VAC	YCP1.5A6
1.5Amp	12V	14.5V	13.65V	230/110VAC	YCP1.5A12
2Amp	6V	7.25V	6.83V	230/110VAC	YCP2A6
2Amp	12V	14.5V	13.65V	230/110VAC	YCP2A12



## Yuasa Battery Sales (UK) Ltd

Hawksworth Industrial Estate, Swindon, Wiltshire SN2 1EG Tel: 01793-645700

Fax: 01793-645701 Website: www.yuasa-battery.co.uk

Registered number 1548820

Cat. No.	IBC3SFMay02		