Detailed Specifications & Technical Data



METRIC MEASUREMENT VERSION

1829A Coax - Series 6

For more Information please call

1-800-Belden1



General Description:

Series 6, 18 AWG solid .040" bare copper-covered steel conductor, gas-injected foam polyethylene insulation, Duobond® II + aluminum braid shield (60% coverage), PVC jacket (black, gray, white or neutral).

Phy	sical Charac	teristics (Ov	erall			, ,	- · · ·	
Cor	nductor WG:							
		randing Conducto	or Mate	rial	Dia. (mm)			
	1 18 So	lid BCCS - B	are Co	oper Covered Stee	el 1.016			
	Total Number of	of Conductors:			1			
	ulation sulation Materi	al:						
	Insulation Mater	ial	Di	a. (mm)				
	Gas-injected FPE	- Foam Polyethyle	ne 4.5	572				
	er Shield uter Shield Mat	erial:						
	Layer # Outer S	hield Trade Name	Туре	Outer Shield Ma	terial	Coverage (%)		
		Duofoil®			n Foil-Polyester Tape-Aluminum Foil			
	2		Braid	AL - Aluminum		60		
	e <mark>r Jacket</mark> uter Jacket Mat	erial:						
	Outer Jacket Ma PVC - Polyvinyl C							
•								
	erall Cable Overall Nomina	Diamatan			6.858 mm			
-	Overall Nomina	a Diameter:						
Mec	hanical Cha	racteristics (Over	all)				
	Operating Tem	perature Range	:		-40°C To +80°C			
	Bulk Cable Wei	ight:			40.181 Kg/Km			
	Max. Recomme	ended Pulling Te	ensior	1:	560.473 N			
-	Min. Bend Radi	ius/Minor Axis:			69.850 mm			
App	licable Spec	ifications an	d Ag	ency Comp	liance (Overall)			
		ards & Enviro			. ,			
	NEC/(UL) Spec	ification:			CATV, CM			
_	CEC/C(UL) Specification:			CM				
-	EU Directive 2011/65/EU (ROHS II):			Yes				
_	EU CE Mark:				No			
-	EU Directive 2000/53/EC (ELV):				Yes			
_	EU Directive 2002/95/EC (RoHS):				Yes			
_	EU RoHS Compliance Date (mm/dd/yyyy):			уууу):	01/01/2004			

Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION

750

862

18.3408

19.6204



1829A Coax - Series 6

EU Di	rective 2002/96/EC (WEEE):	Yes	
EU Di	rective 2003/11/EC (BFR):	Yes	
CA Pr	op 65 (CJ for Wire & Cable):	Yes	
MII Or	der #39 (China RoHS):	Yes	
	Type:	Series 6	
lame Te			
	st ime Test:	UL1685 UL Loading	
	Ion-Plenum		
Plenu	m (Y/N):	No	
ectrica	Characteristics (Overall)		
	racteristic Impedance:		
Impedar	ce (Ohm)		
75.000			
om. Indu	ctance:		
Inductar	ice (µH/m)		
0.318257			
om. Cap	acitance Conductor to Shield:		
	ince (pF/m)		
53.1522			
ominal V	elocity of Propagation:		
VP (%)			
83			
ominal D	elay:		
Delay (n			
3.9372			
om. Con	ductor DC Resistance:		
	20°C (Ohm/km)		
91.868			
ominal C	uter Shield DC Resistance:		
	20°C (Ohm/km)		
29.529			
om. Atte	nuation:		
	Hz) Attenuation (dB/100m)		
5	1.6405		
55	4.5934		
211	8.5306		
500 750	13.4521 16.7331		
862	18.0455		
1000	19.686		
1450	25.5918		
1800	28.2166		
2250	32.1538		
3000	37.0753		
lax. Atter			
	Hz) Attenuation (dB/100m)		
5	2.19827		
55	5.2496		
211 500	9.41647 14.6989		
750	14.0909		

Detailed Specifications & Technical Data

METRIC MEASUREMENT VERSION



1000	21.4577	
1450	26.248	
1800	28.8728	
2250	32.81	
3000	39.0439	

Max. Operating Voltage - UL:

Voltage

350 V RMS

Minimum Structural Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
950	2250	15
2250	3000	10

Sweep Test

Sweep Testing:

950 MHz - 3 GHz

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1829A Q5HU1000	305 MT	13.154 KG	WHITE, NEUTRAL	Z	#18 GIFHDLDPE SH FR PVC
1829A Q5H1000	305 MT	13.608 KG	WHITE, NEUTRAL	Z	#18 GIFHDLDPE SH FR PVC
1829A 008U1000	305 MT	13.154 KG	GRAY	Z	#18 GIFHDLDPE SH FR PVC
1829A 0081000	305 MT	13.608 KG	GRAY	Z	#18 GIFHDLDPE SH FR PVC
1829A 009U1000	305 MT	13.154 KG	WHITE	Z	#18 GIFHDLDPE SH FR PVC
1829A 0091000	305 MT	13.608 KG	WHITE	Z	#18 GIFHDLDPE SH FR PVC
1829A 010U1000	305 MT	13.154 KG	BLACK		#18 GIFHDLDPE SH FR PVC
1829A 0101000	305 MT	13.608 KG	BLACK	С	#18 GIFHDLDPE SH FR PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 6 Revision Date: 08-10-2012

© 2013 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.