



For more Information
please call

1-800-Belden1



General Description:

RG-58A/U type, 20 AWG stranded (19x33) .035" tinned copper conductor, polyethylene insulation, tinned copper braid shield (95% coverage), PVC jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	19x33	TC - Tinned Copper	0.889

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
PE - Polyethylene	2.9464

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.6985

Overall Cable

Overall Nominal Diameter: 4.902 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +75°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight: 37.205 Kg/Km

Max. Recommended Pulling Tension: 186.824 N

Min. Bend Radius/Minor Axis: 50.800 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	58A/U

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
50

Nom. Inductance:

Inductance (µH/m)
0.301852

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
101.055

Nominal Velocity of Propagation:

VP (%)
66

Nominal Delay:

Delay (ns/m)
5.05274

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
35.4348

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
13.4521

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1	1.3124
10	4.9215
50	12.1397
100	17.7174
200	26.5761
400	40.6844
700	58.0737
900	69.2291
1000	74.8068

Max. Operating Voltage - Non-UL:

Voltage
1400 V RMS

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8259 010U1000	305 MT	11.793 KG	BLACK		RG-58A/U 50 OHMS COAX
8259 010U500	152 MT	6.350 KG	BLACK		RG-58A/U 50 OHMS COAX
8259 010100	30 MT	1.497 KG	BLACK		RG-58A/U 50 OHMS COAX
8259 0101000	305 MT	12.247 KG	BLACK	C	RG-58A/U 50 OHMS COAX
8259 010500	152 MT	6.350 KG	BLACK	C	RG-58A/U 50 OHMS COAX
8259 0105000	1,524 MT	61.235 KG	BLACK	C	RG-58A/U 50 OHMS COAX

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 1 Revision Date: 08-01-2013

© 2013 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.