

7921A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable



For more Information
please call

1-800-Belden1



General Description:

24 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, overall Beldfoil® (100% coverage) plus tinned copper braid shield (70% coverage), drain wire, industrial grade sunlight- and oil-resistant PVC jacket. Seq. marking at 2 ft. intervals

Usage (Overall)

Suitable Applications:

Industrial Ethernet, Harsh Environments, Category 5e, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, Noisy Environments, CMX - Outdoor, EtherNet/IP™

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)	Dia. (mm)
PO - Polyolefin	0.305	1.168

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100.000
2		Braid	TC - Tinned Copper	70.000

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
26	Solid	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
Industrial Grade PVC - Polyvinyl Chloride	0.762

Overall Cable

Overall Nominal Diameter: 8.382 mm

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Storage Temperature Range: -40°C To +80°C

7921A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

Installation Temperature Range:	-25°C To +75°C
Operating Temperature Range:	-40°C To +75°C
Bulk Cable Weight:	74.410 Kg/Km
Max. Recommended Pulling Tension:	333.615 N
Min. Bend Radius/Minor Axis:	33.528 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMR, CMX-Outdoor
CEC/C(UL) Specification:	CMR
EU Directive 2011/65/EU (ROHS II):	Yes
Other Standards:	ISO/IEC 11801 ed 2.1 (2008) Class D
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	Category 5e - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 5e, EtherNet/IP™ Compliant

Flame Test

UL Flame Test:	UL1666 Vertical Riser
CSA Flame Test:	FT4

Suitability

Suitability - Outdoor:	Yes
Sunlight Resistance:	Yes
Oil Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)

49.215

Maximum Capacitance Unbalance (pF/100 m): 150

Nominal Velocity of Propagation:

VP (%)

70

Maximum Delay:

Delay (ns/100 m)

538 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)

45

Maximum Conductor DC Resistance:

7921A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

DCR @ 20°C (Ohm/100 m)

9.38

Max. Operating Voltage - UL:

Voltage

300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.0	65.3	62.3	63.0	60.0	20.0	20.0
4	4.1	56.3	53.3	51.0	49.0	23.6	23.6
8	5.8	51.8	48.8	46.0	43.0	25.4	25.4
10	6.5	50.3	47.3	43.0	41.0	26.0	26.0
16	8.2	47.3	44.3	39.0	36.0	26.0	26.0
20	9.3	45.8	42.8	36.5	33.5	26.0	26.0
25	10.4	44.3	41.3	33.9	30.9	25.5	25.5
31.25	11.7	42.9	39.9	31.0	28.0	25.0	25.0
62.5	17.0	38.4	35.4	22.0	19.0	23.5	23.5
100	22.0	35.3	32.3	14.0	11.0	22.5	22.5

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	95-110	63.8	60.8
4	100 ± 15	95-110	51.7	48.7
8	100 ± 15	95-107	45.7	42.7
10	100 ± 15	95-107	43.8	40.8
16	100 ± 15	95-107	39.7	36.7
20	100 ± 15	95-107	37.7	34.7
25	100 ± 15	95-107	35.8	32.8
31.25	100 ± 15	95-107	33.9	30.9
62.5	100 ± 15	95-107	27.8	24.8
100	100 ± 15	95-107	23.8	20.8

Notes (Overall)

Notes: US Patent #'s 5606151; 5734126. EtherNet/IP is a trademark of ControlNet International, Ltd. under license by Open DeviceNet Vendor Association, Inc. Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7921A 0021000	305 MT	24.494 KG	RED	C	4 PR #24 PP SH PVC
7921A 0061000	305 MT	24.494 KG	BLUE, LIGHT	C	4 PR #24 PP SH PVC
7921A 0101000	305 MT	24.494 KG	BLACK	C	4 PR #24 PP SH PVC
7921A 0102000	610 MT	48.081 KG	BLACK	C	4 PR #24 PP SH PVC
7921A 1NH1000	305 MT	24.494 KG	TEAL 1NH	C	4 PR #24 PP SH PVC

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 7 Revision Date: 08-07-2013

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express,

7921A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.