

For more Information
please call

1-800-Belden1



General Description:

18 AWG solid .040" bare copper conductor, gas-injected foam polyethylene insulation, Duobond® + aluminum braid shield (77% coverage), PVC jacket.

Usage (Overall)

Suitable Applications: HDTV, DBS, Broadband CATV, Cable Modem

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	18	Solid	BC - Bare Copper	1.016

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FPE - Foam Polyethylene	4.572

Outer Shield

Outer Shield Material:

Layer #	Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
1	Bonded Duofoil®	Tape	Bonded Aluminum Foil-Polyester Tape-Aluminum Foil	100
2		Braid	AL - Aluminum	77
3		Tape	Bonded Aluminum Foil-Polyester Tape w/Shorting Fold	100

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 6.985 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -40°C To +80°C

UL Temperature Rating: 80°C

Bulk Cable Weight: 47.622 Kg/Km

Max. Recommended Pulling Tension: 404.786 N

Min. Bend Radius/Minor Axis: 69.850 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CATV, CM

CEC/C(UL) Specification: CM

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Series Type:	Series 6

Flame Test

UL Flame Test:	UL1685 UL Loading
----------------	-------------------

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75.000

Nom. Inductance:

Inductance (µH/m)

0.318257

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

53.1522

Nominal Velocity of Propagation:

VP (%)

83

Nominal Delay:

Delay (ns/m)

3.9372

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

20.9984

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

15.0926

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
5	1.6405
55	4.5934
211	8.5306
500	13.4521
750	16.7331
862	18.0455
1000	19.686
1450	25.5918
1800	28.2166
2250	32.1538
3000	37.0753

Max. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

5	2.19827
55	5.2496
211	9.41647
500	14.6989
750	18.3408
862	19.6204
1000	21.4577
1450	26.248
1800	28.8728
2250	32.81
3000	39.0439

Max. Operating Voltage - UL:

Voltage
350 V RMS

Shield Effectiveness:

Start Freq. (MHz)	Stop Freq. (MHz)	Effectiveness (dB)
5	50	105
50	1000	125

Minimum Structural Return Loss:

Start Freq. (MHz)	Stop Freq. (MHz)	Min. SRL (dB)
5	1000	20
1000	2250	15
2250	3000	10

Sweep Test

Sweep Testing: 5 MHz - 3 GHz

Notes (Overall)

Notes: Shielding effectiveness determined from screening attenuation measurement when tested in accordance with IEC 61196-1.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7915A 009U1000	305 MT	13.608 KG	WHITE		#18 GIFHDLDPPE SH FS PVC
7915A 009U500	152 MT	7.031 KG	WHITE		#18 GIFHDLDPPE SH FS FRPVC
7915A 0091000	305 MT	13.608 KG	WHITE	C	#18 GIFHDLDPPE SH FS FRPVC
7915A 009500	152 MT	7.031 KG	WHITE	C	#18 GIFHDLDPPE SH FS FRPVC
7915A 010U1000	305 MT	13.608 KG	BLACK		#18 GIFHDLDPPE SH FS PVC
7915A 010U500	152 MT	7.031 KG	BLACK		#18 GIFHDLDPPE SH FS FRPVC
7915A 0101000	305 MT	13.608 KG	BLACK	C	#18 GIFHDLDPPE SH FS FRPVC
7915A 010500	152 MT	7.031 KG	BLACK	C	#18 GIFHDLDPPE SH FS FRPVC

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 4 Revision Date: 08-10-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not

to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.
Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.