

8760 Multi-Conductor - Shielded Twisted Pair Cable



For more Information
please call

1-800-Belden1

**General Description:**

18 AWG stranded (16x30) tinned copper conductors, polyethylene insulation, twisted pair, overall Beldfoil® shield (100% coverage), 20 AWG stranded tinned copper drain wire, PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
1	18	16x30	TC - Tinned Copper

Total Number of Conductors: 2

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (mm)
PO - Polyolefin	0.457

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape w/Shorting Fold	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	7x28	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.711

Overall Cable

Overall Nominal Diameter: 5.639 mm

Pair**Pair Color Code Chart:**

Number	Color
1	Black & Clear

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +60°C
Bulk Cable Weight:	37.205 Kg/Km
Max. Recommended Pulling Tension:	240.203 N
Min. Bend Radius/Minor Axis:	57.150 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CM

8760 Multi-Conductor - Shielded Twisted Pair Cable

AWM Specification: UL Style 2092 (300 V 60°C)

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: Yes

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 01/01/2004

EU Directive 2002/96/EC (WEEE): Yes

EU Directive 2003/11/EC (BFR): Yes

CA Prop 65 (CJ for Wire & Cable): Yes

MII Order #39 (China RoHS): Yes

Flame Test

UL Flame Test: UL1685 UL Loading

Suitability

Suitability - Indoor: Yes

Plenum/Non-Plenum

Plenum (Y/N): No

Plenum Number: 88760, 87760 or 82760

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (µH/m)

0.59058

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)

89.243

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

21.3265

Max. Operating Voltage - UL:

Voltage

300 V RMS

Max. Recommended Current:

Current

7.2 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
8760 060U1000	305 MT	12.247 KG	CHROME		2 #18 LDPE SH PVC
8760 060U500	152 MT	6.350 KG	CHROME		2 #18 LDPE SH PVC
8760 0601000	305 MT	12.247 KG	CHROME		2 #18 LDPE SH PVC
8760 06010000	3,048 MT	122.471 KG	CHROME	C Y	2 #18 LDPE SH PVC
8760 06010001	3,048 MT	122.471 KG	CHROME	C Z	2 #18 LDPE SH PVC
8760 06015000	4,572 MT	197.314 KG	CHROME	C Y	2 #18 LDPE SH PVC
8760 0602000	610 MT	24.494 KG	CHROME	C	2 #18 LDPE SH PVC
8760 060250	76 MT	3.175 KG	CHROME		2 #18 LDPE SH PVC
8760 060500	152 MT	6.350 KG	CHROME	C	2 #18 LDPE SH PVC
8760 0605000	1,524 MT	65.771 KG	CHROME	C	2 #18 LDPE SH PVC
8760 0609999	305 MT	12.701 KG	CHROME		2 #18 LDPE SH PVC

Notes:

8760 Multi-Conductor - Shielded Twisted Pair Cable

C = CRATE REEL PUT-UP.

Y = FINAL PUT-UP LENGTH MAY VARY -10% TO +20% FROM LENGTH SHOWN.MAY CONTAIN 2 PIECES. MINIMUM LENGTH OF ANY ONE PIECE IS 1500'.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 3 Revision Date: 08-02-2012

© 2013 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.