

7987P Multi-Conductor - 4-Pair UTP Cable for RGB Video



For more Information
please call

1-800-Belden1



General Description:

NanoSkew™ 24 AWG twisted pairs solid bare copper conductors, FEP insulation, rip cord, Flamarrest® jacket.

Usage (Overall)

Suitable Applications: UTP Based Video Applications, Not for data transmission requiring TIA/EIA Category qualifications, RGB

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
FEP - Fluorinated Ethylene Propylene

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

Outer Jacket Ripcord: Yes

Overall Cable

Overall Nominal Diameter: 5.105 mm

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 31.252 Kg/Km

Max. Recommended Pulling Tension: 177.928 N

Min. Bend Radius/Minor Axis: 5.080 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMP
CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	7987R

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)
100

Nominal Velocity of Propagation:

VP (%)
70

Typical Delay Skew:

Delay Skew (ns/m)
0.022

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance
1	100 ± 15	100 ± 15
4	100 ± 15	100 ± 15
8	100 ± 15	100 ± 15
10	100 ± 15	100 ± 15
16	100 ± 15	100 ± 15
20	100 ± 15	100 ± 15
25	100 ± 15	100 ± 15
31.25	100 ± 15	100 ± 15
62.5	100 ± 15	100 ± 15
100	100 ± 15	100 ± 15

7987P Multi-Conductor - 4-Pair UTP Cable for RGB Video

Notes (Overall)

Notes: Jacket sequentially marked at 2 ft. intervals.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
7987P 1NDU1000	305 MT	9.979 KG	MAROON 1ND		4 PR #24 FEP FLRST
7987P 1NDU1640	500 MT	16.366 KG	MAROON 1ND		4 PR #24 FEP FLRST

Revision Number: 3 Revision Date: 08-01-2013

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.