



For more Information  
please call

1-800-Belden1



### General Description:

16 AWG pairs stranded (19x29) tinned copper conductors, twisted pairs, PVC/Nylon insulation, overall Beldfoil® shield (100% coverage), PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

##### AWG:

# Pairs	AWG	Stranding	Conductor Material
1	16	19x29	TC - Tinned Copper

Total Number of Conductors: 2

#### Insulation

##### Insulation Material:

Insulation Material
PVC/Nylon - Polyvinyl Chloride/Nylon

#### Outer Shield

##### Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

##### Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
16	19x29	TC - Tinned Copper

#### Outer Jacket

##### Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.194

Outer Jacket Ripcord: Yes

#### Overall Cable

Overall Nominal Diameter: 7.468 mm

#### Pair

##### Pair Color Code Chart:

Number	Color
1	Black & Red

### Mechanical Characteristics (Overall)

Wet Temperature Range:	-30°C To +75°C
Dry Temperature Range:	-30°C To +90°C
Bulk Cable Weight:	83.339 Kg/Km
Max. Recommended Pulling Tension:	177.928 N
Min. Bend Radius/Minor Axis:	76.200 mm

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

NEC/(UL) Specification:	NPLF, TC
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	ICEA S-73-532, S-61-402

### Flame Test

UL Flame Test:	UL1685 UL Loading
C(UL) Flame Test:	FT4
IEEE Flame Test:	1202

### Suitability

Suitability - Burial:	Yes
Sunlight Resistance:	Yes

### Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

## Electrical Characteristics (Overall)

#### Nom. Inductance:

Inductance (µH/m)
0.6562

#### Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
164.05

#### Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
285.447

#### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
13.780

#### Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
13.780

#### Max. Operating Voltage - UL:

Voltage
600 V RMS (NEC Type TC)
150 V RMS (NPLF)

#### Max. Recommended Current:

Current
8 Amps per conductor @ 30°C

## Notes (Overall)

**Notes:** Alternate color coding available upon request.

## Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

## 9342 Multi-Conductor - 600V Tray Cable

9342 0101000	305 MT	24.948 KG	BLACK	C	2 #16 PVC/NYL SHLD PVC
9342 010500	152 MT	12.474 KG	BLACK	C	2 #16 PVC/NYL SHLD PVC
9342 0105000	1,524 MT	136.078 KG	BLACK		2 #16 PVC/NYL SHLD PVC

**Notes:**

C = CRATE REEL PUT-UP.

Revision Number: 2    Revision Date: 07-30-2013

© 2013 Belden, Inc  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.