


9363 Triad - 300V Power-Limited Tray Cable

For more Information
please call

1-800-Belden1

**General Description:**

22 AWG triads stranded (7x30) tinned copper conductors, twisted triads, PVC insulation, overall Beldfoil shield (100% coverage), PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Triads	AWG	Stranding	Conductor Material
1	22	7x30	TC - Tinned Copper

Total Number of Conductors: 3

Insulation**Insulation Material:**

Insulation Material	Dia. (mm)
PVC - Polyvinyl Chloride	1.5748

Outer Shield**Outer Shield Material:**

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
22	7x30	TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	0.9398

Outer Jacket Ripcord: Yes

Overall Cable**Overall Cabling Color Code Chart:**

Number	Color
1	Black & White & Red

Overall Nominal Diameter: 5.283 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -30°C To +105°C

UL Temperature Rating: 105°C

Bulk Cable Weight: 38.693 Kg/Km

Max. Recommended Pulling Tension: 128.998 N

Min. Bend Radius/Minor Axis: 50.800 mm

Applicable Specifications and Agency Compliance (Overall)**Applicable Standards & Environmental Programs**

NEC/(UL) Specification: ITC, PLTC

9363 Triad - 300V Power-Limited Tray Cable

CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
C(UL) Flame Test:	FT4
IEEE Flame Test:	1202

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes
Sunlight Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Surface Printing (Overall)

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (μH/m)
0.68901

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)
147.645

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
85.306

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
49.215

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)
196.86

Max. Operating Voltage - UL:

Voltage
300

Max. Recommended Current:

Current
3.8 Amps per conductor @ 25°C

Put Ups and Colors:

9363 Triad - 300V Power-Limited Tray Cable

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9363 060U1000	305 MT	11.793 KG	CHROME		3 #22 PVC SHLD PVC
9363 060U500	152 MT	6.124 KG	CHROME		3 #22 PVC SHLD PVC
9363 0602500	762 MT	29.484 KG	CHROME		3 #22 PVC SHLD PVC
9363 0605000	1,524 MT	56.699 KG	CHROME	C Z	3 #22 PVC SHLD PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 3 Revision Date: 09-02-2009

© 2013 Belden, Inc.
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.