


9402 Multi-Conductor - Audio, Control and Instrumentation Cable



For more Information
please call

1-800-Belden1

**General Description:**

20 AWG stranded (7x28) TC conductors, semi-rigid PVC insulation, twisted pairs, individually shielded w/Beldfoil® (100% coverage), 22 AWG stranded TC drain wire, overall PVC jacket.

Physical Characteristics (Overall)**Conductor****AWG:**

# Pairs	AWG	Stranding	Conductor Material
2	20	7x28	TC - Tinned Copper

Total Number of Conductors: 4

Insulation**Insulation Material:**

Insulation Material	Wall Thickness (mm)
S-R PVC - Semi-Rigid Polyvinyl Chloride	0.279

Inner Shield**Inner Shield Material:**

Inner Shield Trade Name	Type	Inner Shield Material	Coverage (%)
Beldfoil® (Z-Fold®)	Tape	Aluminum Foil-Polyester Tape	100

Inner Shield Drain Wire AWG:

AWG
22

Inner Shield Drain Wire Stranding: 19x34

Inner Shield Drain Wire Conductor Material: TC - Tinned Copper

Outer Jacket**Outer Jacket Material:**

Outer Jacket Material	Nom. Wall Thickness (mm)
PVC - Polyvinyl Chloride	1.0414

Overall Cable

Overall Nominal Diameter: 7.620 mm

Pair**Pair Color Code Chart:**

Number	Color
1	Red & Black
2	Green & White

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +80°C

UL Temperature Rating: 80°C (UL AWM Style 2464)

Bulk Cable Weight: 72.922 Kg/Km

Max. Recommended Pulling Tension: 320.270 N

Min. Bend Radius/Minor Axis: 76.200 mm

9402 Multi-Conductor - Audio, Control and Instrumentation Cable

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CMG
CEC/C(UL) Specification:	CMG
AWM Specification:	UL Style 2464 (300 V 80°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	04/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1685 FT4 Loading
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Inductance:

Inductance (μH/m)
0.558

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/m)
180.455

Nom. Capacitance Cond. to Other Conductor & Shield:

Capacitance (pF/m)
311.695

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)
30.5133

Ind. Pair Nominal Shield DC Resistance @ 20 Deg. C:	39.372 Ohm/km
---	---------------

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Recommended Current:

Current
3.1 Amps per conductor @ 25°C

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9402 060U500	152 MT	11.793 KG	CHROME		2 FS PR #20 PVC PVC
9402 0601000	305 MT	23.587 KG	CHROME	C	2 FS PR #20 PVC PVC
9402 0605000	1,524 MT	117.935 KG	CHROME		2 FS PR #20 PVC PVC

Notes:

METRIC MEASUREMENT VERSION

9402 Multi-Conductor - Audio, Control and Instrumentation Cable

C = CRATE REEL PUT-UP.

Revision Number: 3 Revision Date: 08-16-2012

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.