

1243A2 Multi-Conductor - Category 3 Nonbonded-Pair Cable



For more Information
please call

1-800-Belden1



General Description:

CAT3, 2-Pair, U/UTP-Unshielded, Plenum-CMP, Premise Horizontal Cable, 24 AWG solid bare copper conductors, LS-PVC insulation, LS-PVC jacket

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
2	24	Solid	BC - Bare Copper

Total Number of Conductors: 4

Insulation

Insulation Material:

Insulation Material
LS PVC - Low Smoke Polyvinyl Chloride

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

Outer Jacket Diameter:

Nom. Dia. (in.)
0.135

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue & Blue
2	White/Orange & Orange

Mechanical Characteristics (Overall)

Installation Temperature Range:	0°C To +60°C
Operating Temperature Range:	-20°C To +75°C
Bulk Cable Weight:	12 lbs/1000 ft.
Max. Recommended Pulling Tension:	15 lbs.
Min. Bend Radius/Minor Axis:	1 in.
Min. Bend/Installation:	1.350 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

1243A2 Multi-Conductor - Category 3 Nonbonded-Pair Cable

CEC/C(UL) Specification:	CMP
EU Directive 2011/65/EU (ROHS II):	Yes
IEEE Specification:	802.3 10BaseT, 100BaseT4
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	06/01/2007
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Telecommunications Standards:	568-B.2 Category 3
Other Specification:	NEMA WC-63 Category 3, UL verified to TIA/EIA-568-B.2, Category 3.

Flame Test

UL Flame Test:	NFPA 262 Plenum Flame Test (UL910)(FT6)
CSA Flame Test:	FT6

Plenum/Non-Plenum

Non-Plenum Number:	1227A1
--------------------	--------

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/ft)

19

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

VP (%)

61

Nominal Delay:

Delay (ns/ft)

1.5

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)

9.38

Max. Operating Voltage - UL:

Voltage

300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)

5

Electrical Characteristics-Premise (Overall)

Premise Cable Electricals:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. SRL (dB)	Fitted Imp. (Ohms)
1	2.56	41.0	No Spec	12.0	100 ± 15%
4	5.58	32.0	No Spec	12.0	100 ± 15%
10	9.71	26.	No Spec	12.00	100 ± 15%
16	13.10	23	No Spec	9.96	100 ± 15%

Notes (Overall)

1243A2 Multi-Conductor - Category 3 Nonbonded-Pair Cable

Notes: Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 3.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1243A2 009U1000	1,000 FT	12.000 LB	WHITE		CAT3 2PR U/UTP CMP BOX

Revision Number: 1 Revision Date: 02-06-2013

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.