

For more Information
please call

1-800-Belden1



General Description:

15 AWG stranded (19x27) .064" bare copper conductor, foam HDPE insulation, paper tape separator, bare copper braid shields (90% and 80% coverage), CSPE - Chlorosulphonated Polyethylene jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	15	19x27	BC - Bare Copper	1.6256

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Material	Dia. (mm)
Gas-injected FHDPE - Foam High Density Polyethylene	7.9248

Inner Shield

Inner Shield Material:

Type	Inner Shield Material	Coverage (%)
Braid	BC - Bare Copper	90

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (mm)
PE - Polyethylene	9.9314

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	BC - Bare Copper	80.000

Outer Shield Separator Material: Paper Tape

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
CSPE - Chlorosulphonated Polyethylene

Overall Cable

Overall Nominal Diameter: 13.208 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

UL Temperature Rating: 60°C

Non-UL Temperature Rating: 75°C

Bulk Cable Weight: 200.907 Kg/Km

Max. Recommended Pulling Tension: 1063.120 N

Min. Bend Radius/Minor Axis: 133.350 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

AWM Specification:	UL Style 1641 (30 V 60°C)
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	No
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2004
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	11/U

Flame Test

UL Flame Test:	VW-1
Other Flame Test:	UL2556

Suitability

Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes
Suitability - Burial:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

75

Nom. Inductance:

Inductance (µH/m)

0.318257

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

56.7613

Nominal Velocity of Propagation:

VP (%)

78

Nominal Delay:

Delay (ns/m)

4.2653

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

10.1711

Nom. Inner Shield DC Resistance:

DCR @ 20°C (Ohm/km)

5.2496

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

5.2496

Nom. Attenuation:

Freq. (MHz)	Attenuation (dB/100m)
1.000	0.328
3.600	0.984
10.000	1.641
71.500	3.937
135.000	5.906
270.000	8.531
360.000	10.171
540.000	12.796
720.000	15.421
750.000	15.749
1000.000	18.702

Max. Operating Voltage - UL:

Voltage
30 V RMS

Max. Operating Voltage - Non-UL:

Voltage
300 V RMS

Other Electrical Characteristic 1: Nominal Capacitance 1st Shield to 2nd Shield: 205 pF/ft.

Other Electrical Characteristic 2: Nominal Voltage Breakdown: 20K V RMS

Minimum Return Loss:

Description	Freq. (MHz)	Start Freq. (MHz)	Stop Freq. (MHz)	Min. RL (dB)
		5	450	21

Sweep Test

Sweep Testing: 100% sweep tested 5 MHz to 450 MHz.

Misc. Information (Overall)

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
9232 0101000	305 MT	63.957 KG	BLACK	C	75 OHM TRIAX
9232 010500	152 MT	34.246 KG	BLACK	C	75 OHM TRIAX

Notes:
C = CRATE REEL PUT-UP.

Revision Number: 10 Revision Date: 08-12-2013

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale. Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.