

5306FM Multi-Conductor - Commercial Applications, Addressable Systems

For more Information
please call

1-800-Belden1



General Description:

18 AWG stranded (7x26) bare copper conductors, ceramifiable silicone insulation, Beldfoil® shield, FRPE (low smoke non-halogen) jacket, sequential footage marking every two feet.

Usage (Overall)

Suitable Applications:

Survivability, Survivability from Attach by Fire, Fire Alarm Circuit Integrity, CI, Survivability by NFPA72, Sim to MI, Similar to Mineral Insulated, FPLR-CI, Emergency Circuits, Notification Devices, Fire Pumps, 2 hour fire rating

Physical Characteristics (Overall)

Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
8	18	7x26	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
Silicone Rubber	.034

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Polyester Tape-Aluminum Foil	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
20	7x28	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
FRPE - Flame Retardant Polyethylene	.045

Overall Cable

Overall Cabling Lay Length & Direction:

Length (in.)	Twists (twist/ft)
5.75	2

Overall Cabling Color Code Chart:

Number	Color
1	Black#1
2	Black#2
3	Black#3
4	Black#4
5	Black#5
6	Black#6
7	Black#7
8	Black#8

Overall Nominal Diameter: 0.471 in.

5306FM Multi-Conductor - Commercial Applications, Addressable Systems

Mechanical Characteristics (Overall)

Operating Temperature Range:	-20°C To +105°C
UL Temperature Rating:	105°C
Bulk Cable Weight:	137 lbs/1000 ft.
Max. Recommended Pulling Tension:	179.200 lbs.
Min. Bend Radius/Minor Axis:	4.700 in.

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	FPLR-CI
NEC Articles:	760
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	01/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Flame Test

UL Flame Test:	UL1666 Riser, UL2196 Two Hour Circuit Integrity
----------------	---

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Capacitance Conductor to Conductor:

Capacitance (pF/ft)

27

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

5.86

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

9

Max. Operating Voltage - UL:

Voltage	Description
300 V RMS	FPLR only applications
41 V RMS	CI applications

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 1 Revision Date: 07-18-2011

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications

5306FM Multi-Conductor - Commercial Applications, Addressable Systems

described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.