

1212F Multi-Conductor - Enhanced Category 5e Nonbonded-Pair Cable



For more Information
please call

1-800-Belden1



General Description:

CAT5e+ (350MHz), 4-Pair, F/UTP-Foil shielded, Riser-CMR, Premise Horizontal Cable, 24 AWG solid bare copper conductors, polyolefin insulation, overall Beldfoil® shield, PVC jacket, RJ-45 compatible

Usage (Overall)

Suitable Applications:

Premise Horizontal Cable, Gigabit Ethernet, HDBaseT, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU, Digital Video, RS-422, Noisy Environments, 100 MHz Category 5e

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material
4	24	Solid	BC - Bare Copper

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material
PO - Polyolefin

Outer Shield

Outer Shield Material:

Outer Shield Trade Name	Type	Outer Shield Material	Coverage (%)
Beldfoil®	Tape	Aluminum Foil-Polyester Tape	100

Outer Shield Drain Wire AWG:

AWG	Stranding	Drain Wire Conductor Material
24	7x32	TC - Tinned Copper

Outer Jacket

Outer Jacket Material:

Outer Jacket Material
PVC - Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 6.604 mm

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Operating Temperature Range: -20°C To +75°C

Bulk Cable Weight: 44.646 Kg/Km

1212F Multi-Conductor - Enhanced Category 5e Nonbonded-Pair Cable

Max. Recommended Pulling Tension:	111.205 N
Min. Bend Radius/Minor Axis:	25.400 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

CEC/C(UL) Specification:	CMR
EU Directive 2011/65/EU (ROHS II):	Yes
EU CE Mark:	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	12/09/2011
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1 Category 5e, UL Verified to Category 5e

Flame Test

UL Flame Test:	UL1666 Riser
CSA Flame Test:	FT4

Plenum/Non-Plenum

Plenum (Y/N):	No
Plenum Number:	1213F

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)
49.215

Maximum Capacitance Unbalance (pF/100 m): 330

Nominal Velocity of Propagation:

VP (%)
70

Maximum Delay:

Delay (ns/100 m)
538 @ 100MHz

Max. Delay Skew:

Delay Skew (ns/100 m)
45

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9.38

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

1212F Multi-Conductor - Enhanced Category 5e Nonbonded-Pair Cable

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)	Min. SRL (dB)
1	2.000	70.3	68.3	70.3	66.3	20.000	23.0
4	4.000	61.3	59.3	59.3	55.3	23.000	23.0
8	5.700	56.8	54.8	53.1	49.1	24.500	24.5
10	6.400	55.3	53.3	50.9	46.9	25.000	25.0
16	8.100	52.2	50.2	46.1	42.1	25.000	25.0
20	9.100	50.8	48.8	43.7	39.7	25.000	25.0
25	10.200	49.3	47.3	41.1	37.1	24.300	24.3
31.25	11.400	47.9	45.9	38.5	34.5	23.600	23.6
62.5	16.400	43.4	41.4	29.0	25.0	21.500	21.5
100	21.000	40.3	38.3	21.3	17.3	20.100	20.1
155	26.600	37.4	35.4	12.8	8.9	18.800	
200	30.500	35.8	33.8	7.3	3.3	18.000	
250	34.400	34.3	32.3	1.9		17.300	
300	38.000	33.1	28.2			16.800	
350	41.400	32.1	27.2			16.300	
400	44.600	31.3	26.3			15.900	
450	47.600	30.5	25.6			15.500	

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 15	100 ± 15	67.8	64.8
4	100 ± 15	100 ± 15	55.8	52.8
8	100 ± 15	100 ± 15	49.7	46.7
10	100 ± 15	100 ± 15	47.8	44.8
16	100 ± 15	100 ± 15	43.7	40.7
20	100 ± 15	100 ± 15	41.8	38.8
25	100 ± 15	100 ± 15	39.8	36.8
31.25	100 ± 15	100 ± 15	37.9	34.9
62.5	100 ± 15	100 ± 15	31.9	28.9
100	100 ± 15	100 ± 15	27.8	24.8
155	100 ± 22	100 ± 15	24.0	21.0
200	100 ± 22	100 ± 15	21.8	18.8
250	100 ± 32	100 ± 15	19.8	16.8
300	100 ± 32	100 ± 15	18.2	15.2
350	100 ± 32	100 ± 15	16.9	13.9

Notes (Overall)

Notes: Shield is bonded to jacket inner wall for electrical stability. RJ-45 Compatible. Jacket sequentially marked at 2 ft. intervals. Third party verified to TIA/EIA-568-B.2, Category 5e.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
1212F 002A1000	305 MT	13.608 KG	RED		CAT5E+ 4PR F/UTP CMR RIB
1212F 0021000	305 MT	13.608 KG	RED		CAT5E+ 4PR F/UTP CMR REEL
1212F 003A1000	305 MT	13.608 KG	ORANGE		CAT5E+ 4PR F/UTP CMR RIB
1212F 0031000	305 MT	13.608 KG	ORANGE		CAT5E+ 4PR F/UTP CMR REEL
1212F 004A1000	305 MT	13.608 KG	YELLOW		CAT5E+ 4PR F/UTP CMR RIB
1212F 0041000	305 MT	13.608 KG	YELLOW		CAT5E+ 4PR F/UTP CMR REEL
1212F 005A1000	305 MT	13.608 KG	GREEN, DARK		CAT5E+ 4PR F/UTP CMR RIB
1212F 0051000	305 MT	13.608 KG	GREEN, DARK		CAT5E+ 4PR F/UTP CMR REEL
1212F 006A1000	305 MT	13.608 KG	BLUE, LIGHT		CAT5E+ 4PR F/UTP CMR RIB
1212F 006A500	152 MT	9.299 KG	BLUE, LIGHT	C	CAT5E+ 4PR F/UTP CMR RIB
1212F 0061000	305 MT	13.608 KG	BLUE, LIGHT		CAT5E+ 4PR F/UTP CMR REEL
1212F 008A1000	305 MT	13.608 KG	GRAY		CAT5E+ 4PR F/UTP CMR RIB
1212F 0081000	305 MT	13.608 KG	GRAY		CAT5E+ 4PR F/UTP CMR REEL
1212F 009A1000	305 MT	13.608 KG	WHITE		CAT5E+ 4PR F/UTP CMR RIB
1212F 009A500	152 MT	9.299 KG	WHITE	C	CAT5E+ 4PR F/UTP CMR RIB
1212F 0091000	305 MT	13.608 KG	WHITE		CAT5E+ 4PR F/UTP CMR REEL
1212F 010A1000	305 MT	13.608 KG	BLACK		CAT5E+ 4PR F/UTP CMR RIB

METRIC MEASUREMENT VERSION

1212F Multi-Conductor - Enhanced Category 5e Nonbonded-Pair Cable

1212F 0101000	305 MT	13.608 KG	BLACK		CAT5E+ 4PR F/UTP CMR REEL
---------------	--------	-----------	-------	--	---------------------------

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 10-11-2013

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.