

Absorbent Specification Guide

www.BradyID.com/SPC

Part Numbers	Type	Size	Perforated	Absorbency Factor (gl/g)	Absorbency Capacity (gal)	Shipping Wt. (lbs)	Pallet Qty.*	Quantity
SPC1900	Sweep	19"X100'	n/a	15	26	13	36	1/bale
SPC5510	SPC Boom	5"x10"	n/a	12.1	61	38	12	2/bale
SPC19150	Heavy Wt. Roll	19" x 144'	No	15	35	17	36	1/bale*
SPC-ACID	2lb Acid Neutralizing Polymer Shaker	n/a	n/a	n/a	0.65	2	1200	1/each
SPC-BASE	2lb Base Neutralizing Polymer Shaker	n/a	n/a	n/a	0.65	2	1200	1/each
SPCUN1019	Medium Wt. Roll	15"x150'	Yes, 15" and every 15"	12.5	39	24	15	2/case
SPCUN1113	Medium Wt. Pad	12"x12"	No	16	12.5	16	30	200/case
SPCUN1113-50	Medium Wt. Pad	12"X12"	No	12.5	5.5	4	120	50/case
SPCUN1719	Medium Wt. Pad	15"x19"	Yes, 7.5"	12.5	20.5	14.5	30	100/case
SPCUN3800	Medium Wt. Roll	30"x150'	Yes, 15" and every 15"	12.5	39	27	12	1/case
SR100	Heavy Wt. Pad	15" x19"	No	13	26	14.5	30	100/bale
SR1825	Medium Wt. Pad	15"x19"	No	15	6	3.2	90	25/bale
SR3600	Heavy Wt. Roll	30"x150'	No	15	44	22	18	1/bale
SR3625	Heavy Wt. Pad	30"x30"	No	13	16	9	14	25/bale
SRP75P	Heavy Wt. Roll	7.5" x 50'	Yes, 10"	12.5	3.3	1.85	96	1/bale
SRP100	Heavy Wt. Pad	7.5"x10"	No	12.5	5.5	4	96	100/case
SRP200	Heavy Wt. Pad	7.5"x10"	No	12.5	11.1	7.5	96	200/case
SRPH75P	Heavy Wt. Plus Roll	7.5" x 50'	Yes, 10"	12.5	3.3	1.85	96	1/bale
SRPH100	Heavy Wt. Plus Pad	7.5"x10"	No	12.5	5.5	4	96	100/case
SRPH200	Heavy Wt. Plus Pad	7.5"x10"	No	12.5	11.1	7.5	96	200/case
SRPO75P	Heavy Wt. Roll	7.5" x 50'	Yes, 10"	12.5	3.3	1.85	96	1/bale
SRPO100	Heavy Wt. Pad	7.5"x10"	No	12.5	5.5	4	96	100/case
SRPO200	Heavy Wt. Pad	7.5"x10"	No	12.5	11.1	7.5	96	200/case
SW46	SOC	3"x42"	n/a	3	20	50	16	40/case
SXT15P	Heavy Wt. Roll	15"x150'	Yes, every 18"	12	18	14	30	1/case
SXT30DP	Heavy Wt. Roll	30"x150'	Yes, 15" and every 15"	12	37	26.5	12	1/case
SXT100	Heavy Wt. Pad	15"x19"	Yes, 7.5"	12	19.5	14.5	30	100/case
SXT200	Light Wt. Pad	15"x19"	Yes, 7.5"	14	31.5	18	24	200/case
SXT300	Medium Wt. Pad	15"x19"	Yes, 7.5"	12	17	10	30	100/case
TM19	Heavy Wt. Roll	19"x80'	No	9	26	32	18	2/bale
TM29	Heavy Wt. Roll	29"x80'	No	9	20	24	32	1/bale
TM30	Heavy Wt. Pad	29"x29"	No	9	25	15	15	30/bale
TM58	Heavy Wt. Roll	58"x80'	No	9	55	34	9	1/bale
UXT15P	Heavy Wt. Roll	15"x150'	Yes, every 18"	11	17	14.5	30	1/case
UXT30DP	Medium Wt. Roll	30"x150'	Yes, 15" and every 15"	11	35	27.5	12	1/case
UXT100	Heavy Wt. Pad	15"x19"	Yes, 7.5"	11	19	14.5	30	100/case
UXT200	Light Wt. Pad	15"x19"	Yes, 7.5"	14	31.5	18.5	24	200/case
UXT300	Medium Wt. Pad	15"x19"	Yes, 7.5"	11	17	12	30	100/case
VS12P	Heavy Wt. Roll	12"x60"	Yes, 12"	12.5	13.6	9.5	30	20/case
VS75P	Heavy Wt. Roll	7.5"x50"	Yes, 10"	12.5	5.56	4.27	40	20/case
VSH12P	Heavy Wt. Roll	12"x60"	Yes, 12"	12.5	13.6	9.5	30	20/case
VSH75P	Heavy Wt. Roll	7.5"x50"	Yes, 10"	12.5	5.56	4.27	40	20/case
VSO12P	Heavy Wt. Roll	12"x60"	Yes, 12"	12.5	13.6	9.5	30	20/case
VSO75P	Heavy Wt. Roll	7.5"x50"	Yes, 10"	12.5	5.56	4.27	40	20/case

* In an effort to reduce shipping costs for our customers, pallet quantities may vary.

DISCLAIMER: The above properties are "nominal" values used for PROCESS CONTROL when the product is produced and/or inspected. Performance "nominals" may vary depending upon the specific application, and/or the environment being applied, stored, or shipped. The "Absorbency" Spec and "SPCTM004" test method is based on the protocol of ASTM F726, using SAE20 non-detergent as the Oil Type, medium viscosity.