


ENERGIZER E96

AAAA



Industry Standard Dimensions

mm (inches)




Classification:	Alkaline
Chemical System:	Zinc-Manganese Dioxide (Zn/MnO ₂) No added mercury or cadmium
Designation:	ANSI-25A, IEC-LR8D425, LR61
Nominal Voltage:	1.5 volts
Typical IR:	150 to 300 milliohms (fresh)
Operating Temp:	-18°C to 55°C (0°F to 130°F)
Storage Temp:	-40°C to 50°C (-40°F to 150°F)
Typical Weight:	6.6 grams (0.2 oz.)
Typical Volume:	2.2 cubic centimeters (0.1 cubic inch)
Shelf Life:	5 years at 21°C

*All data shown tested at 21°C unless otherwise stated.


Milliamp-Hours Capacity

Constant Current Discharge to 0.8 Volts




Discharge Profile

Constant Current Discharge




Industry Standard Tests

LIGHTING
5.1 Ohms 5 Min ON 23 Hours/55 Min OFF



LASER POINTER
75 Ohms 1 Hour/Day



Important Notice


This datasheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.

ENERGIZER E96

AAAA


Internal Resistance Profile

Cell Ohmic Resistance - Dual Pulse Method




Constant Power Performance

Typical Characteristics to 0.8 Volts



Constant Current Performance

Typical Characteristics to 0.8 Volts



Important Notice

This datasheet contains typical information specific to products manufactured at the time of its publication.
©Energizer Holdings, Inc. - Contents herein do not constitute a warranty.