

For more Information
please call

1-800-Belden1



General Description:

RG-58/U type, 20 AWG solid .032" bare copper conductor, plenum, FEP teflon insulation, tinned copper braid shield (95% coverage), Flamarrest® jacket.

Physical Characteristics (Overall)

Conductor

AWG:

# Coax	AWG	Stranding	Conductor Material	Dia. (mm)
1	20	Solid	BC - Bare Copper	0.8128

Total Number of Conductors: 1

Insulation

Insulation Material:

Insulation Trade Name	Insulation Material	Dia. (mm)
Teflon®	FEP - Fluorinated Ethylene Propylene	2.7178

Outer Shield

Outer Shield Material:

Type	Outer Shield Material	Coverage (%)
Braid	TC - Tinned Copper	95

Outer Jacket

Outer Jacket Material:

Outer Jacket Trade Name	Outer Jacket Material
Flamarrest®	LS PVC - Low Smoke Polyvinyl Chloride

Overall Cable

Overall Nominal Diameter: 4.039 mm

Mechanical Characteristics (Overall)

Operating Temperature Range: 0°C To +75°C

UL Temperature Rating: 75°C

Bulk Cable Weight: 35.717 Kg/Km

Max. Recommended Pulling Tension: 209.065 N

Min. Bend Radius/Minor Axis: 44.450 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification: CMP

CEC/C(UL) Specification: CMP

EU Directive 2011/65/EU (ROHS II): Yes

EU CE Mark: No

EU Directive 2000/53/EC (ELV): Yes

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 10/01/2005

EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
RG Type:	58/U

Flame Test

UL Flame Test:	NFPA 262
CSA Flame Test:	FT6

Suitability

Suitability - Indoor:	Yes
-----------------------	-----

Plenum/Non-Plenum

Plenum (Y/N):	Yes
Non-Plenum Number:	8240

Electrical Characteristics (Overall)

Nom. Characteristic Impedance:

Impedance (Ohm)

53

Nom. Inductance:

Inductance (µH/m)

0.22967

Nom. Capacitance Conductor to Shield:

Capacitance (pF/m)

86.6184

Nominal Velocity of Propagation:

VP (%)

69.5

Nominal Delay:

Delay (ns/m)

4.85588

Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/km)

33.4662

Nominal Outer Shield DC Resistance:

DCR @ 20°C (Ohm/km)

21.9827

Nom. Attenuation:

Freq. (MHz) Attenuation (dB/100m)

1	1.6405
10	3.9372
50	9.843
100	14.1083
200	20.9984
400	31.8257
700	44.9497
900	52.8241
1000	56.7613

Nom. Power Rating:

Freq. (MHz) Rating (W)

1	4798.7
10	1937.2

50	782.4
100	542.2
200	370.3
400	248.5
700	177.7
900	153.0
1000	143.2

Max. Operating Voltage - UL:

Voltage
300 V RMS

Max. Operating Voltage - Non-UL:

Voltage
1400 V RMS

Notes (Overall)

Notes: Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
82240 877U1000	305 MT	11.793 KG	NATURAL		#20 FEP RG58/U FLMRST
82240 877U500	152 MT	6.124 KG	NATURAL		#20 FEP RG58/U FLMRST
82240 8771000	305 MT	11.793 KG	NATURAL	C	#20 FEP RG-58/U FLMRST

Notes:

C = CRATE REEL PUT-UP.

Revision Number: 2 Revision Date: 08-27-2013

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.