


121700A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

For more Information
please call

1-800-Belden1



General Description:

24 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, PVC inner jacket, rip cord, polyester wrap, aluminum interlocked armor, industrial grade outer PVC jacket. Sequential marking at one meter intervals.

Usage (Overall)

Suitable Applications: Industrial Ethernet Cable, Harsh Environments, 350MHz Enhanced Category 5e, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, RJ-45 Compatible, Flexible Applications, Armored for Extra Protection

Physical Characteristics (Overall)

Conductor

AWG:

# Pairs	AWG	Stranding	Conductor Material	Dia. (mm)
4	24	Solid	BC - Bare Copper	0.508

Total Number of Conductors: 8

Insulation

Insulation Material:

Insulation Material	Wall Thickness (mm)	Dia. (mm)
PO - Polyolefin	0.229	0.965

Inner Jacket

Inner Jacket Material:

Inner Jacket Material	Nom. Dia. (mm)
PVC - Polyvinyl Chloride	5.232

Inner Jacket Ripcord: Yes

Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (mm)
Industrial Grade PVC - Polyvinyl Chloride	1.143

Outer Jacket over Armor (y/n): Yes

Armor

Armor Type: Interlocked

Armor Material: Aluminum

Diameter over Armor: .463

Overall Cable

Overall Cabling Separator Material: Polyester

Overall Nominal Diameter: 14.046 mm

121700A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

Pair

Pair Color Code Chart:

Number	Color
1	White/Blue Stripe & Blue
2	White/Orange Stripe & Orange
3	White/Green Stripe & Green
4	White/Brown Stripe & Brown

Mechanical Characteristics (Overall)

Storage Temperature Range:	-40°C To +85°C
Installation Temperature Range:	-25°C To +75°C
Operating Temperature Range:	-40°C To +75°C
Bulk Cable Weight:	150.308 Kg/Km
Max. Recommended Pulling Tension:	177.928 N
Min. Bend Radius/Minor Axis:	165.100 mm

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

NEC/(UL) Specification:	CM
CEC/C(UL) Specification:	CMG, HL
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2002/95/EC (RoHS):	Yes
EU RoHS Compliance Date (mm/dd/yyyy):	10/01/2005
EU Directive 2002/96/EC (WEEE):	Yes
EU Directive 2003/11/EC (BFR):	Yes
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes
Other Specification:	NEMA WC-63.1 Category 5e, UL verified to Category 5e

Flame Test

UL Flame Test:	UL1685 UL Loading
CSA Flame Test:	FT4

Suitability

Sunlight Resistance:	Yes
Oil Resistance:	Yes

Plenum/Non-Plenum

Plenum (Y/N):	No
---------------	----

Electrical Characteristics (Overall)

Nom. Mutual Capacitance:

Capacitance (pF/m)	49.215
--------------------	--------

Maximum Capacitance Unbalance (pF/100 m):	66
---	----

Nominal Velocity of Propagation:

VP (%)	70
--------	----

Maximum Delay:

Delay (ns/100 m)	
------------------	--

METRIC MEASUREMENT VERSION

121700A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

510

Max. Delay Skew:

Delay Skew (ns/100 m)
25

Maximum Conductor DC Resistance:

DCR @ 20°C (Ohm/100 m)
9

Max. Operating Voltage - UL:

Voltage
300 V RMS

Maximum DCR Unbalanced:

DCR Unbalance @ 20°C (%)
3

Electrical Characteristics-Premise (Overall)

Premise Cable Electrical Table 1:

Freq. (MHz)	Max. Attenuation (dB/100 m)	Min. NEXT (dB)	Min. PSNEXT (dB)	Min. ACR (dB)	Min. PSACR (dB)	Min RL (dB)
1	2.0	65.3	65.3	63.3	63.3	20.0
4	4.0	56.3	56.3	52.3	52.3	23.0
8	5.7	51.8	51.8	46.1	46.1	24.5
10	6.4	50.3	50.3	43.9	43.9	25.0
16	8.1	47.3	47.3	39.1	39.1	25.0
20	9.2	45.8	45.8	35.2	35.2	25.0
25	10.3	44.3	44.3	34.1	34.1	24.3
31.25	11.6	42.9	42.9	31.3	31.3	23.6
62.5	16.8	38.4	38.4	21.6	21.6	21.5
100	21.7	35.3	35.3	17.1	17.1	20.1
155	27.7	32.5	32.5	4.7	4.7	19.0
200	32.0	30.8	30.8	3.0	3.0	19.0
250	36.4	29.3	29.3	>0	>0	18.0
300	40.5	28.2	28.2	>0	>0	18.0
310	41.3	27.9	27.9			18.0
350	44.3	27.2	27.2			17.0

Premise Cable Electrical Table 2:

Freq. (MHz)	Input (Unfitted) Imp. (Ohms)	Fitted Impedance	Min. ELFEXT (dB)	Min. PSELFEXT (dB)
1	100 ± 12	105 ± 10	63.8	60.8
4	100 ± 12	100 ± 10	51.7	48.7
8	100 ± 12	100 ± 10	45.7	42.7
10	100 ± 12	100 ± 10	43.8	40.8
16	100 ± 12	100 ± 10	39.7	36.7
20	100 ± 12	100 ± 10	37.7	34.7
25	100 ± 15	100 ± 10	35.8	32.8
31.25	100 ± 15	100 ± 10	33.9	30.9
62.5	100 ± 15	100 ± 10	27.8	24.8
100	100 ± 15	100 ± 10	23.8	20.8
155	100 ± 18	100 ± 10	19.9	16.9
200	100 ± 20	100 ± 10	17.7	14.7
250	100 ± 20	100 ± 10	15.8	12.8
300	100 ± 20	100 ± 10	14.2	11.2
310	100 ± 20	100 ± 10	13.9	10.9
350	100 ± 22	100 ± 10	12.9	9.9

Notes (Overall)

Notes: US Patent #'s 5606151; 5734126 Operating temperatures are subject to length de-rating. Cable passes -40C Cold Bend per UL 1581.

Put Ups and Colors:

121700A Multi-Conductor - Category 5e DataTuff® Twisted Pair Cable

Item #	Putup	Ship Weight	Color	Notes	Item Desc
121700A 0081000	305 MT	57.606 KG	GRAY	C Z	1700A ALUM ARMOR PVC
121700A 0101000	305 MT	62.596 KG	BLACK	C Z	1700A ALUM ARMOR PVC
121700A 0103000	914 MT	198.674 KG	BLACK	C Z	1700A ALUM ARMOR PVC
121700A 0105000	1,524 MT	315.248 KG	BLACK	C Z	1700A ALUM ARMOR PVC

Notes:

C = CRATE REEL PUT-UP.

Z = FINAL PUT-UP LENGTH MAY VARY (+ OR -) 10% FOR SPOOLS OR REELS AND(+ OR -) 5% FOR UNREEL CARTONS FROM LENGTH SHOWN.

Revision Number: 12 Revision Date: 08-02-2013

© 2013 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.