


Short circuit proof PCB transformer AVB 0,35/2/18



Advantages


Minimum size at high output
Unconditionally short-circuit proof
Double input voltage for series or parallel connection
Also with double output voltage for series or parallel connection
Designed for high ambient temperatures
Permanent corrosion protection, high insulation value and maximum electrical reliability thanks to XtraDensiFill resin encapsulation
Coil shell in 2-chamber technology
Self-extinguishing potting and hood material

Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As a safety transformer for the safe electrical isolation of the input and output sides. The transformer is suitable for creating SELV and PELV circuits because of the limit on the output voltage.

Circuit Diagram



Standards



Mains transformer
to: VDE 0570 Teil 2-1, DIN EN 61558-2-1, EN 61558-2-1, IEC 61558-2-1, UL 5085-1/-2, CSA 22.2 No.66

Approvals



UL 5085-1/-2, CSA 22.2 No.66



Short circuit proof PCB transformer


AVB 0,35/2/18

Electrical data

Type	AVB 0,35/2/18
Input	
Rated input Voltage	2 x 115 Vac
Rated frequency	50 - 60 Hz
Output	
Rated output voltage	2 x 18 Vac
Rated Power	0.35 VA
No-load voltage (app. x factor)	1.80
No-load loss (typ.)	1.30 W
Efficiency	30 %
Standards	
Classification	Mains transformer
Approvals	
Approvals	cURus
Environment	
Ambient temperature max.	70 °C
Safety and protection	
Type	encapsulated
Class of Insulation System	VDE-B, UL=class 105
Protection index	IP 00
Safety class (prepared)	II
Short circuit strength	inherently short-circuit proof
Order numbers	
Order Number	AVB 0,35/2/18

Mechanical data

Type	AVB 0,35/2/18
Terminal and mounting	
Terminals	Pins for printed circuit boards
Pin (ø)	0.6
Measures and weights	
Core type	EE 20/6,1
Weight	0.02 kg



Subjects to change.