

This product is going obsolete. Please use D4 series for all new designs.

MINIATURE

K Series

Features


- Choice of current ratings up to 25 amps
- Choice of actuators
- Choice of terminals
- 3 contact arrangements
- Choice of operating force
- Long mechanical life
- Wiping contact action
- Snap over actuators
- Agency approved extended life versions

International Approved Versions

K Series switches, except 25A (KWS), are internationally approved. Switches with straight terminals may require insulated connectors for international approval.

Electrical Ratings

Switch Series	BS EN 605 Rating	UL 1054 Rating	Electrical Life at Rated Load	
			According to VDE (Min. Operations)	According to UL (Min. Operations)
KWA/KWB	50mA, 28VDC	50mA, 28VDC	50,000	100,000
KWC/KWD	1(0.5)A, 250VAC	1.0A, 125/250VAC	50,000	100,000
KWE/KWF	3(1)A, 250VAC	3A, 1/10 HP, 125/250VAC	50,000	100,000
KWG/KWH	6(2)A, 250VAC	5A, 1/4 HP, 125/250VAC	50,000	100,000
KWJ/KWK	10(3)A, 250VAC	10A, 1/2 HP, 125/250VAC	50,000	100,000
KWL	N/A	15.1A, 1/2 HP, 125/250VAC 5A, 125VAC Lamp Load (85°C only) 0.5A, 125VDC (85°C only) 0.25A, 250VDC (85°C only)	N/A	100,000
KWM	16(4)A, 250VAC	15.1A, 1/2 HP, 125/250VAC 0.5A, 125VDC (85°C and 150°C only) 0.25A, 250VDC (85°C and 150°C only) 15.1A, 1/2 HP, 125/250VAC (200°C only)	50,000	100,000
KWS	N/A	25A, 125/250VAC (85°C only) 1 HP, 125VAC (85°C only) 2 HP, 250VAC (85°C only)	N/A	100,000



Specifications

Electrical

Temperature Rating: -40° to +85°C, 150°C or 200°C

Flammability Rating: UL94V-0

Materials

Case/Cover: Thermoplastic Polyester (85°C or 150°C)
Liquid Crystal Polymer (200°C)


Button: Thermoplastic Acetal (85°C)
Thermoplastic Polyester (150°C)
Liquid Crystal Polymer (200°C)

Auxiliary Actuator: Cold-Rolled Steel (Nickel-Plated)

Terminals: Brass
Copper (25 amp only)

Moving Blade: Beryllium Copper


Contacts: Silver Alloy (except KWA and KWB — Gold-Plated)



This product is going obsolete. Please use D4 series for all new designs.




Dimensions inches (mm)



Actuators

Standard type snap over hinged lever and roller actuators are available in choice of two pivot positions. Lengths are dimensioned from centerline of switch upper mounting hole as shown here.

Auxiliary Actuator



Mounting

Recommended mounting screw size: #4-40 Round head. Recommended torque on screw: 3 inch lbs. max.

Actuator Specifications

Actuator Type	Switch Type	Maximum Operating Force (gms.)						Maximum Pre-Travel inches (mm)	Operating Point* inches (mm)	Minimum Over-Travel inches (mm)	Max. Movement Differential inches (mm)	Actuation Length** inches (mm)
		KWA	KWC, KWE	KWG	KWD, KWI	KWJ	KWH, KWK, KWM					
A		25		50	75		150	0.056 (1.42)	0.602/0.563 (15.29/14.30)	0.050 (1.27)	0.010 (0.25)	—
B		25		50	75		150	0.075 (1.90)	0.631/0.585 (16.03/14.85)	0.051 (1.29)	0.012 (0.31)	0.865 (21.97)
C		14		27	40		80	0.146 (3.71)	0.659/0.569 (16.74/14.45)	0.085 (2.16)	0.030 (0.76)	1.400 (35.56)
D		6		12	18		36	0.330 (8.38)	0.725/0.527 (18.41/13.38)	0.182 (4.62)	0.051 (1.30)	2.722 (69.14)
E		15		30	44		88	0.133 (3.38)	0.653/0.572 (16.59/14.52)	0.074 (1.88)	0.021 (0.54)	1.077 (27.36)
F		8		15	23		45	0.267 (6.78)	0.702/0.541 (17.83/13.74)	0.146 (3.71)	0.041 (1.05)	1.612 (40.94)
G		4		7	10		20	0.593 (15.06)	0.820/0.467 (20.83/11.86)	0.407 (10.33)	0.091 (2.32)	2.934 (74.52)
J		16		31	46		92	0.128 (3.25)	0.776/0.698 (19.71/17.72)	0.088 (2.23)	0.020 (0.51)	1.254 (31.85)
M		9		18	26		52	0.232 (5.88)	0.813/0.675 (20.65/17.14)	0.115 (2.92)	0.036 (0.92)	1.466 (37.24)
Q		15		29	43		85	0.140 (3.56)	0.872/0.786 (22.15/19.96)	0.096 (2.43)	0.022 (0.56)	1.340 (34.04)
T		8		16	24		47	0.253 (6.43)	0.912/0.761 (23.16/19.32)	0.173 (4.39)	0.039 (1.00)	1.552 (39.42)

*Measured above reference line. Refer to dimensional drawing above. **Actuator tolerance ± 0.031 inches (0.79mm).

Ordering Information

KW		A		D		Q		A C A	
Series/Prefix				Code		Code		Snap Over Actuators	
Light	Standard	Current	Notes	Code	Temperature Rating	Code	Terminal Type	Code	Type
Code	Force	Code	Force	Rating		Code	Terminal Type	Code	Actuation Length
A	25	B	75	50mA	1	P4	0.062 x 0.032 (1.57 x 0.81) PCB*	A	Button
C	25	D	75	1A	1	Q	0.187 x 0.020 (4.75 x 0.51) Straight	B	Straight SR
E	25	F	75	3A	1	R	0.187 x 0.020 (4.75 x 0.51) Dog Leg	C	Straight SR
G	50	H	150	5A	1	S	0.187 x 0.032 (4.75 x 0.81) Straight	D	Straight SR
J	75	K	150	10A	1	T	0.187 x 0.032 (4.75 x 0.81) Dog Leg	E	Straight HR
		L	150	15A	3	V	0.250 x 0.032 (6.35 x 0.81) Straight	F	Straight HR
		M	150	15A	2	W	0.250 x 0.032 (6.35 x 0.81) Dog Leg	G	Straight HR
		S	225	25A	3, 5			J	SIM Roller SR
								M	SIM Roller HR
								Y†	Roller SR
								Q	Roller SR
								W†	Roller HR
								T	Roller HR

Specifications subject to change without notice.

*Available as internal mounting only.